

Firm Silicone Foam

Silicone displays excellent resistance to high and low temperatures, compression set, chemicals and weather. Applications include gaskets, heat shields, fire stops, cushions, and insulation for a wide variety of applications. This firm Silicone is stronger and more durable than our standard offering for the most demanding of applications.



Part Number	Shape	Cell Type	Material	Grade	Thickness	Width	Length	Color	Firmness	Backing Type	Texture	Specs Met
ZUSASSR-F-1	Strip	Closed Cell	Silicone	Standard	1/16"	1/2"	10 ft.	Red	Firm (14+ psi)	High Temperature Adhesive	Textured	ASTM D1056 2D4
ZUSASSR-F-6	Strip	Closed Cell	Silicone	Standard	1/16"	3/4"	10 ft.	Red	Firm (14+ psi)	High Temperature Adhesive	Textured	ASTM D1056 2D4
ZUSASSR-F-11	Strip	Closed Cell	Silicone	Standard	1/16"	1"	10 ft.	Red	Firm (14+ psi)	High Temperature Adhesive	Textured	ASTM D1056 2D4
ZUSASSR-F-16	Strip	Closed Cell	Silicone	Standard	1/16"	2"	10 ft.	Red	Firm (14+ psi)	High Temperature Adhesive	Textured	ASTM D1056 2D4
ZUSASSR-F-2	Strip	Closed Cell	Silicone	Standard	1/8"	1/2"	10 ft.	Red	Firm (14+ psi)	High Temperature Adhesive	Textured	ASTM D1056 2D4
ZUSASSR-F-7	Strip	Closed Cell	Silicone	Standard	1/8"	3/4"	10 ft.	Red	Firm (14+ psi)	High Temperature Adhesive	Textured	ASTM D1056 2D4
ZUSASSR-F-12	Strip	Closed Cell	Silicone	Standard	1/8"	1"	10 ft.	Red	Firm (14+ psi)	High Temperature Adhesive	Textured	ASTM D1056 2D4
ZUSASSR-F-17	Strip	Closed Cell	Silicone	Standard	1/8"	2"	10 ft.	Red	Firm (14+ psi)	High Temperature Adhesive	Textured	ASTM D1056 2D4
ZUSASSR-F-3	Strip	Closed Cell	Silicone	Standard	1/4"	1/2"	10 ft.	Red	Firm (14+ psi)	High Temperature Adhesive	Textured	ASTM D1056 2D4
ZUSASSR-F-8	Strip	Closed Cell	Silicone	Standard	1/4"	3/4"	10 ft.	Red	Firm (14+ psi)	High Temperature Adhesive	Textured	ASTM D1056 2D4
ZUSASSR-F-13	Strip	Closed Cell	Silicone	Standard	1/4"	1"	10 ft.	Red	Firm (14+ psi)	High Temperature Adhesive	Textured	ASTM D1056 2D4
ZUSASSR-F-18	Strip	Closed Cell	Silicone	Standard	1/4"	2"	10 ft.	Red	Firm (14+ psi)	High Temperature Adhesive	Textured	ASTM D1056 2D4
ZUSASSR-F-4	Strip	Closed Cell	Silicone	Standard	3/8"	1/2"	10 ft.	Red	Firm (14+ psi)	High Temperature Adhesive	Textured	ASTM D1056 2D4
ZUSASSR-F-9	Strip	Closed Cell	Silicone	Standard	3/8"	3/4"	10 ft.	Red	Firm (14+ psi)	High Temperature Adhesive	Textured	ASTM D1056 2D4
ZUSASSR-F-14	Strip	Closed Cell	Silicone	Standard	3/8"	1"	10 ft.	Red	Firm (14+ psi)	High Temperature Adhesive	Textured	ASTM D1056 2D4
ZUSASSR-F-19	Strip	Closed Cell	Silicone	Standard	3/8"	2"	10 ft.	Red	Firm (14+ psi)	High Temperature Adhesive	Textured	ASTM D1056 2D4
ZUSASSR-F-5	Strip	Closed Cell	Silicone	Standard	1/2"	1/2"	10 ft.	Red	Firm (14+ psi)	High Temperature Adhesive	Textured	ASTM D1056 2D4
ZUSASSR-F-10	Strip	Closed Cell	Silicone	Standard	1/2"	3/4"	10 ft.	Red	Firm (14+ psi)	High Temperature Adhesive	Textured	ASTM D1056 2D4
ZUSASSR-F-15	Strip	Closed Cell	Silicone	Standard	1/2"	1"	10 ft.	Red	Firm (14+ psi)	High Temperature Adhesive	Textured	ASTM D1056 2D4
ZUSASSR-F-20	Strip	Closed Cell	Silicone	Standard	1/2"	2"	10 ft.	Red	Firm (14+ psi)	High Temperature Adhesive	Textured	ASTM D1056 2D4
ZUSASSR-F-201	Sheet	Closed Cell	Silicone	Standard	1/16"	12"	12"	Red	Firm (14+ psi)	Plain	Textured	ASTM D1056 2D4
ZUSASSR-F-206	Sheet	Closed Cell	Silicone	Standard	1/16"	12"	24"	Red	Firm (14+ psi)	Plain	Textured	ASTM D1056 2D4
ZUSASSR-F-202	Sheet	Closed Cell	Silicone	Standard	1/8"	12"	12"	Red	Firm (14+ psi)	Plain	Textured	ASTM D1056 2D4
ZUSASSR-F-207	Sheet	Closed Cell	Silicone	Standard	1/8"	12"	24"	Red	Firm (14+ psi)	Plain	Textured	ASTM D1056 2D4
ZUSASSR-F-203	Sheet	Closed Cell	Silicone	Standard	1/4"	12"	12"	Red	Firm (14+ psi)	Plain	Textured	ASTM D1056 2D4
ZUSASSR-F-208	Sheet	Closed Cell	Silicone	Standard	1/4"	12"	24"	Red	Firm (14+ psi)	Plain	Textured	ASTM D1056 2D4
ZUSASSR-F-204	Sheet	Closed Cell	Silicone	Standard	3/8"	12"	12"	Red	Firm (14+ psi)	Plain	Textured	ASTM D1056 2D4
ZUSASSR-F-209	Sheet	Closed Cell	Silicone	Standard	3/8"	12"	24"	Red	Firm (14+ psi)	Plain	Textured	ASTM D1056 2D4
ZUSASSR-F-205	Sheet	Closed Cell	Silicone	Standard	1/2"	12"	12"	Red	Firm (14+ psi)	Plain	Textured	ASTM D1056 2D4
ZUSASSR-F-210	Sheet	Closed Cell	Silicone	Standard	1/2"	12"	24"	Red	Firm (14+ psi)	Plain	Textured	ASTM D1056 2D4
ZUSASSR-F-211	Sheet	Closed Cell	Silicone	Standard	1/16"	12"	12"	Red	Firm (14+ psi)	High Temperature Adhesive	Textured	ASTM D1056 2D4
ZUSASSR-F-216	Sheet	Closed Cell	Silicone	Standard	1/16"	12"	24"	Red	Firm (14+ psi)	High Temperature Adhesive	Textured	ASTM D1056 2D4
ZUSASSR-F-212	Sheet	Closed Cell	Silicone	Standard	1/8"	12"	12"	Red	Firm (14+ psi)	High Temperature Adhesive	Textured	ASTM D1056 2D4
ZUSASSR-F-217	Sheet	Closed Cell	Silicone	Standard	1/8"	12"	24"	Red	Firm (14+ psi)	High Temperature Adhesive	Textured	ASTM D1056 2D4
ZUSASSR-F-213	Sheet	Closed Cell	Silicone	Standard	1/4"	12"	12"	Red	Firm (14+ psi)	High Temperature Adhesive	Textured	ASTM D1056 2D4