

# Cords

## Multipurpose Neoprene Foam

Cords are often used to fill gaps, channels, and make custom seals. Foam is easy to compress and conforms to uneven surfaces. Neoprene is a good multipurpose choice with its balance of strength and resistance to oil and weather.



Part Number	Shape	Cell Type	Material	Grade	Cross Section	Length	Color	Firmness	Texture	Specs Met
ZUSA287125-300	Cord	Closed Cell	Neoprene	Standard	1/8"	300 ft.	Black	Medium (9 - 13 psi)	Smooth	ASTM D1056 2C3
ZUSA287125-100	Cord	Closed Cell	Neoprene	Standard	1/8"	100 ft.	Black	Medium (9 - 13 psi)	Smooth	ASTM D1056 2C3
ZUSA287125-30	Cord	Closed Cell	Neoprene	Standard	1/8"	30 ft.	Black	Medium (9 - 13 psi)	Smooth	ASTM D1056 2C3
ZUSA287125-15	Cord	Closed Cell	Neoprene	Standard	1/8"	15 ft.	Black	Medium (9 - 13 psi)	Smooth	ASTM D1056 2C3
ZUSA287125-3	Cord	Closed Cell	Neoprene	Standard	1/8"	3 ft.	Black	Medium (9 - 13 psi)	Smooth	ASTM D1056 2C3
ZUSA287187-300	Cord	Closed Cell	Neoprene	Standard	3/16"	300 ft.	Black	Medium (9 - 13 psi)	Smooth	ASTM D1056 2C3
ZUSA287187-100	Cord	Closed Cell	Neoprene	Standard	3/16"	100 ft.	Black	Medium (9 - 13 psi)	Smooth	ASTM D1056 2C3
ZUSA287187-30	Cord	Closed Cell	Neoprene	Standard	3/16"	30 ft.	Black	Medium (9 - 13 psi)	Smooth	ASTM D1056 2C3
ZUSA287187-15	Cord	Closed Cell	Neoprene	Standard	3/16"	15 ft.	Black	Medium (9 - 13 psi)	Smooth	ASTM D1056 2C3
ZUSA287187-3	Cord	Closed Cell	Neoprene	Standard	3/16"	3 ft.	Black	Medium (9 - 13 psi)	Smooth	ASTM D1056 2C3
ZUSA287250-300	Cord	Closed Cell	Neoprene	Standard	1/4"	300 ft.	Black	Medium (9 - 13 psi)	Smooth	ASTM D1056 2C3
ZUSA287250-100	Cord	Closed Cell	Neoprene	Standard	1/4"	100 ft.	Black	Medium (9 - 13 psi)	Smooth	ASTM D1056 2C3
ZUSA287250-30	Cord	Closed Cell	Neoprene	Standard	1/4"	30 ft.	Black	Medium (9 - 13 psi)	Smooth	ASTM D1056 2C3
ZUSA287250-15	Cord	Closed Cell	Neoprene	Standard	1/4"	15 ft.	Black	Medium (9 - 13 psi)	Smooth	ASTM D1056 2C3
ZUSA287250-3	Cord	Closed Cell	Neoprene	Standard	1/4"	3 ft.	Black	Medium (9 - 13 psi)	Smooth	ASTM D1056 2C3
ZUSA287312-300	Cord	Closed Cell	Neoprene	Standard	5/16"	300 ft.	Black	Medium (9 - 13 psi)	Smooth	ASTM D1056 2C3
ZUSA287312-100	Cord	Closed Cell	Neoprene	Standard	5/16"	100 ft.	Black	Medium (9 - 13 psi)	Smooth	ASTM D1056 2C3
ZUSA287312-30	Cord	Closed Cell	Neoprene	Standard	5/16"	30 ft.	Black	Medium (9 - 13 psi)	Smooth	ASTM D1056 2C3
ZUSA287312-15	Cord	Closed Cell	Neoprene	Standard	5/16"	15 ft.	Black	Medium (9 - 13 psi)	Smooth	ASTM D1056 2C3
ZUSA287312-3	Cord	Closed Cell	Neoprene	Standard	5/16"	3 ft.	Black	Medium (9 - 13 psi)	Smooth	ASTM D1056 2C3
ZUSA287375-300	Cord	Closed Cell	Neoprene	Standard	3/8"	300 ft.	Black	Medium (9 - 13 psi)	Smooth	ASTM D1056 2C3
ZUSA287375-100	Cord	Closed Cell	Neoprene	Standard	3/8"	100 ft.	Black	Medium (9 - 13 psi)	Smooth	ASTM D1056 2C3
ZUSA287375-30	Cord	Closed Cell	Neoprene	Standard	3/8"	30 ft.	Black	Medium (9 - 13 psi)	Smooth	ASTM D1056 2C3
ZUSA287375-15	Cord	Closed Cell	Neoprene	Standard	3/8"	15 ft.	Black	Medium (9 - 13 psi)	Smooth	ASTM D1056 2C3
ZUSA287375-3	Cord	Closed Cell	Neoprene	Standard	3/8"	3 ft.	Black	Medium (9 - 13 psi)	Smooth	ASTM D1056 2C3
ZUSA287500-300	Cord	Closed Cell	Neoprene	Standard	1/2"	300 ft.	Black	Medium (9 - 13 psi)	Smooth	ASTM D1056 2C3
ZUSA287500-100	Cord	Closed Cell	Neoprene	Standard	1/2"	100 ft.	Black	Medium (9 - 13 psi)	Smooth	ASTM D1056 2C3
ZUSA287500-30	Cord	Closed Cell	Neoprene	Standard	1/2"	30 ft.	Black	Medium (9 - 13 psi)	Smooth	ASTM D1056 2C3
ZUSA287500-15	Cord	Closed Cell	Neoprene	Standard	1/2"	15 ft.	Black	Medium (9 - 13 psi)	Smooth	ASTM D1056 2C3
ZUSA287500-3	Cord	Closed Cell	Neoprene	Standard	1/2"	3 ft.	Black	Medium (9 - 13 psi)	Smooth	ASTM D1056 2C3
ZUSA287625-100	Cord	Closed Cell	Neoprene	Standard	5/8"	100 ft.	Black	Medium (9 - 13 psi)	Smooth	ASTM D1056 2C3
ZUSA287625-30	Cord	Closed Cell	Neoprene	Standard	5/8"	30 ft.	Black	Medium (9 - 13 psi)	Smooth	ASTM D1056 2C3
ZUSA287625-15	Cord	Closed Cell	Neoprene	Standard	5/8"	15 ft.	Black	Medium (9 - 13 psi)	Smooth	ASTM D1056 2C3
ZUSA287625-3	Cord	Closed Cell	Neoprene	Standard	5/8"	3 ft.	Black	Medium (9 - 13 psi)	Smooth	ASTM D1056 2C3
ZUSA287750-100	Cord	Closed Cell	Neoprene	Standard	3/4"	100 ft.	Black	Medium (9 - 13 psi)	Smooth	ASTM D1056 2C3
ZUSA287750-30	Cord	Closed Cell	Neoprene	Standard	3/4"	30 ft.	Black	Medium (9 - 13 psi)	Smooth	ASTM D1056 2C3
ZUSA287750-15	Cord	Closed Cell	Neoprene	Standard	3/4"	15 ft.	Black	Medium (9 - 13 psi)	Smooth	ASTM D1056 2C3
ZUSA287750-3	Cord	Closed Cell	Neoprene	Standard	3/4"	3 ft.	Black	Medium (9 - 13 psi)	Smooth	ASTM D1056 2C3
ZUSA287100-100	Cord	Closed Cell	Neoprene	Standard	1"	100 ft.	Black	Medium (9 - 13 psi)	Smooth	ASTM D1056 2C3
ZUSA287100-30	Cord	Closed Cell	Neoprene	Standard	1"	30 ft.	Black	Medium (9 - 13 psi)	Smooth	ASTM D1056 2C3
ZUSA287100-15	Cord	Closed Cell	Neoprene	Standard	1"	15 ft.	Black	Medium (9 - 13 psi)	Smooth	ASTM D1056 2C3
ZUSA287100-3	Cord	Closed Cell	Neoprene	Standard	1"	3 ft.	Black	Medium (9 - 13 psi)	Smooth	ASTM D1056 2C3