

# Santoprene Tubing

Santoprene tubing is used in applications that require movement. Santoprene is highly flexible and can withstand harsh chemicals.



Part Number	Material	ID	OD	Wall Thickness	Length	Durometer	Reinforcement	Color	Clarity	Specs Met
ZUSA-HT-4780	Santoprene Rubber	2mm	4mm	1mm	100 ft.	55A	None	Natural	Opaque	
ZUSA-HT-4789	Santoprene Rubber	2mm	4mm	1mm	50 ft.	55A	None	Natural	Opaque	
ZUSA-HT-4798	Santoprene Rubber	2mm	4mm	1mm	25 ft.	55A	None	Natural	Opaque	
ZUSA-HT-4807	Santoprene Rubber	2mm	4mm	1mm	10 ft.	55A	None	Natural	Opaque	
ZUSA-HT-4781	Santoprene Rubber	3mm	5mm	1mm	100 ft.	55A	None	Natural	Opaque	
ZUSA-HT-4790	Santoprene Rubber	3mm	5mm	1mm	50 ft.	55A	None	Natural	Opaque	
ZUSA-HT-4799	Santoprene Rubber	3mm	5mm	1mm	25 ft.	55A	None	Natural	Opaque	
ZUSA-HT-4808	Santoprene Rubber	3mm	5mm	1mm	10 ft.	55A	None	Natural	Opaque	
ZUSA-HT-4782	Santoprene Rubber	4mm	7mm	1.5mm	100 ft.	55A	None	Natural	Opaque	
ZUSA-HT-4791	Santoprene Rubber	4mm	7mm	1.5mm	50 ft.	55A	None	Natural	Opaque	
ZUSA-HT-4800	Santoprene Rubber	4mm	7mm	1.5mm	25 ft.	55A	None	Natural	Opaque	
ZUSA-HT-4809	Santoprene Rubber	4mm	7mm	1.5mm	10 ft.	55A	None	Natural	Opaque	
ZUSA-HT-4783	Santoprene Rubber	5mm	8mm	1.5mm	100 ft.	55A	None	Natural	Opaque	
ZUSA-HT-4792	Santoprene Rubber	5mm	8mm	1.5mm	50 ft.	55A	None	Natural	Opaque	
ZUSA-HT-4801	Santoprene Rubber	5mm	8mm	1.5mm	25 ft.	55A	None	Natural	Opaque	
ZUSA-HT-4810	Santoprene Rubber	5mm	8mm	1.5mm	10 ft.	55A	None	Natural	Opaque	
ZUSA-HT-4784	Santoprene Rubber	6mm	10mm	2mm	100 ft.	55A	None	Natural	Opaque	
ZUSA-HT-4793	Santoprene Rubber	6mm	10mm	2mm	50 ft.	55A	None	Natural	Opaque	
ZUSA-HT-4802	Santoprene Rubber	6mm	10mm	2mm	25 ft.	55A	None	Natural	Opaque	
ZUSA-HT-4811	Santoprene Rubber	6mm	10mm	2mm	10 ft.	55A	None	Natural	Opaque	
ZUSA-HT-4820	Santoprene Rubber	6mm	10mm	2mm	5 ft.	55A	None	Natural	Opaque	
ZUSA-HT-4785	Santoprene Rubber	8mm	12mm	2mm	100 ft.	55A	None	Natural	Opaque	
ZUSA-HT-4794	Santoprene Rubber	8mm	12mm	2mm	50 ft.	55A	None	Natural	Opaque	
ZUSA-HT-4803	Santoprene Rubber	8mm	12mm	2mm	25 ft.	55A	None	Natural	Opaque	
ZUSA-HT-4812	Santoprene Rubber	8mm	12mm	2mm	10 ft.	55A	None	Natural	Opaque	
ZUSA-HT-4821	Santoprene Rubber	8mm	12mm	2mm	5 ft.	55A	None	Natural	Opaque	
ZUSA-HT-4786	Santoprene Rubber	9mm	13mm	2mm	100 ft.	55A	None	Natural	Opaque	
ZUSA-HT-4795	Santoprene Rubber	9mm	13mm	2mm	50 ft.	55A	None	Natural	Opaque	
ZUSA-HT-4804	Santoprene Rubber	9mm	13mm	2mm	25 ft.	55A	None	Natural	Opaque	
ZUSA-HT-4813	Santoprene Rubber	9mm	13mm	2mm	10 ft.	55A	None	Natural	Opaque	
ZUSA-HT-4822	Santoprene Rubber	9mm	13mm	2mm	5 ft.	55A	None	Natural	Opaque	
ZUSA-HT-4787	Santoprene Rubber	10mm	14mm	2mm	100 ft.	55A	None	Natural	Opaque	
ZUSA-HT-4796	Santoprene Rubber	10mm	14mm	2mm	50 ft.	55A	None	Natural	Opaque	
ZUSA-HT-4805	Santoprene Rubber	10mm	14mm	2mm	25 ft.	55A	None	Natural	Opaque	
ZUSA-HT-4814	Santoprene Rubber	10mm	14mm	2mm	10 ft.	55A	None	Natural	Opaque	
ZUSA-HT-4823	Santoprene Rubber	10mm	14mm	2mm	5 ft.	55A	None	Natural	Opaque	
ZUSA-HT-4788	Santoprene Rubber	12mm	16mm	2mm	100 ft.	55A	None	Natural	Opaque	
ZUSA-HT-4797	Santoprene Rubber	12mm	16mm	2mm	50 ft.	55A	None	Natural	Opaque	
ZUSA-HT-4806	Santoprene Rubber	12mm	16mm	2mm	25 ft.	55A	None	Natural	Opaque	
ZUSA-HT-4815	Santoprene Rubber	12mm	16mm	2mm	10 ft.	55A	None	Natural	Opaque	
ZUSA-HT-4824	Santoprene Rubber	12mm	16mm	2mm	5 ft.	55A	None	Natural	Opaque	