

Suspended Pipe Fittings

A10145 Lantern type hanging band



Lantern type hanging band for SGP pipe

Part number A10145 Lantern type hanging band

Units (mm)

Size code	Diameter size (A)	Nominal diameter (B)	Applicable pipe outer diameter	t	C	Tightening bolt Dia. x Length	D	F
0016	15A	1/2	21.7	2.8	25	M 8×25	25	8
0035	20A	3/4	27.2	2.8	25	M 8×25	25	8
0040	25A	1	34.0	2.8	25	M 8×25	25	8
0054	32A	1 1/4	42.7	2.8	25	M 8×25	25	8
0069	40A	1 1/2	48.6	2.8	25	M 8×25	25	8
0073	50A	2	60.5	2.8	25	M 8×25	25	8
0088	65A	2 1/2	76.3	2.8	25	M10×30	25	8
0092	80A	3	89.1	2.8	25	M10×30	25	8
0105	100A	4	114.3	2.8	25	M10×30	25	8
0110	125A	5	139.8	3.2	32	M12×45	36	11
0124	150A	6	165.2	3.2	32	M12×45	36	11

A10146 Lantern type hanging band with lock



Lantern type hanging band for SGP pipe

Part number A10146 Lantern type hanging band with lock

Units (mm)

Size code	Diameter size (A)	Nominal diameter (B)	Applicable pipe outer diameter	t	C	Tightening bolt Dia. x Length	D	H	Hanging bolt diameter
0013	15A	1/2	21.7	2.8	25	M 8×25	25	72	W 3/8
0028	20A	3/4	27.2	2.8	25	M 8×25	25	74	W 3/8
0032	25A	1	34.0	2.8	25	M 8×25	25	78	W 3/8
0047	32A	1 1/4	42.7	2.8	25	M 8×25	25	82	W 3/8
0051	40A	1 1/2	48.6	2.8	25	M 8×25	25	85	W 3/8
0066	50A	2	60.5	2.8	25	M 8×25	25	91	W 3/8
0085	65A	2 1/2	76.3	2.8	25	M10×30	25	98	W 3/8
0090	80A	3	89.1	2.8	25	M10×30	25	104	W 3/8
0102	100A	4	114.3	2.8	25	M10×30	25	117	W 3/8
0117	125A	5	139.8	3.2	32	M12×45	36	144	W 1/2
0121	150A	6	165.2	3.2	32	M12×45	36	157	W 1/2