

Stereo/Metal Microscopes



■ Specification

- Eyepiece : WF10× (field No. V18)
- Object Lens : 4× · 10× · 40×
- Eye Width Range : 48~75mm
- Lighting : 6V 20W Halogen Lamp
- Stage : 150×140mm
- Filter : Blue · Green · Yellow
- Power Supply : AC100V 50/60Hz
- Dimensions : 192×427×413mm
- Weight : 9kg



■ Specification

- Eyepiece : WF-10× (field No. V18)
- Object Lens : 4× · 10× · 40×
- Light Source : 6V 20W Halogen lamp
- Stage Dimensions : 150×140mm
- Focus Control : Uniaxial Coarse Handle
- Filter : Blue, Green, Yellow
- Power Supply : AC110V 50/60Hz 3-pin Plug
- Dimensions : 192×427×413mm
- Weight : 9kg

TRIPLE-LENS METALLURGICAL MICROSCOPE CN

Order No.	Model No.	Total Magnification	JPY	Ref.No
1-3432-01	NJF-120A	40~400×	¥ 198,000	063560

■ Feature

- Suitable for surface observation of metal non-penetrating substance.
- CCD camera · adapter can be attached.



■ Specification

- Dimensions : 219 × 433 × 417mm
- Stage Dimensions : 140 × 160mm
- Power Supply : AC110V 50/60Hz 2-pin Plug
- Light Source : 6V 20W Halogen Lamp
- Eyepiece : Wide Field 10 × 2
- Object Lens : PL5× · PL10× · PL40× · PL60×
- Focus Control : Uniaxial Coarse and Fine Focusing Adjustment
- Weight : 9kg

METALLURGICAL MICROSCOPE CN

Order No.	Model No.	Total Magnification	JPY	Ref.No
1-1928-01	MT-320	40~400×	¥ 198,000	063560

■ Specification

- Eyepiece : WF10× (field number V20)
- Object Lens : 4× · 10× · 20× · 40×
- Eye Width Range : 48~75mm
- Lighting : 6V 20W Halogen Lamp
- Stage : 150×140mm
- Filter : Blue · Green · Yellow
- Power Supply : AC100V 50/60Hz
- Dimensions : 116×191×340mm
- Weight : 9kg

METAL REFLECTING MICROSCOPE CN

Order No.	Model No.	Type	Total Magnification	JPY	Ref.No
1-9214-01	TMR-1	Trinocular	50~600×	¥ 230,000	063560
1-9214-11	C-Mount Adapter		1×	¥ 11,000	063570
1-9214-12	Replacement Lamp 6V20W			¥ 1,500	063570

METAL MICROSCOPE

Order No.	Model No.	Type	JPY	Ref.No
3-6411-01	HRM-330M-B	Dedicated for episcopic illumination	¥ 721,600	063508
3-6411-02	HRM-330T-BD	For episcopic/transmitted illumination	¥ 991,400	063508
3-6411-03	HRM-330T-U3A-PRO		¥ 2,686,600	063508

※ No PC is included.

■ Feature

- Adopts eye-friendly eyepiece and high-resolution aspherical object lenses.
- A wide variety of customizable models from simple and low cost bright field/episcopic illumination-dedicated models to bright field/dark field/differential interference/simple polarization/3D observation/episcopic · transmitted illumination models.

■ Specification

- Total magnification: ×50 ~ ×1000
- Lens tube: Upright trinocular lens tube
- Eyepiece: 10X (field number 25mm)
- Object lens: Plan semi-achromat
- Light: 330M-B / Bright field light projection tube (12V 100W halogen lamp), Others / Universal light projection tube (12V 100W halogen lamp)
- Stage: 4 lower right handle (with plate)
- Power supply: AC100V 50/60Hz
- Dimensions: 247×572×514
- Weight: 19kg
- With 3D profile software & 2M camera (330T-U3A-PRO only)

STANDING TRIPLE-LENS METALLURGICAL MICROSCOPE CN

Order No.	Model No.	Total Magnification	JPY	Ref.No
1-3431-01	NIM-100	40~400×	¥ 298,000	063560



HRM-330T-BD



Software Panasis Image



HRM-330T-U3A-PRO

NEW