

1 Laboratory Equipment

2 Measuring Equipment

3 Laboratory Furniture

4 Life Science and Analysis

5 Bottles and Containers

6 Laboratory Related Tools and Fixtures

7 Cleaning and Sterilization

8 Safety Protection Supplies

9 Clean Environment Equipment

A Clean Room Equipment

B Clean Room Supplies

C Antistatic Equipment

D Antistatic Supplies

E Wafer Carriers and Precision Tools

## Antistatic Brushes

### ANTI-STATIC BRUSHES

Order No.	Model No.	Dimensions (mm)	JPY	Ref.No
1-5274-01	BB-512A	180×12×14	¥ 770	226950
1-5274-02	BB-520A	230×22×22	¥ 1,110	226950

#### ■ Specification

- Material : Grip/Conductive PP (polypropylene), Brush/Nylon



BA-512A

BB-520A

### ANTI-STATIC BRUSHES

JP

Order No.	Type	Specification	Length×Bristle Length×Bristle Width (mm)	JPY	Ref.No
9-5656-04	STAC99	Mini Brush Type	86×25× 5	¥ 1,000	226960
9-5656-01	STAC14	Sweep Type	135×40× 15	¥ 3,200	226960
9-5656-02	STAC33	Compact Type	107×23×100	¥ 2,900	226960
9-5656-03	STAC200	Large 200	345×50×200	¥ 12,600	226960

#### ■ Feature

- Since manufactured with gold acrylic fiber with 40 deniers, not to damage plastic or film.
- STAC99 - 33 - 200 can be connected to ground wire to effectively eliminate static elimination and dust removal.

#### ■ Specification

- Bristle Material : Organic Conductive Fiber 100%
- Handle Material : STAC14・STAC200 / Wood, STAC99・STAC33 / Aluminium
- Fiber Dia. : 0.04mm



Large 200

Compact Type

Sweep Type

Mini Brush Type

### ANTI-STATIC BRUSHES

JP

Order No.	Model No.	Length×Dia.×Bristle Length (mm)	JPY	Ref. No
2-8252-01	Large	225×φ25×60	¥ 2,700	226960
2-8252-02	Small (Long Handle)	300×φ15×45	¥ 2,500	226960
2-8252-03	Small (Short Handle)	130×φ15×40	¥ 2,200	226960

#### ■ Feature

- Suitable for corners and narrow spaces.

#### ■ Specification

- Bristle Material : Large / Thunderon® + Mixed Grizzled Goat Hair, Small (Long Handle) - Small (Short Handle) / Thunderon®
- Handle Material : Large - Small (Short Handle) / Wood, Small (Long Handle) / Stainless Steel



Large

Small (long handle)

Small (short handle)

### ANTI-STATIC BRUSHES

JP

Order No.	Model No.	Length×Bristle Length×Brush Part (mm)	JPY	Ref. No
9-4040-01	Rabbit	100× 30	¥ 3,500	226950
9-4040-04	120	240× 30×120	¥ 4,100	226950
9-4040-02	145	290× 30×145	¥ 5,300	226950
9-4040-03	Large	450× 50×300	¥ 16,500	226950

#### ■ Specification

- Fiber Dia. : 0.07mm



Large

145

120

Rabbit

### ANTI-STATIC BRUSHES

Order No.	Model No.	Type	Bristle Length×Bristle Width×Length (mm)	JPY	Ref. No
1-9201-01	STAC140	Plastic	25×140×270	¥ 7,400	226960
1-9201-02	STAC180		50×180×310	¥ 11,000	226960
1-9201-03	STAC141	Plasticwith	30×140×270	¥ 8,600	226960
1-9201-04	STAC181	Ground Cord	50×180×310	¥ 12,900	226960

#### ■ Feature

- Copper plate processing is provided to the handle.
- Resistance of 1MΩ is contained in STAC141・181 for human body protection.

#### ■ Specification

- Bristle Material : STAC140・180 / Organic Conductive Fiber, STAC141・181 / 0.15mm Carbon Fiber
- Handle Material : ABS (acrylonitrile butadiene styrene resin)



STAC180

STAC181