


▶ Diagram




Note: Cover insert is available for socket insert with #16 or #20 contacts only.

▶ Cable Receptacle

CE01-1A22-14PCW-D0(R1)

① ② ③ ④ ⑤ ⑥ ⑦ ⑧

① Connector Style	1A : Cable Receptacle
② Shell Size	18, 20, 22, 24 and 28
③ Insert Arrangement	Refer to page 2.
④ Contact Style	P : Pin Contact S : Socket Contact
⑤ Contact Type	C : Crimp Contact
⑥ Alternate Insert Position	Omit : Standard Position W, X, Y, Z : Refer to page 3.
⑦ Plating /Finish	D : Zinc Plating / Black Trivalent Chromium Treatment
⑧ Contact	0 : Less Contact (Available separately)



Shell Size	Number of Contact	Part Number	A	V	Contact Size	L Min.	
						Pin Insert	Socket Insert
18	5	CE01-1A18-11 □ C-D0(R1)	28.87	1-20UNEF-2A	# 12	46	43.0
	10	CE01-1A18-1 □ C-D0(R1)			# 16	43	38.0
	19	CE01-1A18-19A □ C-D0(R1)			# 20	40	36.5
20	7	CE01-1A20-15 □ C-D0(R1)	33.95	1 1/8-18UNEF-2A	# 12	46	43.0
	17	CE01-1A20-29 □ C-D0(R1)			# 16	43	38.0
	30	CE01-1A20-30A □ C-D0(R1)			# 20	40	36.5
22	4	CE01-1A22-22 □ C-D0(R1)	35.22	1 1/4-18UNEF-2A	# 8	48	48.0
	8	CE01-1A22-23 □ C-D0(R1)			# 12	46	43.0
	19	CE01-1A22-14 □ C-D0(R1)			# 16	43	38.0
24	7	CE01-1A24-10 □ C-D0(R1)	38.39	1 3/8-18UNEF-2A	# 8	48	48.0
	24	CE01-1A24-28 □ C-D0(R1)			# 16	43	38.0
	52	CE01-1A24-52A □ C-D0(R1)			# 20	40	36.5
28	37	CE01-1A28-21 □ C-D0(R1)	44.74	1 5/8-18UNEF-2A	# 16	43	38.0
	73	CE01-1A28-73A □ C-D0(R1)			# 20	40	36.5

© Specifications and/or dimensions in this catalog are subject to change without notice.
Your checking the latest specifications with our drawings would be highly appreciated.