



Bore Diameter:		Outer Diameter:		Width: B		Radius:		Bearing Reference				
d		D				rs(min)		Open	Shield	Seal		
mm	inch	mm	inch	mm	inch	mm	inch			ZZ	2RS	2RU
10	0.3937	26	1.0236	8	0.3150	0.3	0.0118	6000H ^{(1),(2)}	ZZ	2RS	2RU	-
		30	1.1811	9	0.3543	0.6	0.0236	6200H ^{(1),(2)}	ZZ	2RS	2RU	-
		35	1.3780	11	0.4331	0.6	0.0236	6300H ⁽¹⁾	ZZ	2RS	2RU	-
12	0.4724	28	1.1024	8	0.3150	0.3	0.0118	6001H ^{(1),(2)}	ZZ	2RS	2RU	TTS
		32	1.2598	10	0.3937	0.6	0.0236	6201H ⁽¹⁾	ZZ	2RS	2RU	-
		37	1.4567	12	0.4724	1.0	0.0394	6301H	ZZ	2RS	2RU	-
15	0.5906	32	1.2598	9	0.3543	0.3	0.0118	6002H ^{(1),(2)}	ZZ	2RS	2RU	-
		35	1.3780	11	0.4331	0.6	0.0236	6202H ⁽¹⁾	ZZ	2RS	2RU	-
		42	1.6535	13	0.5118	1.0	0.0394	6302H ⁽¹⁾	ZZ	2RS	2RU	-
17	0.6693	35	1.3780	10	0.3937	0.3	0.0118	6003H ^{(1),(2)}	ZZ	2RS	2RU	-
		40	1.5748	12	0.4724	0.6	0.0236	6203H ⁽¹⁾	ZZ	2RS	2RU	-
		47	1.8504	14	0.5512	1.0	0.0394	6303H ⁽¹⁾	ZZ	2RS	2RU	-
20	0.7874	42	1.6535	12	0.4724	0.6	0.0236	6004H ⁽¹⁾	ZZ	2RS	2RU	-
		47	1.8504	14	0.5512	1.0	0.0394	6204H ⁽¹⁾	ZZ	2RS	2RU	-
		52	2.0472	15	0.5906	1.1	0.0433	6304H ⁽¹⁾	ZZ	2RS	2RU	-
25	0.9843	47	1.8504	12	0.4724	0.6	0.0236	6005H ⁽¹⁾	ZZ	2RS	2RU	-
		52	2.0472	15	0.5906	1.0	0.0394	6205H ⁽¹⁾	ZZ	2RS	2RU	-
		62	2.4409	17	0.6693	1.1	0.0433	6305H ⁽¹⁾	ZZ	2RS	2RU	-
30	1.1811	55	2.1654	13	0.5118	1.0	0.0394	6006H ⁽¹⁾	ZZ	2RS	2RU	-
		62	2.4409	16	0.6299	1.0	0.0394	6206H ⁽¹⁾	ZZ	2RS	2RU	-
		72	2.8346	19	0.7480	1.1	0.0433	6306H ⁽¹⁾	ZZ	2RS	2RU	-
35	1.3780	62	2.4409	14	0.5512	1.0	0.0394	6007H ⁽¹⁾	ZZ	2RS	2RU	-
		72	2.8346	17	0.6693	1.1	0.0433	6207H ⁽¹⁾	ZZ	2RS	2RU	-
		80	3.1496	21	0.8268	1.5	0.0591	6307H ⁽¹⁾	ZZ	2RS	2RU	-
40	1.5748	68	2.6772	15	0.5906	1.0	0.0394	6008H ⁽¹⁾	ZZ	2RS	2RU	-
		80	3.1496	18	0.7087	1.1	0.0433	6208H ⁽¹⁾	ZZ	2RS	2RU	-
45	1.7717	75	2.9528	16	0.6299	1.0	0.0394	6009H ⁽¹⁾	ZZ	2RS	2RU	-
		85	3.3465	19	0.7480	1.1	0.0433	6209H ⁽¹⁾	ZZ	2RS	2RU	-
50	1.9685	80	3.1496	16	0.6299	1.0	0.0394	6010H ⁽¹⁾	ZZ	2RS	2RU	-
		90	3.5433	20	0.7874	1.1	0.0433	6210H ⁽¹⁾	ZZ	2RS	2RU	-
55	2.1654	90	3.5433	18	0.7087	1.1	0.0433	6011H ⁽¹⁾	ZZ	2RS	2RU	-
		100	3.9370	21	0.8268	1.5	0.0591	6211H ⁽¹⁾	ZZ	2RS	2RU	-
60	2.3622	95	3.7402	18	0.7087	1.1	0.0433	6012H ⁽¹⁾	ZZ	2RS	2RU	-
		110	4.3307	22	0.8661	1.5	0.0591	6212H ⁽¹⁾	ZZ	2RS	2RU	-

1) Open type bearings have shield/seal grooves.

2) SUJ2 material type (without suffix H) is also available. Load ratings of SUJ2 material types are calculated by Cr/0.85 or Cor/0.80 of stainless material types.

3) Single shield or seal types are also available; suffix Z, RS, RU or TS.