


4RBE ラジアスエンドミル 4枚刃

SINCE 1935
F.K.D.®

4RBE 4-Flute Radius Ball End Mills

材質=HSS-Co(SKH56)
刃数=4枚
リード角=右捩れ30°
刃径公差=0~-0.03
R公差=±0.025



○コーナーにのみRを施し、剛性に優れ安定したR加工を演出。

Better rigidity for radius at just corner of end mill.

●注文例=型番、刃径、R、数量 「4RBE 6x0.5R」

型番	刃径(D)	R	刃長(ℓ)	全長(L)	シャン径(d)
4RBE	6	0.5	16	59	6
4RBE	6	0.75	16	59	6
4RBE	6	1	16	59	6
4RBE	6	1.5	16	59	6
4RBE	6	2	16	59	6
4RBE	8	0.5	20	75	8
4RBE	8	0.75	20	75	8
4RBE	8	1	20	75	8
4RBE	8	1.5	20	75	8
4RBE	8	2	20	75	8
4RBE	8	2.5	20	75	8
4RBE	8	3	20	75	8
4RBE	10	0.5	25	80	10
4RBE	10	0.75	25	80	10
4RBE	10	1	25	80	10
4RBE	10	1.5	25	80	10
4RBE	10	2	25	80	10
4RBE	10	2.5	25	80	10
4RBE	10	3	25	80	10
4RBE	12	0.5	30	90	12
4RBE	12	0.75	30	90	12
4RBE	12	1	30	90	12
4RBE	12	1.5	30	90	12
4RBE	12	2	30	90	12
4RBE	12	2.5	30	90	12
4RBE	12	3	30	90	12
4RBE	12	3.5	30	90	12
4RBE	12	4	30	90	12
4RBE	12	5	30	90	12
4RBE	14	0.5	35	100	12
4RBE	14	0.75	35	100	12
4RBE	14	1	35	100	12
4RBE	14	1.5	35	100	12
4RBE	14	2	35	100	12
4RBE	14	2.5	35	100	12
4RBE	14	3	35	100	12
4RBE	14	4	35	100	12
4RBE	14	5	35	100	12
4RBE	15	0.5	40	105	16
4RBE	15	0.75	40	105	16
4RBE	15	1	40	105	16
4RBE	15	1.5	40	105	16
4RBE	15	2	40	105	16
4RBE	15	2.5	40	105	16
4RBE	15	3	40	105	16
4RBE	15	4	40	105	16

型番	刃径(D)	R	刃長(ℓ)	全長(L)	シャン径(d)
4RBE	15	5	40	105	16
4RBE	16	0.5	40	105	16
4RBE	16	0.75	40	105	16
4RBE	16	1	40	105	16
4RBE	16	1.5	40	105	16
4RBE	16	2	40	105	16
4RBE	16	2.5	40	105	16
4RBE	16	3	40	105	16
4RBE	16	4	40	105	16
4RBE	16	5	40	105	16
4RBE	16	6	40	105	16
4RBE	20	0.5	45	130	20
4RBE	20	0.75	45	130	20
4RBE	20	1	45	130	20
4RBE	20	1.5	45	130	20
4RBE	20	2	45	130	20
4RBE	20	2.5	45	130	20
4RBE	20	3	45	130	20
4RBE	20	4	45	130	20
4RBE	20	5	45	130	20
4RBE	20	6	45	130	20
4RBE	22	0.5	45	135	20
4RBE	22	0.75	45	135	20
4RBE	22	1	45	135	20
4RBE	22	1.5	45	135	20
4RBE	22	2	45	135	20
4RBE	22	2.5	45	135	20
4RBE	22	3	45	135	20
4RBE	22	4	45	135	20
4RBE	22	5	45	135	20
4RBE	22	6	45	135	20
4RBE	25	0.5	50	150	25
4RBE	25	0.75	50	150	25
4RBE	25	1	50	150	25
4RBE	25	1.5	50	150	25
4RBE	25	2	50	150	25
4RBE	25	2.5	50	150	25
4RBE	25	3	50	150	25
4RBE	25	4	50	150	25
4RBE	25	5	50	150	25
4RBE	25	6	50	150	25
4RBE	25	8	50	150	25
4RBE	26	0.5	50	150	25
4RBE	26	0.75	50	150	25
4RBE	26	1	50	150	25
4RBE	26	1.5	50	150	25