



Cable ties polyamide 6.6 standard

T-Series in PA66 natural and black


T-Series cable ties for bundling and securing of cables, pipes and hoses. These cable ties can be used for nearly all kind of applications.

Features and benefits

- Available in a wide range of materials and sizes
- High tensile strength with very low insertion force
- Only high quality plastic is used meeting recycling targets
- Inside serrated cable ties for a strong hold onto bundles
- Ergonomic bent tail offers quick and simple installation
- Easy application either manually or with an application tool



Standard T-Series cable ties – for almost any type of application.



TYPE	Width (W)	Length (L)	Bundle Ø max.	N	Material	Colour	Pack Cont.	Tools	Article-No.
T18S	2.3	83.0	16.0	80	PA66	Natural (NA)	1,000 pcs.	2;5-6;25	111-02809
T18R	2.5	100.0	22.0	80	PA66	Black (BK)	100 pcs.	2;5-6;25	111-01910
	2.5	100.0	22.0	80	PA66	Natural (NA)	100 pcs.	2;5-6;25	111-01919
T18I	2.5	145.0	35.0	80	PA66	Black (BK)	100 pcs.	2;5-6;25	111-02370
	2.5	145.0	35.0	80	PA66	Natural (NA)	100 pcs.	2;5-6;25	111-02319
T18L	2.5	205.0	50.0	80	PA66	Black (BK)	100 pcs.	2;5;25	111-02110
	2.5	205.0	50.0	80	PA66	Natural (NA)	100 pcs.	2;5;25	111-02119
T25L	2.8	240.0	65.0	110	PA66	Black (BK)	100 pcs.	2;5-6	111-02500
	2.8	240.0	65.0	110	PA66	Natural (NA)	100 pcs.	2;5-6	111-02519
T25LL	2.8	330.0	95.0	110	PA66	Natural (NA)	100 pcs.	2;5-6	111-02619
T30R	3.5	150.0	35.0	135	PA66	Black (BK)	100 pcs.	2;5-6;25	111-03210
	3.5	150.0	35.0	135	PA66	Natural (NA)	100 pcs.	2;5-6;25	111-03009
T30L	3.5	198.0	50.0	135	PA66	Natural (NA)	100 pcs.	2;5-6;25	111-03419
	3.5	198.0	50.0	135	PA66	Black (BK)	100 pcs.	2;5-6;25	111-03410
T30LL	3.5	290.0	80.0	135	PA66	Black (BK)	100 pcs.	2;5-6;25	111-03500
	3.5	290.0	80.0	135	PA66	Natural (NA)	100 pcs.	2;5-6;25	111-03529
T40R	4.0	175.0	40.0	180	PA66	Natural (NA)	100 pcs.	2;5-6;8;25	111-01626
T50S	4.6	150.0	35.0	225	PA66	Black (BK)	100 pcs.	2-3;5-6;8;10;25	111-05810
	4.6	150.0	35.0	225	PA66	Natural (NA)	100 pcs.	2-3;5-6;8;10;25	111-05819
T50R	4.6	200.0	50.0	225	PA66	Black (BK)	100 pcs.	2-3;5-6;8;10;25	111-05000
	4.6	200.0	50.0	225	PA66	Natural (NA)	100 pcs.	2-3;5-6;8;10;25	111-05013
T50M	4.6	245.0	65.0	225	PA66	Natural (NA)	100 pcs.	2-3;5-6;8;10;25	111-06201
	4.6	245.0	65.0	225	PA66	Black (BK)	100 pcs.	2-3;5-6;8;10;25	111-06200
T50I	4.6	300.0	85.0	225	PA66	Black (BK)	100 pcs.	2-3;5-6;8;10;25	111-05210
	4.6	300.0	85.0	225	PA66	Natural (NA)	100 pcs.	2-3;5-6;8;10;25	111-05219
T50L	4.6	390.0	110.0	225	PA66	Black (BK)	100 pcs.	2-3;5-6;8;10;25	111-05400
	4.6	390.0	110.0	225	PA66	Natural (NA)	100 pcs.	2-3;5-6;8;10;25	111-05409
T50LL	4.6	445.0	130.0	225	PA66	Black (BK)	500 pcs.	2-3;5-6;8;10;25	111-06002

All dimensions in mm. Subject to technical changes.

Minimum Order Quantity (MOQ) may differ from package content. Other packaging options may also be available.



For product specific approvals and specifications please refer to the Appendix.



Add items to your watchlist!

www.HT.click/9-38

