


























2. Available Items and Sizes, Standard Class 150.

<p>Fig.1</p>  <p>Elbows, plain, equal(L) 3/8" up to 6"</p>	<p>Fig.2</p>  <p>Elbows, banded, equal(BL) 1/8" up to 8" Elbows,banded, reducing (BRL) 1/4"×1/8" up to 6"×5"</p>	<p>Fig.4</p>  <p>Elbows, banded, 45° (BL 45°) 1/8" up to 6"</p>	<p>Fig.6</p>  <p>Street Elbows, banded, equal (SL) 1/8" up to 4" Street Elbows, banded, reducing (RSL) 1/2"×3/8" up to 2"×11/2"</p>	<p>Fig.7</p>  <p>Street Elbows, banded 45° (SL 45°) 1/8" up to 2"</p>
<p>Fig.9</p>  <p>Side Outlet Elbows, plain (SOL) 3/8" up to 2"</p>	<p>Fig.10</p>  <p>Tees, plain, equal (T) 1/8" up to 2"</p>	<p>Fig.11</p>  <p>Tees, banded, equal (BT) 1/8" up to 6" Tees, banded, reducing (BRT) 1/4"×1/4"×1/8" up to 8"×8"×6"</p>	<p>Fig.12</p>  <p>Service Tees, banded, equal(ST) 3/8" up to 3" Service Tees, banded, reducing (RST) 1"×3/4"×1"up to 2"×1-1/2"×2"</p>	<p>Fig.13</p>  <p>Side Outlet Tees, plain (SOT) 1/2" up to 2"</p>
<p>Fig.14</p>  <p>Y Branches, banded, equal, 45° (BY 45) 1/2" up to 2"</p>	<p>Fig.16</p>  <p>Crosses, banded, equal (BCR) 1/8" up to 6" Crosses, banded, reducing(BRCR) 3/4"×3/4"×1/2"×1/2" up to 3"×3"×2"×2"</p>	<p>Fig.18</p>  <p>Caps, banded (BCa) 1/8" up to 6"</p>	<p>Fig.19</p>  <p>Sockets, plain, with ribs (S) 1/8" up to 2"</p>	<p>Fig.19-a</p>  <p>Sockets, plain, without ribs (PS) 1/2" up to 2"</p>
<p>Fig.20</p>  <p>Sockets, banded, with ribs (BS) 1/8" up to 8"</p>	<p>Fig.22</p>  <p>Reducing Sockets, banded, with ribs (BRS) 1/4"×1/8" up to 6"×5"</p>	<p>Fig.22-a</p>  <p>Reducing Sockets, eccentric, banded (BExRS) 3/4"×1/2" up to 5"×4"</p>	<p>Fig.23</p>  <p>Flange Unions, round, with bolts (F) 3/8" up to 8"</p>	<p>Fig.24</p>  <p>Backnuts or Locknuts (LN) 1/8" up to 6"</p>
<p>Fig.25</p>  <p>Extension Pieces, plain (X) 3/8" up to 2"</p>	<p>Fig.26</p>  <p>Hexagon Bushes or Bushings (Bu) 1/4"×1/8" up to 8"×6"</p>	<p>Fig.28</p>  <p>Plugs (P) 1/8" up to 6"</p>	<p>Fig.31</p>  <p>Unions, standard, flat seat, without gasket (U) 1/8" up to 6"</p>	<p>Fig.31-a</p>  <p>Unions, female, conical joint (UC) 1/8" up to 6"</p>