



Shaft dia. 6 – 15mm

Shaft dia. mm	Identification number		Boundary dimensions mm			Combinable bearings				
	Single lip	Double lips	d_1	D	b	TA...Z YT TLA...Z YTL	RNA TR TAF GTR	RNAF	NAX NBX	
6	OS 6102.5	—	6	10	2.5	TLA 69Z	—	—	—	
7	OS 7112.5	—	7	11	2.5	TLA 79Z	—	—	—	
8	OS 8123	—	8	12	3	TLA 810Z	—	—	—	
	OS 8153	—	8	15	3	TA 810Z TA 815Z TA 820Z YT 810	RNA 496 TAF 81512 TAF 81516	RNAF 81510	—	
	—	—	—	—	—	—	—	—	—	
9	OS 9133	—	9	13	3	TLA 910Z TLA 912Z	—	—	—	
	OS 9163	—	9	16	3	TA 912Z TA 916Z YT 912	TAF 91612 TAF 91616	—	—	
10	OS 10143	—	10	14	3	TLA 1010Z TLA 1012Z TLA 1015Z	—	—	—	
	OS 10173	—	10	17	3	TA 1010Z TA 1012Z TA 1015Z TA 1020Z	TAF 101712 TAF 101716	RNAF 101710	—	