


Standard Flange in Stock

FF

Flat Face Flange



BF

Blind Flange




STF

Thread Flange



RF

Socket Welding Flange




BDRF

Blind Flange RF



FFC

Lap Joint Flange



Material	SUS F304																				
Description	Flat face flange			Blind flange			Socket welding flange		Blind flange RF		BDRF	Slip on flange	Thread flange		Water supply line flange			Slip on flange		Blind flange	
Marking	FF			BF			RF		BDRF		FFC	SORF	STF		WF	WBF	WRF	SORF		BDRF	
Specification	JIS B 2220														JIS G 3443-2			JPI-7S-15			
Pressure Size	5K	10K	20K	5K	10K	20K	10K	20K	10K	20K	10K	20K (A type)	5K	10K	F12			150	300	150	300
10 ^A	3/8 ^B	●	●	●	●	●	●	●	●	●	-	-	-	-	-	-	-	-	-	-	-
15	1/2	●	●	●	●	●	●	●	●	●	●	●	●	●	-	-	-	●	●	●	●
20	3/4	●	●	●	●	●	●	●	●	●	●	●	●	●	-	-	-	●	●	●	●
25	1	●	●	●	●	●	●	●	●	●	●	●	●	●	-	-	-	●	●	●	●
32	1 1/4	●	●	●	●	●	●	●	●	●	●	-	●	●	-	-	-	-	-	-	-
40	1 1/2	●	●	●	●	●	●	●	●	●	●	●	●	●	-	-	-	●	●	●	●
50	2	●	●	●	●	●	●	●	●	●	●	●	●	●	-	-	-	●	●	●	●
65	2 1/2	●	●	●	●	●	●	●	●	●	●	●	●	●	-	-	-	●	●	●	●
80	3	●	●	●	●	●	●	●	●	●	●	●	●	●	●	●	●	●	●	●	●
90	3 1/2	●	●	-	●	●	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-
100	4	●	●	●	●	●	●	●	●	●	●	●	●	●	●	●	●	●	●	●	●
125	5	●	●	●	●	●	-	●	●	●	-	●	-	-	-	-	●	●	●	●	-
150	6	●	●	●	●	●	-	●	●	●	-	●	-	-	-	-	●	●	●	●	-
200	8	●	●	●	●	●	-	●	●	●	-	●	-	-	-	-	●	●	●	●	-
250	10	●	●	●	●	●	-	●	●	●	-	-	-	-	-	-	●	●	●	●	-
300	12	●	●	●	●	●	-	●	●	●	-	-	-	-	-	-	●	●	●	●	-
350	14	●	●	-	●	●	-	●	-	-	-	-	-	-	-	-	●	●	-	-	-
400	16	●	●	-	●	●	-	●	-	-	-	-	-	-	-	-	●	●	-	-	-
450	18	●	●	-	●	●	-	-	-	-	-	-	-	-	-	-	●	-	-	-	-
500	20	●	●	-	●	●	-	-	-	-	-	-	-	-	-	-	●	-	-	-	-
550	22	●	●	-	●	●	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-
600	24	●	●	-	●	●	-	-	-	-	-	-	-	-	-	-	●	-	-	-	-