



TYPE	GLOBE					GLOBE			GLOBE			GLOBE			GLOBE		
Ductile Iron																	
FIG	10SP					10SPBF			10SPBOF			10SPD			10SPDBF		
PRESSURE	10K					10K			10K			10K			10K		
END CONNECTION	BS21 (JIS B0203)					JIS B2239			JIS B2239			BS21 (JIS B0203)			JIS B2239		
DIMENSIONS	inch	mm	L	H	D	L	H	D	L	H	D	L	H	D	L	H	D
	3/8	10	64	107	60	108	107	60	-	-	-	-	-	-	-	-	-
	1/2	15	70	125	80	108	125	80	-	-	-	70	125	80	108	125	80
	3/4	20	80	125	80	117	125	80	-	-	-	80	125	80	117	125	80
	1	25	90	145	100	127	145	100	-	-	-	90	146	100	127	145	100
	1 1/4	32	110	162	115	140	162	115	-	-	-	110	162	115	140	162	115
	1 1/2	40	120	180	115	165	180	115	-	-	-	120	180	115	165	180	115
	2	50	140	198	135	203	198	135	203	302	200	140	198	135	203	198	135
	2 1/2	65	-	-	-	-	-	-	216	317	225	-	-	-	-	-	-
	3	80	-	-	-	-	-	-	241	356	250	-	-	-	-	-	-
	4	100	-	-	-	-	-	-	292	377	250	-	-	-	-	-	-
	5	125	-	-	-	-	-	-	356	460	300	-	-	-	-	-	-
	6	150	-	-	-	-	-	-	406	524	350	-	-	-	-	-	-
	8	200	-	-	-	-	-	-	495	585	400	-	-	-	-	-	-
BODY	Ductile Iron					Ductile Iron			Ductile Iron			Ductile Iron			Ductile Iron		
BONNET	Ductile Iron					Ductile Iron			Ductile Iron			Ductile Iron			Ductile Iron		
STEM	Stainless Steel					Stainless Steel			Stainless Steel			Stainless Steel			Stainless Steel		
DISC	Stainless Steel					Stainless Steel			Stainless Steel / Ductile Iron			G/F PTFE			G/F PTFE		
												Soft Seated disc			Soft Seated disc		

TYPE	GLOBE					GLOBE			GLOBE			GLOBE			GLOBE		
Ductile Iron																	
FIG	10SPDBOF					10SD			10SDBF			10SDL			10SDLBF		
PRESSURE	10K					10K			10K			10K			10K		
END CONNECTION	JIS B2239					BS21 (JIS B0203)			JIS B2239			BS21 (JIS B0203)			JIS B2239		
DIMENSIONS	inch	mm	L	H	D	L	H	D	L	H	D	L	H	D	L	H	D
	1/4	8	-	-	-	50	108	60	-	-	-	-	-	-	-	-	-
	3/8	10	-	-	-	55	108	60	85	108	60	55	112	55	85	112	55
	1/2	15	-	-	-	65	123	70	85	123	70	65	122	60	85	122	60
	3/4	20	-	-	-	80	123	80	95	123	80	80	130	70	95	130	70
	1	25	-	-	-	90	144	90	110	144	90	90	149	80	110	149	80
	1 1/4	32	-	-	-	105	159	100	130	159	100	105	169	90	130	169	90
	1 1/2	40	-	-	-	120	178	115	150	178	115	120	187	100	150	187	100
	2	50	203	302	200	140	197	135	180	197	135	140	205	115	180	205	115
	2 1/2	65	216	317	225	180	262	180	210	262	180	-	-	-	-	-	-
	3	80	241	356	250	200	295	225	240	295	225	-	-	-	-	-	-
	4	100	292	377	250	-	-	-	-	-	-	-	-	-	-	-	-
	5	125	356	460	300	-	-	-	-	-	-	-	-	-	-	-	-
	6	150	406	527	350	-	-	-	-	-	-	-	-	-	-	-	-
	8	200	495	600	400	-	-	-	-	-	-	-	-	-	-	-	-
BODY	Ductile Iron					Ductile Iron			Ductile Iron			Ductile Iron			Ductile Iron		
BONNET	Ductile Iron					Ductile Iron			Ductile Iron			Ductile Iron			Ductile Iron		
STEM	Stainless Steel					Stainless Steel			Stainless Steel			Stainless Steel			Stainless Steel		
DISC	G/F PTFE					G/F PTFE			G/F PTFE			G/F PTFE			G/F PTFE		
	Soft Seated disc					Soft Seated disc			Soft Seated disc			Soft Seated disc			Soft Seated disc		

Bronze & Brass
 Cast Iron
 Ductile Iron
 Stainless Steel
 Carbon Steel
 Butterfly Valve
 Ball Valve
 Ball Valve Seal
 Actuated Valve