



TYPE		NEEDLE				NEEDLE			NEEDLE			NEEDLE			NEEDLE		
mm., Series																	
FIG		UN3-AP-				UN3-BP-			UN3-CP-			UN3-DP-			UN3-EP-		
PRESSURE		30K				30K			30K			30K			30K		
END CONNECTION		BS21 (JIS B0203)				BS21 (JIS B0203)			COUPLE LOK			COUPLE LOK			JIS B0203 / COUPLE LOK		
DIMENSIONS	mm	L	H	D	L	H	D	L	H	D	L	H	D	L	H	D	
	6	40	59	40	15	59	40	60.8	59	40	30.4	59	40	55.4	59	40	
	8	40	59	40	15	59	40	60.8	59	40	30.4	59	40	55.4	59	40	
	10	45	64	40	18	64	40	62.4	64	40	—	—	—	56.2	64	40	
	10	—	—	—	—	—	—	—	—	—	—	—	—	56.2	64	40	
	12	55	79	50	—	—	—	70.2	64	40	—	—	—	60.1	64	40	
12	—	—	—	—	—	—	—	—	—	—	—	—	60.1	64	40		
BODY		Stainless Steel				Stainless Steel			Stainless Steel			Stainless Steel			Stainless Steel		
STEM		Stainless Steel				Stainless Steel			Stainless Steel			Stainless Steel			Stainless Steel		
FIG		Rc1/8": UN3-AP-1 Rc1/4": UN3-AP-2 Rc3/8": UN3-AP-3 Rc1/2": UN3-AP-4				Rc1/8": UN3-BP-1 Rc1/4": UN3-BP-2 Rc3/8": UN3-BP-3			6mm : UN3-CP-6 8mm : UN3-CP-8 10mm : UN3-CP-10 12mm : UN3-CP-12			6mm : UN3-DP-6 8mm : UN3-DP-8			6mm x R1/8" : UN3-EP-6-2 8mm x R1/8" : UN3-EP-8-2 10mm x R1/8" : UN3-EP-10-2 10mm x R3/8" : UN3-EP-10-3 12mm x R1/4" : UN3-EP-12-2 12mm x R3/8" : UN3-EP-12-3		

TYPE		NEEDLE				NEEDLE			NEEDLE			NEEDLE		
mm., Series														
FIG		UN3-FP-				UN26-AP-			UN26-CP-			UN26-SP-		
PRESSURE		30K				260K			260K			260K		
END CONNECTION		JIS B0203 / COUPLE LOK				BS21 (JIS B0203)			COUPLE LOK			JIS B2316		
DIMENSIONS	mm	L	H	D	L	H	D	L	H	D	L	H	D	
	6	30.4	59	40	48	69	40	64.8	69	40	60	69	40	
	8	30.4	59	40	48	69	40	64.8	69	40	60	69	40	
	10	31.2	64	40	55	81	70	68.4	83	50	65	81	70	
	12	35.1	64	40	—	—	—	74.7	83	50	—	—	—	
	15	—	—	—	60	86	70	—	—	—	75	86	70	
	20	—	—	—	70	99	85	—	—	—	85	99	85	
25	—	—	—	85	119	85	—	—	—	100	119	85		
BODY		Stainless Steel				Stainless Steel			Stainless Steel			Stainless Steel		
STEM		Stainless Steel				Stainless Steel			Stainless Steel			Stainless Steel		
FIG		6mm x R1/4" : UN3-FP-6-2 8mm x R1/4" : UN3-FP-8-2 10mm x R1/4" : UN3-FP-10-2 10mm x R3/8" : UN3-FP-10-3 12mm x R1/4" : UN3-FP-12-2 12mm x R3/8" : UN3-FP-12-3				Rc1/8" : UN26-AP-1 Rc1/4" : UN26-AP-2 Rc3/8" : UN26-AP-3 Rc1/2" : UN26-AP-4 Rc3/4" : UN26-AP-6 Rc1" : UN26-AP-8			6mm : UN26-CP-6 8mm : UN26-CP-8 10mm : UN26-CP-10 12mm : UN26-CP-12			1/8" : UN26-SP-1 1/4" : UN26-SP-2 3/8" : UN26-SP-3 1/2" : UN26-SP-4 3/4" : UN26-SP-6 1" : UN26-SP-8		

TYPE		NEEDLE				NEEDLE			NEEDLE			NEEDLE			NEEDLE		
Inch Series																	
FIG		UN3-CP-				UN3-DP-			UN3-EP-			UN3-FP-			UN26-CP-		
PRESSURE		30K				30K			30K			30K			260K		
END CONNECTION		COUPLE LOK				COUPLE LOK			JIS B0203 / COUPLE LOK			JIS B0203 / COUPLE LOK			COUPLE LOK		
DIMENSIONS	inch	mm	L	H	D	L	H	D	L	H	D	L	H	D	L	H	D
	1/4	8	60.8	59	40	30.4	59	40	55.4	59	40	30.4	59	40	64.8	69	40
	3/8	10	62.4	64	40	—	—	—	56.2	64	40	31.2	64	40	68.4	83	50
	1/2	15	70.2	64	40	—	—	—	60.1	64	40	35.1	64	40	74.7	83	50
BODY		Stainless Steel				Stainless Steel			Stainless Steel			Stainless Steel			Stainless Steel		
STEM		Stainless Steel				Stainless Steel			Stainless Steel			Stainless Steel			Stainless Steel		
FIG		1/4": UN3-CP-02 3/8": UN3-CP-03 1/2": UN3-CP-04				1/4": UN3-DP-02			1/4": UN3-EP-02-2 3/8": UN3-EP-03-2 3/8": UN3-EP-03-3 1/2" x R1/4" : UN3-EP-04-2 1/2" x R3/8" : UN3-EP-04-3			1/4" x R1/4" : UN3-FP-02-2 3/8" x R1/4" : UN3-FP-03-2 3/8" x R3/8" : UN3-FP-03-3 1/2" x R1/4" : UN3-FP-04-2 1/2" x R3/8" : UN3-FP-04-3			1/4": UN26-CP-02 3/8": UN26-CP-03 1/2": UN26-CP-04		