



TYPE	BUTTERFLY					BUTTERFLY			BUTTERFLY			BUTTERFLY			BUTTERFLY		
Butterfly Valve																	
FIG	10UB					GL-10UB			GL-150UB			10NFJNE			G-10NFJNE		
PRESSURE	10K					10K			Class 150			10K			10K		
END CONNECTION	Wafer Type (JIS 10K)					Wafer Type (JIS 10K)			Wafer Type (ASME B16.5 CL150)			Wafer Type (JIS 5K,10K)			Wafer Type (JIS 5K,10K)		
DIMENSIONS	inch	mm	L	H	D	L	H	B	L	H	B	L	H	D	L	H	B
	1½	40	33	183	230	33	202	150	33	202	150	—	—	—	—	—	—
	2	50	43	176	230	43	192	150	43	192	150	43	176	180	43	179	122
	2½	65	46	186	230	46	202	150	46	202	150	46	184	180	46	187	122
	3	80	46	207	280	46	226	195	46	226	195	46	194	180	46	213	135
	4	100	52	221	280	52	240	195	52	240	195	52	204	180	52	223	135
	5	125	56	241	350	56	261	204	56	261	204	56	249	230	56	258	150
	6	150	56	263	350	56	283	204	56	283	204	56	261	230	56	270	150
	8	200	—	—	—	71	348	280	71	348	280	—	—	—	60	311	180
	10	250	—	—	—	76	416	310	—	—	—	—	—	—	68	381	250
	12	300	—	—	—	83	443	310	—	—	—	—	—	—	78	406	250
	14	350	—	—	—	92	475	358	—	—	—	—	—	—	—	—	—
	16	400	—	—	—	102	572	360	—	—	—	—	—	—	—	—	—
	18	450	—	—	—	114	607	360	—	—	—	—	—	—	—	—	—
20	500	—	—	—	127	623	360	—	—	—	—	—	—	—	—	—	
24	600	—	—	—	154	757	371	—	—	—	—	—	—	—	—	—	
BODY	Stainless Steel					Stainless Steel			Stainless Steel			Ductile Iron			Ductile Iron		
STEM	Stainless Steel					Stainless Steel			Stainless Steel			Stainless Steel			Stainless Steel		
DISC	Stainless Steel					Stainless Steel			Stainless Steel			Ductile Iron+Nylon11			Ductile Iron+Nylon11		
SEAT	PTFE					PTFE			PTFE			EPDM			EPDM		
												Nylon Coated disc			Nylon Coated disc		

TYPE	BUTTERFLY					BUTTERFLY			DAMPER			DAMPER			DAMPER		
Butterfly Valve																	
FIG	10NFJNW					G-10NFJNW			10D			GL-10D			GL-10A		
PRESSURE	10K					10K			10K			10K			10K		
END CONNECTION	Wafer Type (JIS 5K,10K)					Wafer Type (JIS 5K,10K)			Wafer Type (JIS 5K,10K)			Wafer Type (JIS 5K,10K)			Wafer Type (JIS 5K,10K)		
DIMENSIONS	inch	mm	L	H	D	L	H	B	L	H	D	L	H	B	L	H	B
	2	50	43	176	180	43	179	122	40	183	200	40	198	150	40	198	150
	2½	65	46	184	180	46	187	122	45	191	200	45	206	150	45	206	150
	3	80	46	194	180	46	213	135	50	198	200	50	213	150	50	213	150
	4	100	52	204	180	52	223	135	60	208	200	60	223	150	60	223	150
	5	125	56	249	230	56	258	150	65	237	280	65	249	190	65	249	190
	6	150	56	261	230	56	270	150	70	247	280	70	259	190	70	259	190
	8	200	—	—	—	60	311	180	80	272	280	80	284	190	80	284	190
10	250	—	—	—	68	381	250	90	340	350	90	355	195	90	355	195	
12	300	—	—	—	78	406	250	100	365	350	100	380	195	100	380	195	
BODY	Ductile Iron					Ductile Iron			Cast Iron+HCr			Cast Iron+HCr			Cast Iron+HCr		
STEM	Stainless Steel					Stainless Steel			Stainless Steel			Stainless Steel			Stainless Steel		
DISC	Ductile Iron+Nylon11					Ductile Iron+Nylon11			Stainless Steel			Stainless Steel			Stainless Steel		
SEAT	White-NBR					White-NBR			—			—			—		
	Nylon Coated disc					Nylon Coated disc											