

KSV-2

KSV-2-120°形  先端角度120° $+30$
 -0

品番 Code No.	刃径 D Flute Diameter	刃長 ℓ Flute Length	全長 L Total Length	柄径 d Shank Diameter	先端フラット径 Edge Flat Diameter	備考 Remarks
KSV-212005	0.5	1	40	3	0.06	
KSV-212006	0.6	1.2	40	3	0.06	
KSV-212007	0.7	1.4	40	3	0.06	
KSV-212008	0.8	1.6	40	3	0.06	
KSV-212009	0.9	2	40	3	0.06	
KSV-212010	1	2	45	4	0.1	
KSV-212011	1.1	2.5	45	4	0.1	
KSV-212012	1.2	2.5	45	4	0.1	
KSV-212013	1.3	3	45	4	0.1	
KSV-212014	1.4	3	45	4	0.1	
KSV-212015	1.5	3	45	4	0.1	
KSV-212016	1.6	3.5	45	4	0.1	
KSV-212017	1.7	3.5	45	4	0.1	
KSV-212018	1.8	4	45	4	0.1	
KSV-212019	1.9	4	45	4	0.1	
KSV-212020	2	4	45	4	0.2	
KSV-212021	2.1	4.5	45	4	0.2	
KSV-212022	2.2	4.5	45	4	0.2	
KSV-212023	2.3	5	45	4	0.2	
KSV-212024	2.4	5	45	4	0.2	
KSV-212025	2.5	5	45	4	0.2	
KSV-212026	2.6	6	45	4	0.2	
KSV-212027	2.7	6	45	4	0.2	
KSV-212028	2.8	6	45	4	0.2	
KSV-212029	2.9	6	45	4	0.2	
KSV-212030	3	6	45	4	0.2	
KSV-212035	3.5	7	50	6	0.2	
KSV-212040	4	8	50	6	0.2	
KSV-212045	4.5	9	50	6	0.3	
KSV-212050	5	10	60	6	0.3	
KSV-212055	5.5	11	60	6	0.3	
KSV-212060	6	12	60	6	0.3	

KSV-2-30°形  先端角度30° $+30$
 -0

品番 Code No.	刃径 D Flute Diameter	刃長 ℓ Flute Length	全長 L Total Length	柄径 d Shank Diameter	先端フラット径 Edge Flat Diameter	備考 Remarks
KSV-23005	0.5	1	40	3	0.06	
KSV-23010	1	2	45	4	0.08	
KSV-23015	1.5	3	45	4	0.08	
KSV-23020	2	4	45	4	0.1	
KSV-23025	2.5	5	45	4	0.1	
KSV-23030	3	6	45	4	0.1	
KSV-23040	4	8	60	6	0.15	
KSV-23050	5	10	70	6	0.2	
KSV-23060	6	12	70	6	0.2	

KSV-2-45°形  先端角度45° $+30$
 -0

品番 Code No.	刃径 D Flute Diameter	刃長 ℓ Flute Length	全長 L Total Length	柄径 d Shank Diameter	先端フラット径 Edge Flat Diameter	備考 Remarks
KSV-24505	0.5	1	40	3	0.06	
KSV-24510	1	2	45	4	0.08	
KSV-24515	1.5	3	45	4	0.08	
KSV-24520	2	4	45	4	0.1	
KSV-24525	2.5	5	45	4	0.1	
KSV-24530	3	6	45	4	0.1	
KSV-24540	4	8	60	6	0.15	
KSV-24550	5	10	70	6	0.2	
KSV-24560	6	12	70	6	0.2	

KSV-2-70°形  先端角度70° $+30$
 -0

品番 Code No.	刃径 D Flute Diameter	刃長 ℓ Flute Length	全長 L Total Length	柄径 d Shank Diameter	先端フラット径 Edge Flat Diameter	備考 Remarks
KSV-27005	0.5	1	40	3	0.06	
KSV-27010	1	2	45	4	0.08	
KSV-27015	1.5	3	45	4	0.08	
KSV-27020	2	4	45	4	0.1	
KSV-27025	2.5	5	45	4	0.1	
KSV-27030	3	6	45	4	0.1	
KSV-27040	4	8	50	6	0.15	
KSV-27050	5	10	60	6	0.2	
KSV-27060	6	12	60	6	0.2	

KSV-2-80°形  先端角度80° $+30$
 -0

品番 Code No.	刃径 D Flute Diameter	刃長 ℓ Flute Length	全長 L Total Length	柄径 d Shank Diameter	先端フラット径 Edge Flat Diameter	備考 Remarks
KSV-28005	0.5	1	40	3	0.06	
KSV-28010	1	2	45	4	0.08	
KSV-28015	1.5	3	45	4	0.08	
KSV-28020	2	4	45	4	0.1	
KSV-28025	2.5	5	45	4	0.1	
KSV-28030	3	6	45	4	0.1	
KSV-28040	4	8	50	6	0.15	
KSV-28050	5	10	60	6	0.2	
KSV-28060	6	12	60	6	0.2	