



Wiring Duct

Ro Product in compliance with RoHS Directive

Material ● Rigid vinyl chloride (Self-extinguishing material rated 94V-0)

Color ● Gray

Length ● 2m

Designation Format ● KD-(Type)-(Length)-(Side Holes)
 Example: Type 26, length 2m, and H type side holes
 > KD-26-20-H

Type	23	53	N23	33	24	34
Cross Section						
Length (mm)	2,000	2,000	2,000	2,000	2,000	2,000
Wire Capacity(AWG14)	15	50	20	30	40	55
Quantity (sets)	50	40	50	40	40	40

Type	44	64	74	26	36	46
Cross Section						
Length (mm)	2,000	2,000	2,000	2,000	2,000	2,000
Wire Capacity(AWG14)	60	100	105	60	65	90
Quantity (sets)	40	20	20	40	30	30

Type	56	66	76	86	106	156
Cross Section						
Length (mm)	2,000	2,000	2,000	2,000	2,000	2,000
Wire Capacity(AWG14)	110	130	150	190	240	310
Quantity (sets)	20	20	20	20	10	6

Type	67	87	137	28	38	48
Cross Section						
Length (mm)	2,000	2,000	2,000	2,000	2,000	2,000
Wire Capacity(AWG14)	150	190	340	70	90	120
Quantity (sets)	16	16	6	24	24	18