

**SSH-SD** Made of Steel · Ferrosferric Oxide Film

Unit : mm

Part Number	M (Coarse)		L	D ₁	L ₁	L _b	B	t	Max. Torque* ¹ (N·m)	Mass (g)	Qty per pack
	Nominal of Thread	Pitch									
SSH-M3-SD	M3	0.5	6 8 10 12	5	1.3	1.5	1.5	2	0.7	0.4 - 0.7	10
SSH-M4-SD	M4	0.7	6 8 10 12 16	6	1.5	1.6	2	2.5	1.7	0.7 - 1.5	10
SSH-M5-SD	M5	0.8	6 8 10 12 16 20	8	1.5	2	3	3	6.2	1.2 - 2.9	10
SSH-M6-SD	M6	1	6 8 10 12 16 20 25 30	9	1.5	2.5	3	4	6.3	1.6 - 5.8	10
SSH-M8-SD	M8	1.25	8 10 12 16 20 25 30	11	1.5	3	4	5	14	3.1 - 10	10
SSH-M10-SD	M10	1.5	10 12 16 20 25 30	13.5	1.5	3.5	5	6	27	5.7 - 16	10

*1: The maximum tightening torque of the screw body. With reference to the Precautions for Use, consider the seating surface pressure when deciding on the tightening torque. Values in chart are for reference only. They are not guaranteed values.

- When purchasing less volume than one full bag, a separate handling fee is charged. For details, see the Sold Separately Service.

SSH-SD-EL Made of Steel · Electroless Nickel Plating

Unit : mm

Part Number	M (Coarse)		L	D ₁	L ₁	L _b	B	t	Max. Torque* ¹ (N·m)	Mass (g)	Qty per pack
	Nominal of Thread	Pitch									
SSH-M3-SD-EL	M3	0.5	6 8 10 12	5	1.3	1.5	1.5	2	0.7	0.4 - 0.7	10
SSH-M4-SD-EL	M4	0.7	6 8 10 12 16	6	1.5	1.6	2	2.5	1.7	0.7 - 1.5	10
SSH-M5-SD-EL	M5	0.8	6 8 10 12 16 20	8	1.5	2	3	3	6.2	1.2 - 2.9	10
SSH-M6-SD-EL	M6	1	6 8 10 12 16 20 25 30	9	1.5	2.5	3	4	6.3	1.6 - 5.8	10
SSH-M8-SD-EL	M8	1.25	8 10 12 16 20 25 30	11	1.5	3	4	5	14	3.1 - 10	10
SSH-M10-SD-EL	M10	1.5	10 12 16 20 25 30	13.5	1.5	3.5	5	6	27	5.7 - 16	10

*1: The maximum tightening torque of the screw body. With reference to the Precautions for Use, consider the seating surface pressure when deciding on the tightening torque. Values in chart are for reference only. They are not guaranteed values.

- When purchasing less volume than one full bag, a separate handling fee is charged. For details, see the Sold Separately Service.

SSH-SD Made of Stainless Steel

Unit : mm

Part Number	M (Coarse)		L	D ₁	L ₁	L _b	B	t	Max. Torque* ¹ (N·m)	Mass (g)	Qty per pack
	Nominal of Thread	Pitch									
SSH-M2-SD	M2	0.4	5 6 8	3.2	1.1	1.2	1.3	1.2	0.18	0.087 - 0.15	10
SSH-M2.5-SD	M2.5	0.45	5 6 8	4	1.3	1.4	1.3	1.5	0.36	0.19 - 0.28	10
SSH-M3-SD	M3	0.5	6 8 10 12	5	1.3	1.5	1.5	2	0.6	0.4 - 0.7	10
SSH-M4-SD	M4	0.7	6 8 10 12 16	6	1.5	1.6	2	2.5	1.5	0.7 - 1.5	10
SSH-M5-SD	M5	0.8	6 8 10 12 16 20	8	1.5	2	3	3	3.1	1.2 - 2.9	10
SSH-M6-SD	M6	1	6 8 10 12 16 20 25 30	9	1.5	2.5	3	4	5.3	1.6 - 5.8	10
SSH-M8-SD	M8	1.25	8 10 12 16 20 25 30	11	1.5	3	4	5	12	3.1 - 10	10
SSH-M10-SD	M10	1.5	10 12 16 20 25 30	13.5	1.5	3.5	5	6	25	5.7 - 16	10

*1: The maximum tightening torque of the screw body. With reference to the Precautions for Use, consider the seating surface pressure when deciding on the tightening torque. Values in chart are for reference only. They are not guaranteed values.

- When purchasing less volume than one full bag, a separate handling fee is charged. For details, see the Sold Separately Service.

- Part number specification

SSH-M5-20-SD-EL

