

単位 (Unit) : mm

直径 DC	全長 LF	溝長 ℓ	先端 PL	在庫 Stock
6.7	300	175	1.7	
6.7	350	200		
6.8	150	100		
6.8	150	110		
6.8	200	100		
6.8	200	125		
6.8	200	135		
6.8	250	120		
6.8	250	150		
6.8	300	150		
6.8	300	175		
6.8	350	200		
6.8	400	250		
6.9	150	100		
6.9	150	110		
6.9	200	125		
6.9	200	135		
6.9	250	150		
6.9	300	175		
6.9	350	200		
7.0	150	100		
7.0	150	110		
7.0	200	100		
7.0	200	125		
7.0	200	135		
7.0	250	120		
7.0	250	150		
7.0	300	150		
7.0	300	175		
7.0	350	200		
7.0	400	250		
7.0	500	350		
7.1	150	100		
7.1	150	110		
7.1	200	125		
7.1	200	135		
7.1	250	150		
7.1	300	175		
7.1	350	200		
7.2	150	100		
7.2	150	110		
7.2	200	100		
7.2	200	125		
7.2	200	135		
7.2	250	120		
7.2	250	150		
7.2	300	150		
7.2	300	175		
7.2	350	200		
7.2	400	250		
7.3	150	100		
7.3	150	110		
7.3	200	125		
7.3	200	135		
7.3	250	150		
7.3	300	175		
7.3	350	200		
7.4	150	100		
7.4	150	110		
7.4	200	125		
7.4	200	135		
7.4	250	150		
7.4	300	175		
7.4	350	200		
7.5	150	100		
7.5	150	110		
7.5	200	100		
7.5	200	125		
7.5	200	135		
7.5	250	120		

直径 DC	全長 LF	溝長 ℓ	先端 PL	在庫 Stock
7.5	250	150	2.0	
7.5	300	150		
7.5	300	175		
7.5	350	200		
7.5	400	250		
7.5	500	350		
7.6	150	100		
7.6	150	110		
7.6	200	125		
7.6	200	135		
7.6	250	150		
7.6	300	175		
7.6	350	200		
7.7	150	100		
7.7	150	110		
7.7	200	125		
7.7	200	135		
7.7	250	150		
7.7	300	175		
7.7	350	200		
7.8	150	100		
7.8	150	110		
7.8	200	100		
7.8	200	125		
7.8	200	135		
7.8	250	120		
7.8	250	150		
7.8	300	150		
7.8	300	175		
7.8	350	200		
7.8	400	250		
7.9	150	100		
7.9	150	110		
7.9	200	125		
7.9	200	135		
7.9	250	150		
7.9	300	175		
7.9	350	200		
8.0	150	100		
8.0	150	110		
8.0	200	100		
8.0	200	125		
8.0	200	135		
8.0	250	120		
8.0	250	150		
8.0	300	150		
8.0	300	175		
8.0	350	200		
8.0	400	250		
8.0	500	350		
8.0	600	450		
8.1	150	110		
8.1	200	125		
8.1	200	135		
8.1	250	150		
8.1	300	175		
8.1	350	200		
8.2	150	110		
8.2	200	100		
8.2	200	125		
8.2	200	135		
8.2	250	120		
8.2	250	150		
8.2	300	150		
8.2	300	175		
8.2	350	200		
8.2	400	250		
8.3	150	110		
8.3	200	125		
8.3	200	135		

直径 DC	全長 LF	溝長 ℓ	先端 PL	在庫 Stock
8.3	250	150	2.2	
8.3	300	175		
8.3	350	200		
8.4	150	110		
8.4	200	125		
8.4	200	135		
8.4	250	150		
8.4	300	175		
8.4	350	200		
8.5	150	110		
8.5	200	100		
8.5	200	125		
8.5	200	135		
8.5	250	120		
8.5	250	150		
8.5	300	175		
8.5	350	200		
8.5	400	250		
8.5	500	350		
8.6	150	110		
8.6	200	125		
8.6	200	135		
8.6	250	150		
8.6	300	175		
8.6	350	200		
8.7	150	110		
8.7	200	125		
8.7	200	135		
8.7	250	150		
8.7	300	175		
8.7	350	200		
8.8	150	110		
8.8	200	100		
8.8	200	125		
8.8	200	135		
8.8	250	120		
8.8	250	150		
8.8	300	175		
8.8	350	200		
8.8	400	250		
8.9	150	110		
8.9	200	125		
8.9	200	135		
8.9	250	150		
8.9	300	175		
8.9	350	200		
9.0	150	110		
9.0	200	100		
9.0	200	125		
9.0	200	135		
9.0	250	120		
9.0	250	150		
9.0	300	150		
9.0	300	175		
9.0	350	200		
9.0	400	250		
9.0	500	350		
9.1	150	110		
9.1	200	125		
9.1	200	135		
9.1	250	150		
9.1	300	175		
9.1	350	200		
9.2	150	110		
9.2	200	100		
9.2	200	125		
9.2	250	120		
9.2	250	150		

新商品

超硬ドリル

ハイスドリル

タップ

超硬  
エンドミル

ハイス  
エンドミル

切断工具

バック・  
セット商品  
その他

精密工具

技術資料  
索引