



USE • For general measurement and reference standard in workshop

MATERIAL
• High carbon high chromium steel

FEATURES
• Conforms to JIS (Grade 1) standard

SPECIFICATIONS

Size (mm)		Grade1	
Over	Below	Tolerance (μm)	Dimensional Deviation (μm)
–	10	± 0.20	0.16
10	25	± 0.30	0.16
25	50	± 0.40	0.18
50	75	± 0.50	0.18
75	100	± 0.60	0.20
100	150	± 0.80	0.20
150	200	± 1.00	0.25
200	250	± 1.20	0.25
250	300	± 1.40	0.25
300	400	± 1.80	0.30
400	500	± 2.20	0.35
500	600	± 2.60	0.40

Order No.	Model No.	Size
150810	GB1-05	0.5mm
150820	GB1-10	1.0mm
150822	GB1-1-001	1.001mm
150823	GB1-1-002	1.002mm
150824	GB1-1-003	1.003mm
150825	GB1-1-004	1.004mm
150826	GB1-1-005	1.005mm
150827	GB1-1-006	1.006mm
150828	GB1-1-007	1.007mm
150829	GB1-1-008	1.008mm
150830	GB1-1-009	1.009mm
150831	GB1-101	1.01mm
150832	GB1-102	1.02mm
150833	GB1-103	1.03mm
150834	GB1-104	1.04mm
150835	GB1-105	1.05mm
150836	GB1-106	1.06mm
150837	GB1-107	1.07mm
150838	GB1-108	1.08mm
150839	GB1-109	1.09mm
150840	GB1-110	1.10mm
150841	GB1-111	1.11mm
150842	GB1-112	1.12mm
150843	GB1-113	1.13mm
150844	GB1-114	1.14mm
150845	GB1-115	1.15mm
150846	GB1-116	1.16mm
150847	GB1-117	1.17mm
150848	GB1-118	1.18mm
150849	GB1-119	1.19mm
150850	GB1-120	1.20mm
150851	GB1-121	1.21mm
150852	GB1-122	1.22mm
150853	GB1-123	1.23mm
150854	GB1-124	1.24mm
150855	GB1-125	1.25mm
150856	GB1-126	1.26mm
150857	GB1-127	1.27mm
150858	GB1-128	1.28mm
150859	GB1-129	1.29mm
150860	GB1-130	1.30mm
150861	GB1-131	1.31mm

Order No.	Model No.	Size
150862	GB1-132	1.32mm
150863	GB1-133	1.33mm
150864	GB1-134	1.34mm
150865	GB1-135	1.35mm
150866	GB1-136	1.36mm
150867	GB1-137	1.37mm
150868	GB1-138	1.38mm
150869	GB1-139	1.39mm
150870	GB1-140	1.40mm
150871	GB1-141	1.41mm
150872	GB1-142	1.42mm
150873	GB1-143	1.43mm
150874	GB1-144	1.44mm
150875	GB1-145	1.45mm
150876	GB1-146	1.46mm
150877	GB1-147	1.47mm
150878	GB1-148	1.48mm
150879	GB1-149	1.49mm
150880	GB1-150	1.50mm
150885	GB1-200	2.00mm
150886	GB1-250	2.50mm
150887	GB1-300	3.00mm
150888	GB1-350	3.50mm
150889	GB1-400	4.00mm
150890	GB1-450	4.50mm
150891	GB1-500	5.00mm
150893	GB1-550	5.50mm
150894	GB1-600	6.00mm
150895	GB1-650	6.50mm
150896	GB1-700	7.00mm
150897	GB1-750	7.50mm
150899	GB1-800	8.00mm
150900	GB1-850	8.50mm
150901	GB1-900	9.00mm
150902	GB1-950	9.50mm
150903	GB1-1000	10.00mm
150905	GB1-1050	10.50mm
150906	GB1-1100	11.00mm
150907	GB1-1150	11.50mm
150908	GB1-1200	12.00mm
150909	GB1-1250	12.50mm
150911	GB1-1300	13.00mm

Order No.	Model No.	Size
150912	GB1-1350	13.50mm
150913	GB1-1400	14.00mm
150914	GB1-1450	14.50mm
150915	GB1-1500	15.00mm
150916	GB1-1550	15.50mm
150917	GB1-1660	16.00mm
150918	GB1-1650	16.50mm
150919	GB1-1700	17.00mm
150920	GB1-1750	17.50mm
150921	GB1-1800	18.00mm
150922	GB1-1850	18.50mm
150923	GB1-1900	19.00mm
150924	GB1-1950	19.50mm
150925	GB1-2000	20.00mm
150927	GB1-2050	20.50mm
150928	GB1-2100	21.00mm
150929	GB1-2150	21.50mm
150930	GB1-2200	22.00mm
150931	GB1-2250	22.50mm
150933	GB1-2300	23.00mm
150934	GB1-2350	23.50mm
150935	GB1-2400	24.00mm
150936	GB1-2450	24.50mm
150937	GB1-2500	25.00mm
150939	GB1-3000	30.00mm
150940	GB1-4000	40.00mm
150941	GB1-5000	50.00mm
150942	GB1-6000	60.00mm
150944	GB1-7000	70.00mm
150945	GB1-7500	75.00mm
150946	GB1-8000	80.00mm
150947	GB1-9000	90.00mm
150948	GB1-10000	100.00mm
150949	GB1-12500	125mm
150950	GB1-15000	150mm
150794	GB1-17500	175mm
150795	GB1-20000	200mm
150796	GB1-25000	250mm
150797	GB1-30000	300mm
150798	GB1-40000	400mm
150799	GB1-50000	500mm
150800	GB1-60000	600mm

BLOCK GAUGES

PIN GAUGES

PIN VISE

PIN GAUGE ACCESSORIES

GAUGES

THREAD GAUGES

PLUG GAUGES

RING GAUGES

THICKNESS GAUGES

TAPER GAUGES

WELDING GAUGES

OTHER GAUGES