

【 Power supply side 】 < Socket (female) contact used >

NWPC-14 ■ -P □

S Type

↕

Coupled

↕

【 Power receiving side 】 < Pin (male) contact used >

NWPC-14 ■ -R

Plug cap : NWPC-14-PCa

NWPC-14 ■ -Ad □

For the plug and adapter , be sure to select □ (cable packing symbol).

Table □

In order to secure the intended waterproof function, a cable to be used for the plug/adapter should have an appropriate specification and structure.

Shell size	Symbol	Outer diameter of cable used
14	5	φ 5.0 to φ 5.9
	6	φ 6.0 to φ 6.9
	7	φ 7.0 to φ 8.0

Accessory

Receptacle cap : NWPC-14-RCa

Adapter cap : NWPC-14-AdCa

■ indicates the number of contacts. The conductor cross sectional area is less than the following value.

Shell size	Number of Contacts	1	2
14	Contact arrangement <When viewed from the pin (male) contact coupling side>		
	Safety standard	—	
	Rating	125V 5A	
	Limit operating voltage (Note-1)	200V	
	Withstand voltage (V r.m.s.)	1,000	
	Wire size (mm²)	0.75	

Note-1 : For the limit operating voltage, see p.131.