

Limiting speed min <sup>-1</sup>	Roller Follower number		Mass kg (approx.)	OD <sup>1)</sup> mm <i>D</i> 0 -0.05
	Spherical outer ring	Cylindrical outer ring		
10 000	<b>RNA22/6LL/3AS</b>	<b>RNA22/6XLL/3AS</b>	0.018	<b>19</b>
10 000	<b>RNA22/8LL/3AS</b>	<b>RNA22/8XLL/3AS</b>	0.027	<b>24</b>
10 000	<b>RNA2200LL/3AS</b>	<b>RNA2200XLL/3AS</b>	0.052	<b>30</b>
9 500	<b>RNA2201LL/3AS</b>	<b>RNA2201XLL/3AS</b>	0.057	<b>32</b>
7 500	<b>RNA2202LL/3AS</b>	<b>RNA2202XLL/3AS</b>	0.060	<b>35</b>
7 000	<b>RNA2203LL/3AS</b>	<b>RNA2203XLL/3AS</b>	0.094	<b>40</b>
6 000	<b>RNA2204LL/3AS</b>	<b>RNA2204XLL/3AS</b>	0.152	<b>47</b>
5 000	<b>RNA2205LL/3AS</b>	<b>RNA2205XLL/3AS</b>	0.179	<b>52</b>
4 300	<b>RNA2206LL/3AS</b>	<b>RNA2206XLL/3AS</b>	0.284	<b>62</b>
3 600	<b>RNA2207LL/3AS</b>	<b>RNA2207XLL/3AS</b>	0.432	<b>72</b>
3 100	<b>RNA2208LL/3AS</b>	<b>RNA2208XLL/3AS</b>	0.530	<b>80</b>
2 900	<b>RNA2209LL/3AS</b>	<b>RNA2209XLL/3AS</b>	0.545	<b>85</b>
2 600	<b>RNA2210LL/3AS</b>	<b>RNA2210XLL/3AS</b>	0.563	<b>90</b>