

Limiting speed min <sup>-1</sup>	Roller Follower number		Mass kg (approx.)	OD <sup>1)</sup> mm <i>D</i> 0 -0.05
	Spherical outer ring	Cylindrical outer ring		
5 500	<b>NUTR202/3AS</b>	<b>NUTR202X/3AS</b>	0.100	<b>35</b>
4 700	<b>NUTR203/3AS</b>	<b>NUTR203X/3AS</b>	0.147	<b>40</b>
5 500	<b>NUTR302/3AS</b>	<b>NUTR302X/3AS</b>	0.160	<b>42</b>
4 700	<b>NUTR303/3AS</b>	<b>NUTR303X/3AS</b>	0.222	<b>47</b>
4 000	<b>NUTR204/3AS</b>	<b>NUTR204X/3AS</b>	0.245	
4 000	<b>NUTR304/3AS</b>	<b>NUTR304X/3AS</b>	0.321	<b>52</b>
3 300	<b>NUTR205/3AS</b>	<b>NUTR205X/3AS</b>	0.281	
3 300	<b>NUTR305/3AS</b>	<b>NUTR305X/3AS</b>	0.450	<b>62</b>
2 900	<b>NUTR206/3AS</b>	<b>NUTR206X/3AS</b>	0.466	
2 900	<b>NUTR306/3AS</b>	<b>NUTR306X/3AS</b>	0.697	<b>72</b>
2 400	<b>NUTR207/3AS</b>	<b>NUTR207X/3AS</b>	0.630	
2 400	<b>NUTR307/3AS</b>	<b>NUTR307X/3AS</b>	0.840	<b>80</b>
2 100	<b>NUTR208/3AS</b>	<b>NUTR208X/3AS</b>	0.817	
1 900	<b>NUTR209/3AS</b>	<b>NUTR209X/3AS</b>	0.883	<b>85</b>
2 100	<b>NUTR308/3AS</b>	<b>NUTR308X/3AS</b>	1.13	<b>90</b>
1 800	<b>NUTR210/3AS</b>	<b>NUTR210X/3AS</b>	0.950	
1 900	<b>NUTR309/3AS</b>	<b>NUTR309X/3AS</b>	1.40	<b>100</b>
1 800	<b>NUTR310/3AS</b>	<b>NUTR310X/3AS</b>	1.69	<b>110</b>