

JB-W Female threaded with 2-row terminal blocks

RoHS2

Protection Color

IP67 Black Light gray Beige

Rated voltage Rated current Oilproof Weatherproof

300V 15A OIL Weather E

Number of poles

5P 7P 11P

■ Model designation

JB-WG3□□□□

- Nil . . . Black
 - C1 . . . Light gray
 - BJ . . . Beige
 - Nil . . . Oilproof
 - E . . . Weatherproof
- Number of poles

※JB-WG305/307 are designed for both waterproof and weatherproof use.



Model			Rating	Applicable crimp terminal (mm)	Working temperature	Cable cross section	Number of poles	Terminal screw	Weight	Q'ty per package
Black	Light gray	Beige								
JB-WG305	JB-WG305C1	JB-WG305BJ	AC/DC 300V 15A		-25 to +80°C	Max. 1.25mm ²	5P	M3×8 fall prevention terminal screw	98g	1 pc.
JB-WG307	JB-WG307C1	JB-WG307BJ					7P		124g	
JB-WG311/311E	JB-WG311C1	JB-WG311BJ/311EBJ					11P		208g	

JB-W Simple connection type

RoHS2

Protection Color

IP67 Black Light gray

Rated voltage Rated current Oilproof Weatherproof Number of poles

600V 20A OIL Weather E 4P

■ Model designation

JB-W44□□

- Nil . . . Black
- C1 . . . Light gray
- Nil . . . Oilproof
- E . . . Weatherproof



100g

Model		Rating	Applicable crimp terminal (mm)	Working temperature	Cable cross section	Number of poles	Weight	Q'ty per package
Black	Light gray							
JB-W44/44E	JB-W44C1	AC/DC 600V 20A	M3.5 or M4 (round terminal) Max. 8.5	-25 to +80°C	Max. 2.0mm ²	4P	95g	1 pc.

JB-W for Power supply with 2 row female thread terminal blocks

RoHS2

Protection Color

IP67 Black Light gray Beige

Rated voltage Rated current Oilproof Weatherproof Number of poles

600V 20A OIL Weather E 6P

■ Model designation

JB-WP□□6□□

- Nil . . . Black
 - C1 . . . Light gray
 - BJ . . . Beige
 - Nil . . . Oilproof
 - E . . . Weatherproof
- Number of poles
- Female thread size



Model			Rating	Applicable crimp terminal (mm)	Working temp.	Cable cross section	Number of poles	Terminal screw	Weight	Q'ty per package
Black	Light gray	Beige								
JB-WP166	JB-WP166C1	JB-WP166BJ	AC/DC 600V 20A		-25 to +80°C	Max. 2.0mm ²	6P	M3.5 × 10 fall prevention terminal screw	122g	1 pc.
JB-WP226	JB-WP226C1	JB-WP226BJ							151g	

JB-W Female threaded with spring terminal block

RoHS2

Protection Color

IP67 Black Light gray Beige

Rated voltage Rated current Oilproof Weatherproof Number of poles

600V 20A OIL Weather E 6P

■ Model designation

JB-WR□□6□□

- Nil . . . Black
 - C1 . . . Light gray
 - BJ . . . Beige
 - Nil . . . Oilproof
 - E . . . Weatherproof
- Number of poles
- Female thread size



Model			Rating	Working temp.	Number of poles	Weight	Q'ty per package
Black	Light gray	Beige					
JB-WR226	JB-WR226C1	JB-WR226BJ	AC/DC 600V 20A	-25 to +80°C	6P, Model: ST2.5 by Phoenix Contact	173g	1 pc.

JB-W Female threaded blank type

RoHS2

Protection Color

IP67 Black Light gray Beige

Oilproof Weatherproof

OIL Weather E

■ Model designation

JB-WB2209□□

- Nil . . . Black
 - C1 . . . Light gray
 - BJ . . . Beige
 - Nil . . . Oilproof
 - E . . . Weatherproof
- Female thread size



Model			Working temperature	Weight	Q'ty per package
Black	Light gray	Beige			
JB-WB2209	JB-WB2209C1	JB-WB2209BJ	-25 to +80°C	127g	1 pc.