

PB 211

Key L-wrenches, long

- for hexagon socket screws
- precisely chamfered edges, ensures easy insertion into screws
- from size 1.27 mm chrome-plated
- special alloy based on spring steel, exceptional elasticity coupled with high grade hardening
- laser-marked serial number, lifetime guarantee

Llave acodada larga

- para tornillos con hexágono interior
- bordes quebrados precisos, inserción segura en los tornillos
- cromada a partir de tamaño 1,27 mm
- aleación especial de acero para resortes, elasticidad extraordinaria y gran dureza
- rotulación láser con n.º de serie, garantía de por vida



PB 211.0,71	0.71	1.4	-	7	50	0.3	10	7 610733 015818
PB 211.0,89	0.89	2	-	10	60	0.4	10	7 610733 015825
PB 211.1,27	1.27	2.5	1.4	12	70	1	10	7 610733 015832
PB 211.1,5	1.5	3	1.6-2	14	80	2	10	7 610733 015849
PB 211.2	2	4	2.5	16	90	3	10	7 610733 012855
PB 211.2,5	2.5	5	3	18	110	5	10	7 610733 012862
PB 211.3	3	6	4	20	125	9	10	7 610733 012879
PB 211.4	4	8	5	22	150	18	10	7 610733 012886
PB 211.5	5	10	6	25	165	32	10	7 610733 012893
PB 211.6	6	12-14	8	28	185	51	10	7 610733 012909
PB 211.7	7	-	-	30	192	72	10	7 610733 044498
PB 211.8	8	16	10	32	200	99	10	7 610733 012916
PB 211.10	10	18-20	12	36	220	171	10	7 610733 012923
PB 211.12	12	22-24	14	40	240	271	10	7 610733 044665
PB 211.14	14	-	16-18	45	265	408	10	7 610733 044672
PB 211.17	17	-	20-22	50	290	668	10	7 610733 044689
PB 211.19	19	-	24-27	56	320	929	10	7 610733 044696
PB 211.22	22	-	30	63	350	1357	5	7 610733 044702