

PB 212 LR

Key L-wrenches, long, with ball point and retainer ring

- for hexagon socket screws
- spring ring in ball point holds screws securely on tool
- perfectly shaped ball point, allows screws to be turned at an angle of up to 30°
- special alloy based on spring steel, exceptional elasticity coupled with high grade hardening
- laser-marked serial number, lifetime guarantee

Llave acodada larga, con cabeza esférica y anillo de retención

- para tornillos con hexágono interior
- arandela elástica en la cabeza esférica, para sujetar los tornillos a la herramienta con seguridad
- cabeza esférica de forma perfecta, que permite girar tornillos con un ángulo de hasta 30°
- aleación especial de acero para resortes, elasticidad extraordinaria y gran dureza
- rotulación láser con n.º de serie, garantía de por vida



PB 212.LR 2,5	2.5	5	3	18	110	5	10	7 610733 015009
PB 212.LR 3	3	6	4	20	125	9	10	7 610733 015016
PB 212.LR 4	4	8	5	22	150	18	10	7 610733 015023
PB 212.LR 5	5	10	6	25	165	31	10	7 610733 015030
PB 212.LR 6	6	12-14	8	28	185	50	10	7 610733 015047
PB 212.LR 8	8	16	10	32	200	98	10	7 610733 015054
PB 212.LR 10	10	18-20	12	36	220	168	10	7 610733 015061

PB 212 LR H

Key L-wrenches, long, with ball point and holding ring, set in a practical plastic holder

- for hexagon socket screws
- spring ring in ball point holds screws securely on tool
- perfectly shaped ball point, allows screws to be turned at an angle of up to 30°
- special alloy based on spring steel, exceptional elasticity coupled with high grade hardening
- laser-marked serial number, lifetime guarantee

Llaves acodadas largas, con cabeza esférica y anillo de retención; juego en práctico soporte de plástico

- para tornillos con hexágono interior
- arandela elástica en la cabeza esférica, para sujetar los tornillos a la herramienta con seguridad
- cabeza esférica de forma perfecta, que permite girar tornillos con un ángulo de hasta 30°
- aleación especial de acero para resortes, elasticidad extraordinaria y gran dureza
- rotulación láser con n.º de serie, garantía de por vida



PB 212.LR H-10	1.5, 2, 2.5, 3, 4, 5, 6, 8, 10	404	10	7 610733 014125

**In blister packs
En embalaje blister**



PB 212.LR H-10 CN	1.5, 2, 2.5, 3, 4, 5, 6, 8, 10	436	10	7 610733 236527