

PB 212ZL

Key L-wrenches, long, with ball point

- for hexagon socket screws (inch)
- perfectly shaped ball point, allows screws to be turned at an angle of up to 30°
- special alloy based on spring steel, exceptional elasticity coupled with high grade hardening
- laser-marked serial number, lifetime guarantee

Llave acodada larga, con cabeza esférica

- para tornillos con hexágono interior (pulgadas)
- cabeza esférica de forma perfecta, que permite girar tornillos con un ángulo de hasta 30°
- aleación especial de acero para resortes, elasticidad extraordinaria y gran dureza
- rotulación láser con n.º de serie, garantía de por vida



PB 212Z.L 1/20	1/20"	12	70	1	10	7 610733 008056
PB 212Z.L 1/16	1/16"	15	80	2	10	7 610733 008070
PB 212Z.L 5/64	5/64"	16	90	3	10	7 610733 040292
PB 212Z.L 3/32	3/32"	17	97	4	10	7 610733 008216
PB 212Z.L 7/64	7/64"	18	105	7	10	7 610733 040308
PB 212Z.L 1/8	1/8"	19	115	8	10	7 610733 008148
PB 212Z.L 9/64	9/64"	20	125	13	10	7 610733 040315
PB 212Z.L 5/32	5/32"	22	132	16	10	7 610733 008155
PB 212Z.L 3/16	3/16"	24	145	25	10	7 610733 008162
PB 212Z.L 7/32	7/32"	26	162	38	10	7 610733 008179
PB 212Z.L 1/4	1/4"	29	180	55	10	7 610733 008186
PB 212Z.L 5/16	5/16"	32	200	95	10	7 610733 008193
PB 212Z.L 3/8	3/8"	35	220	150	10	7 610733 040322

PB 212Z H

Key L-wrenches with ball point, set in a practical plastic holder

- for hexagon socket screws (inch)
- perfectly shaped ball point, allows screws to be turned at an angle of up to 30°
- special alloy based on spring steel, exceptional elasticity coupled with high grade hardening
- laser-marked serial number, lifetime guarantee

Llaves acodadas con cabeza esférica; juego en práctico soporte de plástico

- para tornillos con hexágono interior (pulgadas)
- cabeza esférica de forma perfecta, que permite girar tornillos con un ángulo de hasta 30°
- aleación especial de acero para resortes, elasticidad extraordinaria y gran dureza
- rotulación láser con n.º de serie, garantía de por vida



PB 212Z.H	3/32, 1/8, 5/32, 3/16, 7/32, 1/4, 5/16	151	10	7 610733 008223
PB 212Z.H-12	1/20, 1/16, 5/64, 3/32, 7/64, 1/8, 9/64, 5/32, 3/16, 7/32, 1/4, 5/16	195	10	7 610733 007325

**In blister packs
En embalaje blister**



PB 212Z.H CN	3/32, 1/8, 5/32, 3/16, 7/32, 1/4, 5/16	196	10	7 610733 235544