

RoHS compliant



Model code	Tube O.D. (ømm)	Tube I.D. (ømm)	Cover O.D. (ømm)	Cover thickness (mm)	Tube length (m)	Min. Bending Radius (mm)	Min. Installation Radius (mm)	Weight (g/m)
FB 0425-□	4	2.5	6	1	20 · 100	14	21	33.5
FB 0640-□	6	4	8	1	20 · 100	18	27	49
FB 0860-□	8	6	10	1	20 · 100	28	42	65
FB 1075-□	10	7.5	12	1	20 · 100	36	54	88
FB 1290-20	12	9	14	1	20	40	60	113

※ □ in model code : Replace with Tube length

FITTING
CONTROLLER
VALVE
TUBE