



The products listed in this page are ECO-friendly products.
 * Please refer to page 4 for the details of ECO-friendly products.

PG Unequal Union Straight	Model type		Model type		PM Bulkhead Union	Model type		Model type	
	Standard pkg	Clean-room pkg	Standard pkg	Clean-room pkg		Standard pkg	Clean-room pkg	Standard pkg	Clean-room pkg
	PGøD1-øD2 [4]		PGøD1-øD2 [4] C			PMøD [4]		PMøD [4] C	
	PG6-4 [4]	PG ³ / ₁₆ - ⁵ / ₃₂ [4]	PG6-4 [4] C	PG ³ / ₁₆ - ⁵ / ₃₂ [4] C		PM4 [4]	PM ⁵ / ₃₂ U	PM4 [4] C	PM ⁵ / ₃₂ UC
	PG8-4 [4]	PG ¹ / ₄ - ³ / ₁₆ [4]	PG8-4 [4] C	PG ¹ / ₄ - ³ / ₁₆ [4] C		PM6 [4]	PM ³ / ₁₆ U	PM6 [4] C	PM ³ / ₁₆ UC
	PG8-6 [4]	PG ¹ / ₄ - ⁵ / ₃₂ [4]	PG8-6 [4] C	PG ¹ / ₄ - ⁵ / ₃₂ [4] C		PM8 [4]	PM ¹ / ₄ U	PM8 [4] C	PM ¹ / ₄ UC
	PG10-6 [4]	PG ¹ / ₄ - ¹ / ₂ [4]	PG10-6 [4] C	PG ¹ / ₄ - ¹ / ₂ [4] C		PM10 [4]	PM ⁵ / ₁₆ U	PM10 [4] C	PM ⁵ / ₁₆ UC
	PG10-8 [4]	PG ⁵ / ₁₆ - ³ / ₁₆ [4]	PG10-8 [4] C	PG ⁵ / ₁₆ - ³ / ₁₆ [4] C		PM12 [4]	PM ³ / ₈ U	PM12 [4] C	PM ³ / ₈ UC
	PG12-8 [4]	PG ⁵ / ₁₆ - ¹ / ₄ [4]	PG12-8 [4] C	PG ⁵ / ₁₆ - ¹ / ₄ [4] C		PM16 [4]	PM ¹ / ₂ U	PM16 [4] C	PM ¹ / ₂ UC
	PG12-10 [4]	PG ³ / ₈ - ¹ / ₄ [4]	PG12-10 [4] C	PG ³ / ₈ - ¹ / ₄ [4] C		PM ⁵ / ₃₂ [4]		PM ⁵ / ₃₂ [4] C	
	PG12- ³ / ₈ [4]	PG ³ / ₈ - ³ / ₁₆ [4]	PG12- ³ / ₈ [4] C	PG ³ / ₈ - ³ / ₁₆ [4] C		PM ³ / ₁₆ [4]		PM ³ / ₁₆ [4] C	
	PG16-10 [4]	PG ¹ / ₂ - ¹ / ₄ [4]	PG16-10 [4] C	PG ¹ / ₂ - ¹ / ₄ [4] C		PM ¹ / ₄ [4]		PM ¹ / ₄ [4] C	
	PG16-12 [4]	PG ¹ / ₂ - ⁵ / ₁₆ [4]	PG16-12 [4] C	PG ¹ / ₂ - ⁵ / ₁₆ [4] C		PM ⁵ / ₁₆ [4]		PM ⁵ / ₁₆ [4] C	
		PG ¹ / ₂ - ³ / ₈ [4]		PG ¹ / ₂ - ³ / ₈ [4] C		PM ³ / ₈ [4]		PM ³ / ₈ [4] C	
		PG ⁵ / ₈ - ¹ / ₂ [4]		PG ⁵ / ₈ - ¹ / ₂ [4] C		PM ¹ / ₂ [4]		PM ¹ / ₂ [4] C	
	PE Union Tee	Model type		Model type		PAU Branch Union Elbow	Model type		Model type
Standard pkg		Clean-room pkg	Standard pkg	Clean-room pkg	Standard pkg		Clean-room pkg	Standard pkg	Clean-room pkg
PEøD [4]		PEøD [4] C		PAUøD [4]			PAUøD [4] C		
PE4 [4]		PE ⁵ / ₃₂ [4]	PE4 [4] C	PE ⁵ / ₃₂ [4] C	PAU4 [4]		PAU ⁵ / ₃₂ [4]	PAU4 [4] C	PAU ⁵ / ₃₂ [4] C
PE6 [4]		PE ³ / ₁₆ [4]	PE6 [4] C	PE ³ / ₁₆ [4] C	PAU6 [4]		PAU ³ / ₁₆ [4]	PAU6 [4] C	PAU ³ / ₁₆ [4] C
PE8 [4]		PE ¹ / ₄ [4]	PE8 [4] C	PE ¹ / ₄ [4] C	PAU8 [4]		PAU ¹ / ₄ [4]	PAU8 [4] C	PAU ¹ / ₄ [4] C
PE10 [4]		PE ⁵ / ₁₆ [4]	PE10 [4] C	PE ⁵ / ₁₆ [4] C	PAU10 [4]		PAU ⁵ / ₁₆ [4]	PAU10 [4] C	PAU ⁵ / ₁₆ [4] C
PE12 [4]	PE ³ / ₈ [4]	PE12 [4] C	PE ³ / ₈ [4] C	PAU12 [4]	PAU ³ / ₈ [4]	PAU12 [4] C	PAU ³ / ₈ [4] C		
PE16 [4]	PE ¹ / ₂ [4]	PE16 [4] C	PE ¹ / ₂ [4] C		PAU ¹ / ₂ [4]		PAU ¹ / ₂ [4] C		
PEG Unequal Union Tee	Model type		Model type		PVU Tripod Union	Model type		Model type	
	Standard pkg	Clean-room pkg	Standard pkg	Clean-room pkg		Standard pkg	Clean-room pkg	Standard pkg	Clean-room pkg
	PEGøD1-øD2 [4]		PEGøD1-øD2 [4] C			PVUøD [4]		PVUøD [4] C	
	PEG4-6 [4]	PEG ⁵ / ₃₂ - ³ / ₁₆ [4]	PEG4-6 [4] C	PEG ⁵ / ₃₂ - ³ / ₁₆ [4] C		PVU4 [4]	PVU ⁵ / ₃₂ [4]	PVU4 [4] C	PVU ⁵ / ₃₂ [4] C
	PEG6-4 [4]	PEG ⁵ / ₃₂ - ¹ / ₄ [4]	PEG6-4 [4] C	PEG ⁵ / ₃₂ - ¹ / ₄ [4] C		PVU6 [4]	PVU ³ / ₁₆ [4]	PVU6 [4] C	PVU ³ / ₁₆ [4] C
	PEG6-8 [4]	PEG ³ / ₁₆ - ⁵ / ₃₂ [4]	PEG6-8 [4] C	PEG ³ / ₁₆ - ⁵ / ₃₂ [4] C		PVU8 [4]	PVU ¹ / ₄ [4]	PVU8 [4] C	PVU ¹ / ₄ [4] C
	PEG8-4 [4]	PEG ³ / ₁₆ - ¹ / ₄ [4]	PEG8-4 [4] C	PEG ³ / ₁₆ - ¹ / ₄ [4] C		PVU10 [4]	PVU ⁵ / ₁₆ [4]	PVU10 [4] C	PVU ⁵ / ₁₆ [4] C
	PEG8-6 [4]	PEG ¹ / ₄ - ³ / ₁₆ [4]	PEG8-6 [4] C	PEG ¹ / ₄ - ³ / ₁₆ [4] C		PVU12 [4]	PVU ³ / ₈ [4]	PVU12 [4] C	PVU ³ / ₈ [4] C
	PEG8-10 [4]	PEG ¹ / ₄ - ⁵ / ₃₂ [4]	PEG8-10 [4] C	PEG ¹ / ₄ - ⁵ / ₃₂ [4] C			PVU ¹ / ₂ [4]		PVU ¹ / ₂ [4] C
	PEG10-6 [4]	PEG ¹ / ₄ - ⁵ / ₁₆ [4]	PEG10-6 [4] C	PEG ¹ / ₄ - ⁵ / ₁₆ [4] C					
	PEG10-8 [4]	PEG ¹ / ₄ - ³ / ₈ [4]	PEG10-8 [4] C	PEG ¹ / ₄ - ³ / ₈ [4] C					
	PEG10-12 [4]	PEG ⁵ / ₁₆ - ⁵ / ₃₂ [4]	PEG10-12 [4] C	PEG ⁵ / ₁₆ - ⁵ / ₃₂ [4] C					
	PEG12-8 [4]	PEG ³ / ₁₆ - ³ / ₁₆ [4]	PEG12-8 [4] C	PEG ³ / ₁₆ - ³ / ₁₆ [4] C					
	PEG12-10 [4]	PEG ⁵ / ₁₆ - ¹ / ₄ [4]	PEG12-10 [4] C	PEG ⁵ / ₁₆ - ¹ / ₄ [4] C					
PEG12-16 [4]	PEG ³ / ₈ - ³ / ₁₆ [4]	PEG12-16 [4] C	PEG ³ / ₈ - ³ / ₁₆ [4] C						
PEG16-10 [4]	PEG ³ / ₈ - ¹ / ₄ [4]	PEG16-10 [4] C	PEG ³ / ₈ - ¹ / ₄ [4] C						
PEG16-12 [4]	PEG ³ / ₈ - ⁵ / ₁₆ [4]	PEG16-12 [4] C	PEG ³ / ₈ - ⁵ / ₁₆ [4] C						
	PEG ³ / ₈ - ¹ / ₂ [4]		PEG ³ / ₈ - ¹ / ₂ [4] C						
	PEG ¹ / ₂ - ⁵ / ₁₆ [4]		PEG ¹ / ₂ - ⁵ / ₁₆ [4] C						
	PEG ¹ / ₂ - ³ / ₈ [4]		PEG ¹ / ₂ - ³ / ₈ [4] C						
PW Unequal Union Y	Model type		Model type		PLH 45° Elbow	Model type		Model type	
	Standard pkg	Clean-room pkg	Standard pkg	Clean-room pkg		Standard pkg	Clean-room pkg	Standard pkg	Clean-room pkg
	PWøD1-øD2 [4]		PWøD1-øD2 [4] C			PLHøD-T [4]		PLHøD-T [4] C	
	PW6-4 [4]	PW ³ / ₁₆ - ⁵ / ₃₂ [4]	PW6-4 [4] C	PW ³ / ₁₆ - ⁵ / ₃₂ [4] C		PLH8-01 [4]	PLH ¹ / ₄ -N1U	PLH8-01 [4] C	PLH8-01 [4] C
	PW8-4 [4]	PW ¹ / ₄ - ¹ / ₄ [4]	PW8-4 [4] C	PW ¹ / ₄ - ¹ / ₄ [4] C		PLH8-02 [4]	PLH8-N1U	PLH8-02 [4] C	PLH8-02 [4] C
	PW8-6 [4]	PW ¹ / ₄ - ³ / ₁₆ [4]	PW8-6 [4] C	PW ¹ / ₄ - ³ / ₁₆ [4] C		PLH8-03 [4]	PLH8-N2U	PLH8-03 [4] C	PLH8-03 [4] C
	PW10-6 [4]	PW ¹ / ₄ - ⁵ / ₃₂ [4]	PW10-6 [4] C	PW ¹ / ₄ - ⁵ / ₃₂ [4] C		PLH10-01 [4]		PLH10-01 [4] C	PLH10-01 [4] C
	PW10-8 [4]	PW ⁵ / ₁₆ - ⁵ / ₃₂ [4]	PW10-8 [4] C	PW ⁵ / ₁₆ - ⁵ / ₃₂ [4] C		PLH10-02 [4]		PLH10-02 [4] C	PLH10-02 [4] C
	PW12-8 [4]	PW ⁵ / ₁₆ - ¹ / ₄ [4]	PW12-8 [4] C	PW ⁵ / ₁₆ - ¹ / ₄ [4] C		PLH10-03 [4]		PLH10-03 [4] C	PLH10-03 [4] C
	PW12-10 [4]	PW ³ / ₈ - ¹ / ₄ [4]	PW12-10 [4] C	PW ³ / ₈ - ¹ / ₄ [4] C		PLH10-04 [4]		PLH10-04 [4] C	PLH10-04 [4] C
		PW ³ / ₈ - ⁵ / ₁₆ [4]		PW ³ / ₈ - ⁵ / ₁₆ [4] C		PLH12-02 [4]		PLH12-02 [4] C	PLH12-02 [4] C
		PW ¹ / ₂ - ⁵ / ₁₆ [4]		PW ¹ / ₂ - ⁵ / ₁₆ [4] C		PLH12-03 [4]		PLH12-03 [4] C	PLH12-03 [4] C
		PW ¹ / ₂ - ³ / ₈ [4]		PW ¹ / ₂ - ³ / ₈ [4] C		PLH12-04 [4]		PLH12-04 [4] C	PLH12-04 [4] C
						PLH16-03 [4]		PLH16-03 [4] C	PLH16-03 [4] C
				PLH16-04 [4]		PLH16-04 [4] C	PLH16-04 [4] C		
PLLJ Long Plug-in Elbow	Model type		Model type		PAF Link-up Twin Barjo	Model type		Model type	
	Standard pkg	Clean-room pkg	Standard pkg	Clean-room pkg		Standard pkg	Clean-room pkg	Standard pkg	Clean-room pkg
	PLLJøD [4]		PLLJøD [4] C			PAFøD-T-T [4]		PAFøD-T-T [4] C	
	PLLJ4 [4]	PLLJ ⁵ / ₃₂ [4]	PLLJ4 [4] C	PLLJ ⁵ / ₃₂ [4] C		PAF4-M5 [4]	PAF ¹ / ₄ -N2U *	PAF4-M5 [4] C	PAF4-M5 [4] C
	PLLJ6 [4]	PLLJ ¹ / ₄ [4]	PLLJ6 [4] C	PLLJ ¹ / ₄ [4] C		PAF6-01 [4]		PAF6-01 [4] C	PAF6-01 [4] C
	PLLJ8 [4]	PLLJ ⁵ / ₁₆ [4]	PLLJ8 [4] C	PLLJ ⁵ / ₁₆ [4] C		PAF8-02 [4]		PAF8-02 [4] C	PAF8-02 [4] C
	PLLJ10 [4]	PLLJ ³ / ₈ [4]	PLLJ10 [4] C	PLLJ ³ / ₈ [4] C		PAF10-03 [4]		PAF10-03 [4] C	PAF10-03 [4] C
	PLLJ12 [4]	PLLJ ¹ / ₂ [4]	PLLJ12 [4] C	PLLJ ¹ / ₂ [4] C		PAF12-03 [4]		PAF12-03 [4] C	PAF12-03 [4] C
						PAF12-04 [4]		PAF12-04 [4] C	PAF12-04 [4] C
				Caution *1. Custom-made, build to order production *2. The white-letter model type in [] is new model. *3. [] is replaced with "W" if Light-gray specification is required otherwise please leave it blank. *4. The option: W, C, or WC is build to order production. *5. The model with low sales average may be build to order production. For details, please contact Pisco sales office or sales representative.					
				Package specifications 10 pcs. in a bag: Standard pkg 1 pc. in a bag (10 pcs./set): Clean-room pkg					