







The products listed in this page are ECO-friendly products.


* Please refer to page 4 for the details of ECO-friendly products.


POL Hex. Holed Banjo	Model type		Model type
	Standard pkg	Clean-room pkg	
	POLøD-T [4]	POLøD-TU	POLøD-T [4] C
	POL4-M5 [4]	POL1/4-N1U	POL4-M5 [4] C
	POL6-M10 [4]	POL1/4-N2U	POL6-M10 [4] C
	POL6-01 [4]	POL3/8-N2U	POL6-01 [4] C
	POL6-02 [4]	POL8-N1U **	POL6-02 [4] C
	POL8-01 [4]	POL12-N3U **	POL8-01 [4] C
	POL8-02 [4]		POL8-02 [4] C
	POL8-03 [4]		POL8-03 [4] C
	POL10-02 [4]		POL10-02 [4] C
	POL10-03 [4]		POL10-03 [4] C
	POL12-03 [4]		POL12-03 [4] C
	POL12-04 [4]		POL12-04 [4] C


PA Twin Banjo	Model type		Model type
	Standard pkg	Clean-room pkg	
	PAøD-T [4]	PAøD-TU	PAøD-T [4] C
	PA4-M5 [4]	PA3/32-U10U	PA4-M5 [4] C
	PA6-01 [4]	PA3/16-N1U	PA6-01 [4] C
	PA8-02 [4]	PA1/4-N1U	PA8-02 [4] C
	PA10-03 [4]	PA3/16-N2U	PA10-03 [4] C
	PA12-04 [4]	PA3/8-N3U	PA12-04 [4] C
		PA1/2-N4U	


PLF Female Elbow	Model type		Model type
	Standard pkg	Clean-room pkg	
	PLFøD-T [4]	PLFøD-TU	PLFøD-T [4] C
	PLF4-M5 [4]	PLF3/32-U10U	PLF4-M5 [4] C
	PLF4-M6 [4]	PLF3/32-N1U	PLF4-M6 [4] C
	PLF4-01 [4]	PLF3/32-N2U	PLF4-01 [4] C
	PLF4-02 [4]	PLF3/16-U10U	PLF4-02 [4] C
	PLF6-M5 [4]	PLF3/16-N1U	PLF6-M5 [4] C
	PLF6-M6 [4]	PLF3/16-N2U	PLF6-M6 [4] C
	PLF6-01 [4]	PLF3/16-N3U	PLF6-01 [4] C
	PLF6-02 [4]	PLF1/4-U10U	PLF6-02 [4] C
	PLF6-03 [4]	PLF1/4-N1U	PLF6-03 [4] C
	PLF8-01 [4]	PLF1/4-N2U	PLF8-01 [4] C
	PLF8-02 [4]	PLF1/4-N3U	PLF8-02 [4] C
	PLF8-03 [4]	PLF3/16-N1U	PLF8-03 [4] C
	PLF10-02 [4]	PLF3/16-N2U	PLF10-02 [4] C
	PLF10-03 [4]	PLF3/16-N3U	PLF10-03 [4] C
	PLF10-04 [4]	PLF3/8-N2U	PLF10-04 [4] C
	PLF12-02 [4]	PLF3/8-N3U	PLF12-02 [4] C
	PLF12-03 [4]	PLF3/8-N4U	PLF12-03 [4] C
	PLF12-04 [4]	PLF1/2-N2U	PLF12-04 [4] C
	PLF3/32-M5 [4]	PLF1/2-N3U	PLF3/32-M5 [4] C
	PLF3/32-01 [4]	PLF1/2-N4U	PLF3/32-01 [4] C
	PLF3/32-02 [4]	PLF4-N1U **	PLF3/32-02 [4] C
	PLF3/16-M5 [4]	PLF4-N2U **	PLF3/16-M5 [4] C
	PLF3/16-01 [4]	PLF6-N1U **	PLF3/16-01 [4] C
	PLF3/16-02 [4]	PLF6-N2U **	PLF3/16-02 [4] C
	PLF3/16-03 [4]	PLF8-N1U **	PLF3/16-03 [4] C
	PLF1/4-M5 [4]	PLF8-N2U **	PLF1/4-M5 [4] C
	PLF1/4-01 [4]	PLF10-N2U **	PLF1/4-01 [4] C
	PLF1/4-02 [4]		PLF1/4-02 [4] C
	PLF1/4-03 [4]		PLF1/4-03 [4] C
	PLF3/16-01 [4]		PLF3/16-01 [4] C
	PLF3/16-02 [4]		PLF3/16-02 [4] C
	PLF3/16-03 [4]		PLF3/16-03 [4] C
	PLF3/8-02 [4]		PLF3/8-02 [4] C
	PLF3/8-03 [4]		PLF3/8-03 [4] C
	PLF3/8-04 [4]		PLF3/8-04 [4] C
PLF1/2-02 [4]		PLF1/2-02 [4] C	
PLF1/2-03 [4]		PLF1/2-03 [4] C	
PLF1/2-04 [4]		PLF1/2-04 [4] C	


PIJ Union Stem	Model type		Model type
	Standard pkg	Clean-room pkg	
	PIJøD [4]		PIJøD [4] C
	PIJ4 [4]	PIJ5/32	PIJ4 [4] C
	PIJ6 [4]	PIJ3/16	PIJ6 [4] C
	PIJ8 [4]	PIJ1/4	PIJ8 [4] C
	PIJ10 [4]	PIJ5/16	PIJ10 [4] C
	PIJ12 [4]	PIJ3/8	PIJ12 [4] C
	PIJ16 [4]	PIJ1/2	PIJ16 [4] C


PIG Unequal Union Stem	Model type		Model type
	Standard pkg	Clean-room pkg	
	PIGøD1-øD2 [4]		PIGøD1-øD2 [4] C
	PIG6-4 [4]	PIG3/16-5/32	PIG6-4 [4] C
	PIG8-4 [4]	PIG1/4-5/32	PIG8-4 [4] C
	PIG8-6 [4]	PIG1/4-3/16	PIG8-6 [4] C
	PIG10-6 [4]	PIG5/16-1/4	PIG10-6 [4] C
	PIG10-8 [4]	PIG3/8-5/16	PIG10-8 [4] C
	PIG12-8 [4]	PIG1/2-3/8	PIG12-8 [4] C
	PIG12-10 [4]	PIG5/8-1/2	PIG12-10 [4] C
	PIG16-10 [4]		PIG16-10 [4] C
	PIG16-12 [4]		PIG16-12 [4] C


PP Plug	Model type		Model type
	Standard pkg	Clean-room pkg	
	PPøD [4]		PPøD [4] C
	PP4 [4]	PP3/32	PP4 [4] C
	PP6 [4]	PP3/16	PP6 [4] C
	PP8 [4]	PP1/4	PP8 [4] C
	PP10 [4]	PP3/8	PP10 [4] C
	PP12 [4]	PP1/2	PP12 [4] C
	PP16 [4]		PP16 [4] C


PF Extension Screw Adaptor	Model type		Model type
	Standard pkg	Clean-room pkg	
	PF T-T1	PF T-T1U	PF T-T1C
	PFM5-M5	PFU10-U10U	PFM5-M5C
	PFM5-M5L *	PFU10-N1U	PFM5-M5LC *
	PFM5-01	PFN1-U10U	PFM5-01C
	PF01-M5	PFN1-N1U	PF01-M5C
	PF01-01	PFN1-N2U	PF01-01C
	PF01-02	PFN1-N3U	PF01-02C
	PF01-03	PFN2-U10U	PF01-03C
	PF02-M5	PFN2-N1U	PF02-M5C
	PF02-01	PFN2-N2U	PF02-01C
	PF02-02	PFN2-N3U	PF02-02C
	PF02-03	PFN2-N4U	PF02-03C
	PF02-04	PFN3-N1U	PF02-04C
	PF03-01	PFN3-N2U	PF03-01C
	PF03-02	PFN3-N3U	PF03-02C
	PF03-03	PFN3-N4U	PF03-03C
	PF03-04	PFN4-N4U	PF03-04C
	PF04-04		PF04-04C

PFF Unequal Screw Union	Model type		Model type
	Standard pkg	Clean-room pkg	
	PFF T1-T2		PFF T1-T2C
	PFF01-M5	PFFN1-U10U	PFF01-M5C
	PFF02-01	PFFN2-N1U	PFF02-01C
	PFF03-01	PFFN3-N1U	PFF03-01C
	PFF03-02	PFFN3-N2U	PFF03-02C
	PFF04-02	PFFN4-N2U	PFF04-02C
	PFF04-03	PFFN4-N3U	PFF04-03C

PKVD Twin Triple Run Tee	Model type		Model type
	Standard pkg	Clean-room pkg	
	PKVDøD1-øD2-T [4]		PKVDøD1-øD2-T [4] C
	PKVD8-4-02 [4]		PKVD8-4-02 [4] C
	PKVD8-4-03 [4]		PKVD8-4-03 [4] C
	PKVD8-6-02 [4]		PKVD8-6-02 [4] C
	PKVD8-6-03 [4]		PKVD8-6-03 [4] C
	PKVD10-6-03 [4]		PKVD10-6-03 [4] C
	PKVD10-6-04 [4]		PKVD10-6-04 [4] C
	PKVD10-8-03 [4]		PKVD10-8-03 [4] C
	PKVD10-8-04 [4]		PKVD10-8-04 [4] C

PHF Link-up Banjo	Model type		Model type
	Standard pkg	Clean-room pkg	
	PHFøD-T-T1 [4]		PHFøD-T-T1C
	PHF4-M5 [4]		PHF4-M5 [4] C
	PHF4-01 [4]		PHF4-01 [4] C
	PHF6-M5 [4]		PHF6-M5 [4] C
	PHF6-01 [4]		PHF6-01 [4] C
	PHF6-02 [4]		PHF6-02 [4] C
	PHF8-01 [4]		PHF8-01 [4] C
	PHF8-02 [4]		PHF8-02 [4] C
	PHF8-03 [4]		PHF8-03 [4] C
	PHF10-02 [4]		PHF10-02 [4] C
	PHF10-03 [4]		PHF10-03 [4] C
	PHF12-03 [4]		PHF12-03 [4] C
	PHF12-04 [4]		PHF12-04 [4] C
	PHF3/32-M5 [4]		PHF3/32-M5 [4] C
	PHF3/32-01 [4]		PHF3/32-01 [4] C
	PHF3/16-M5 [4]		PHF3/16-M5 [4] C
	PHF3/16-01 [4]		PHF3/16-01 [4] C
	PHF3/16-02 [4]		PHF3/16-02 [4] C
	PHF1/4-M5 [4]		PHF1/4-M5 [4] C
	PHF1/4-01 [4]		PHF1/4-01 [4] C
	PHF1/4-02 [4]		PHF1/4-02 [4] C
	PHF3/16-01 [4]		PHF3/16-01 [4] C
	PHF3/16-02 [4]		PHF3/16-02 [4] C
	PHF3/16-03 [4]		PHF3/16-03 [4] C
PHF3/8-02 [4]		PHF3/8-02 [4] C	
PHF3/8-03 [4]		PHF3/8-03 [4] C	
PHF1/2-03 [4]		PHF1/2-03 [4] C	
PHF1/2-04 [4]		PHF1/2-04 [4] C	

PMF Bulkhead Female Straight	Model type		Model type
	Standard pkg	Clean-room pkg	
	PMFøD-T [4]		PMFøD-T [4] C
	PMF4-01 [4]	PMF3/32-N1U	PMF4-01 [4] C
	PMF4-02 [4]	PMF3/32-N2U **	PMF4-02 [4] C
	PMF6-01 [4]	PMF3/16-N1U	PMF6-01 [4] C
	PMF6-02 [4]	PMF3/16-N2U	PMF6-02 [4] C
	PMF6-03 [4]	PMF1/4-N1U	PMF6-03 [4] C
	PMF8-01 [4]	PMF1/4-N2U	PMF8-01 [4] C
	PMF8-02 [4]	PMF1/4-N3U	PMF8-02 [4] C
	PMF8-03 [4]	PMF3/16-N1U	PMF8-03 [4] C
	PMF10-02 [4]	PMF3/16-N2U	PMF10-02 [4] C
	PMF10-03 [4]	PMF3/16-N3U	PMF10-03 [4] C
	PMF12-02 [4]	PMF3/8-N1U	PMF12-02 [4] C
	PMF12-03 [4]	PMF3/8-N2U	PMF12-03 [4] C
	PMF12-04 [4]	PMF3/8-N3U	PMF12-04 [4] C
	PMF16-03 [4]	PMF1/2-N2U	PMF16-03 [4] C
	PMF16-04 [4]	PMF1/2-N3U	PMF16-04 [4] C
		PMF1/2-N4U	
		PMF4-N1U **	
		PMF6-N1U **	
		PMF6-N2U **	
	PMF8-N3U **		
	PMF10-N3U **		

PTJ PT Jack	Model type		Model type
	Standard pkg	Clean-room pkg	
	PTJøD-T		PTJøD-T-C
	PTJ4-M5		PTJ4-M5C
	PTJ4-01		PTJ4-01C
	PTJ6-M5		PTJ6-M5C
	PTJ6-01		PTJ6-01C
	PTJ6-02		PTJ6-02C
	PTJ8-01		PTJ8-01C
	PTJ8-02		PTJ8-02C
	PTJ8-03		PTJ8-03C
	PTJ10-03		PTJ10-03C

⚠ Cautions

- *0. PFM5-M5L is long type of PFM5-M5.
- *1. Custom-made, build to order production
- *2. The white-letter model type in [] is new model.
- *3. [] is replaced with "W" if Light-gray specification is required otherwise please leave it blank.
- *4. The option: W, C, or WC is build to order production.
- *5. The model with low sales average may be build to order production. For details, please contact Pisco sales office or sales representative.



Package specifications
10 pcs. in a bag: Standard pkg
1 pc. in a bag (10 pcs./set): Clean-room pkg