



The products listed in this page are ECO-friendly products.  
\* Please refer to page 4 for the details of ECO-friendly products.

PL Elbow	Model type		PB Branch Tee	Model type		POC Inner Hex. Straight	Model type	
	Standard pkg	Clean-room pkg		Standard pkg	Clean-room pkg		Standard pkg	Clean-room pkg
	PLøD-TM (4)	PLøD-TMU		PBøD-T (4) M	PBøD-TMU		POCøD-TM (4)	POCøD-TMU
	PL180-M3M (4)	PL1/8-U10MU		PB180-M3M (4)	PB1/8-U10MU		POC180-M3M (4)	POC1/8-U10MU
	PL180-M5M (4)	PL1/8-N0MU		PB180-M5M (4)	PB1/8-N0MU		POC3-M3M (4)	POC3/8-U10MU
	PL180-01M (4)	PL1/8-N1MU		PB180-M5M (4) C	PB1/8-N1MU		POC3-M5M (4)	POC3/8-N1MU
	PL3-M3M (4)	PL1/8-N2MU		PB3-M3M (4)	PB3-M3M (4) C		POC3-M6M (4)	POC3/16-U10MU **
	PL3-M5M (4)	PL5/32-U10MU		PB3-M5M (4)	PB3-M5M (4) C		POC4-M3M (4)	POC3/16-N1MU **
	PL3-M6M (4)	PL5/32-N0MU		PB3-M6M (4)	PB3-M6M (4) C		POC4-M5M (4)	POC4-M3M (4) C
	PL3-01M (4)	PL5/32-N1MU		PB3-01M (4)	PB3-01M (4) C		POC4-M6M (4)	POC4-M5M (4) C
	PL4-M3M (4)	PL5/32-N2MU		PB3-01M (4) C	PB3-01M (4) C		POC4-M6M (4)	POC4-M6M (4) C
	PL4-M5M (4)	PL1/4-U10MU		PB4-M3M (4)	PB4-M3M (4) C		POC4-01M (4)	POC1/4-N1MU
	PL4-M6M (4)	PL1/4-N0MU		PB4-M5M (4)	PB4-M5M (4) C		POC6-M5M (4)	
	PL4-01M (4)	PL1/4-N1MU		PB4-M6M (4)	PB4-M6M (4) C		POC6-M6M (4)	POC6-M5M (4) C
	PL4-02M (4)	PL1/4-N2MU		PB4-01M (4)	PB4-01M (4) C		POC6-01M (4)	POC6-01M (4) C
	PL6-M5M (4)	PL1/4-N3MU		PB4-02M (4)	PB4-02M (4) C		POC1/8-M3M (4)	POC1/8-M3M (4) C
	PL6-M6M (4)			PB6-M5M (4)	PB6-M5M (4) C		POC1/8-M5M (4)	POC1/8-M5M (4) C
	PL6-01M (4)			PB6-M6M (4)	PB6-M6M (4) C		POC1/8-M6M (4)	POC1/8-M6M (4) C
	PL6-02M (4)			PB6-01M (4)	PB6-01M (4) C		POC1/8-M7M (4) **	POC1/8-M7M (4) C **
	PL6-03M (4)			PB6-02M (4)	PB6-02M (4) C		POC3/32-M3M (4)	POC3/32-M3M (4) C
	PL1/8-M3M (4)			PB6-03M (4)	PB6-03M (4) C		POC3/32-M5M (4) **	POC3/32-M5M (4) C **
	PL1/8-M5M (4)			PB1/8-M3M (4)	PB1/8-M3M (4) C		POC3/32-M6M (4)	POC3/32-M6M (4) C
	PL1/8-M6M (4)			PB1/8-M5M (4)	PB1/8-M5M (4) C		POC3/32-01M (4)	POC3/32-01M (4) C
	PL1/8-01M (4)			PB1/8-M6M (4)	PB1/8-M6M (4) C		POC3/16-M5M (4) **	POC3/16-M5M (4) C **
	PL5/32-M3M (4)			PB1/8-01M (4)	PB1/8-01M (4) C		POC1/4-M5M (4)	POC1/4-M5M (4) C
	PL5/32-M5M (4)			PB3/32-M3M (4)	PB3/32-M3M (4) C		POC1/4-M6M (4)	POC1/4-M6M (4) C
	PL5/32-M6M (4)			PB3/32-M5M (4)	PB3/32-M5M (4) C		POC1/4-M7M (4)	POC1/4-M7M (4) C
	PL5/32-01M (4)			PB3/32-M6M (4)	PB3/32-M6M (4) C		POC1/4-01M (4)	POC1/4-01M (4) C
	PL5/32-02M (4)			PB3/32-01M (4)	PB3/32-01M (4) C			
	PL1/4-M5M (4)			PB3/32-02M (4)	PB3/32-02M (4) C			
	PL1/4-M6M (4)			PB1/4-M5M (4)	PB1/4-M5M (4) C			
	PL1/4-M7M (4)			PB1/4-M6M (4)	PB1/4-M6M (4) C			
PL1/4-01M (4)		PB1/4-01M (4)	PB1/4-01M (4) C					
PL1/4-02M (4)		PB1/4-02M (4)	PB1/4-02M (4) C					
PL1/4-03M (4)		PB1/4-03M (4)	PB1/4-03M (4) C					
	PLLøD-TM (4)	PLLøD-TMU		PDøD-TM (4)	PDøD-TMU		POLøD-TM (4)	POLøD-TMU
	PLL180-M3M (4)	PLL1/8-U10MU		PD180-M3M (4)	PD180-M3M (4) C		POL3-M5M (4)	POL1/8-U10MU
	PLL180-M5M (4)	PLL1/8-N0MU		PD180-M5M (4)	PD180-M5M (4) C		POL4-M5M (4)	POL3/32-U10MU
	PLL3-M3M (4)	PLL1/8-N1MU		PD3-M3M (4)	PD3-M3M (4) C		POL6-M5M (4)	
	PLL3-M5M (4)	PLL5/32-U10MU		PD3-M5M (4)	PD3-M5M (4) C		POL1/8-M5M (4)	POL1/8-M5M (4) C
	PLL3-M6M (4)	PLL5/32-N0MU		PD3-01M (4)	PD3-01M (4) C		POL3/32-M5M (4)	POL3/32-M5M (4) C
	PLL3-01M (4)	PLL5/32-N1MU		PD4-M3M (4)	PD4-M3M (4) C			
	PLL4-M3M (4)	PLL5/32-N2MU		PD4-M5M (4)	PD4-M5M (4) C			
	PLL4-M5M (4)	PLL1/4-U10MU		PD4-M6M (4)	PD4-M6M (4) C			
	PLL4-M6M (4)	PLL1/4-N0MU		PD4-01M (4)	PD4-01M (4) C			
	PLL4-01M (4)	PLL1/4-N1MU		PD4-02M (4)	PD4-02M (4) C			
	PLL4-02M (4)	PLL1/4-N2MU		PD6-M5M (4)	PD6-M5M (4) C			
	PLL6-M5M (4)	PLL1/4-N3MU		PD6-M6M (4)	PD6-M6M (4) C			
	PLL6-M6M (4)			PD6-01M (4)	PD6-01M (4) C			
	PLL6-01M (4)			PD6-02M (4)	PD6-02M (4) C			
	PLL6-02M (4)			PD6-03M (4)	PD6-03M (4) C			
	PLL6-03M (4)			PD1/8-M3M (4)	PD1/8-M3M (4) C			
	PLL1/8-M3M (4)			PD1/8-M5M (4)	PD1/8-M5M (4) C			
	PLL1/8-M5M (4)			PD1/8-M6M (4)	PD1/8-M6M (4) C			
	PLL1/8-M6M (4)			PD1/8-01M (4)	PD1/8-01M (4) C			
	PLL1/8-01M (4)			PD3/32-M3M (4)	PD3/32-M3M (4) C			
	PLL5/32-M3M (4)			PD3/32-M5M (4)	PD3/32-M5M (4) C			
	PLL5/32-M5M (4)			PD3/32-M6M (4)	PD3/32-M6M (4) C			
	PLL5/32-M6M (4)			PD3/32-01M (4)	PD3/32-01M (4) C			
	PLL5/32-01M (4)			PD1/4-M5M (4)	PD1/4-M5M (4) C			
	PLL5/32-02M (4)			PD1/4-M6M (4)	PD1/4-M6M (4) C			
	PLL1/4-M5M (4)			PD1/4-01M (4)	PD1/4-01M (4) C			
	PLL1/4-M6M (4)			PD1/4-02M (4)	PD1/4-02M (4) C			
	PLL1/4-01M (4)			PD1/4-03M (4)	PD1/4-03M (4) C			
	PLL1/4-02M (4)							
PLL1/4-03M (4)								
	PLHøD-TM (4)	PLHoD-TM (4) C		POLLøD-TM (4)	POLLøD-TMU		PLHøD-TM (4)	PLHoD-TM (4) C
	PLH3-M3M (4)	PLH3-M3M (4) C		POLL3-M5M (4)	POLL1/8-U10MU		PLH3-M5M (4)	PLH3-M5M (4) C
	PLH3-M5M (4)	PLH3-M5M (4) C		POLL4-M5M (4)	POLL5/32-U10MU		PLH4-M5M (4)	PLH4-M5M (4) C
	PLH4-M3M (4)	PLH4-M3M (4) C		POLL6-M5M (4)			PLH6-M5M (4)	PLH6-M5M (4) C
	PLH4-M5M (4)	PLH4-M5M (4) C		POLL1/8-M5M (4)			PLH1/8-M5M (4) C	PLH1/8-M5M (4) C
	PLH4-M6M (4)	PLH4-M6M (4) C		POLL3/32-M5M (4)			PLH3/32-M5M (4) C	PLH3/32-M5M (4) C
	PLH4-01M (4)	PLH4-01M (4) C						
	PLH6-M5M (4)	PLH6-M5M (4) C						
	PLH6-M6M (4)	PLH6-M6M (4) C						
	PLH6-01M (4)	PLH6-01M (4) C						
	PLH6-02M (4) **	PLH6-02M (4) C						
	PCCøD-TM (4)	PCCøD-TMU		PCCøD-TM (4)	PCCøD-TMU		PCCøD-TM (4)	PCCøD-TMU
	PCC3-M6M (4)	PCC3-M6M (4) C		PCC3-M6M (4)	PCC3-M6M (4) C		PCC4-M6M (4)	PCC4-M6M (4) C
	PCC4-M6M (4)	PCC4-M6M (4) C		PCC3-01M (4)	PCC3-01M (4) C		PCC4-M8M (4)	PCC4-M8M (4) C
	PCC6-M8M (4)	PCC6-M8M (4) C		PCC3-02M (4)	PCC3-02M (4) C		PCC6-M8M (4)	PCC6-M8M (4) C
				PD1/4-M5M (4)	PD1/4-M5M (4) C		PCC1/8-M6M (4)	PCC1/8-M6M (4) C
				PD1/4-M6M (4)	PD1/4-M6M (4) C			
				PD1/4-01M (4)	PD1/4-01M (4) C			
				PD1/4-02M (4)	PD1/4-02M (4) C			
				PD1/4-03M (4)	PD1/4-03M (4) C			

Package specifications  
10 pcs. in a bag: Mini-Std. pkg  
1 pc. in a bag (10 pcs./set): Mini clean-room pkg

- Cautions**
- \*1. Custom-made, build to order production
  - \*2. The white-letter model type in   is new model.
  - \*3. (4) is replaced with "W" if Light-gray specification is required otherwise please leave it blank.
  - \*4. The option: W, C, or WC is build to order production.
  - \*5. The model with low sales average may be build to order production. For details, please contact Pisco sales office or sales representative.