


















The products listed in this page are ECO-friendly products.  
\* Please refer to page 4 for the details of ECO-friendly products.

PG	Model type: Standard pkg		Model type: Clean-room pkg		PZC	Model type: Standard pkg		Model type: Clean-room pkg		PX	Model type
Unequal Union Straight	PGøD,-øD <sub>2</sub> M [4]		PGøD,-øD <sub>2</sub> M [4] C		Cross C	PZCøD,-øD <sub>2</sub> M [4]		PZCøD,-øD <sub>2</sub> M [4] C		Branch Y	Standard pkg
	PG3-180M [4]	PG3/32-1/8M [4]	PG3-180M [4] C	PG3/32-1/8M [4] C		PZC4-3M [4]	PZC3/32-1/8M [4]	PZC4-3M [4] C	PZC3/32-1/8M [4] C		PXøD-TMU
	PG4-180M [4]	PG3/16-1/8M [4]	PG4-180M [4] C	PG1/4-1/8M [4] C		PZC6-4M [4]		PZC6-4M [4] C			PX1/8-N1MU
	PG4-3M [4]	PG1/4-1/8M [4]	PG4-3M [4] C	PG1/4-5/32M [4] C		PZC4-1/8M [4]		PZC4-1/8M [4] C			PX1/8-N2MU
	PG4-1/8M [4]	PG1/4-5/32M [4]	PG4-1/8M [4] C			PZC6-1/8M [4]		PZC6-1/8M [4] C			
	PG6-3M [4]		PG6-3M [4] C			PZC1/8-3M [4]		PZC1/8-3M [4] C			
	PG6-1/8M [4]		PG6-1/8M [4] C								
	PG6-4M [4]		PG6-4M [4] C								
PV	Model type: Standard pkg		Model type: Clean-room pkg		PGJ	Model type: Standard pkg		Model type: Clean-room pkg			
Union Elbow	PVøDM [4]		PVøDM [4] C		Unequal Plug-in Straight	PGJøD,-øD <sub>2</sub> M [4]		PGJøD,-øD <sub>2</sub> M [4] C			
	PV180M [4]	PV1/8M [4]	PV180M [4] C	PV1/8M [4] C		PGJ3-1/8M [4]	PGJ1/8-5/32M [4]	PGJ3-1/8M [4] C	PGJ1/8-5/32M [4] C		
	PV3M [4]	PV5/32M [4]	PV3M [4] C	PV5/32M [4] C		PGJ3-180M [4]	PGJ1/8-1/4M [4]	PGJ3-180M [4] C	PGJ1/8-1/4M [4] C		
	PV4M [4]	PV1/4M [4]	PV4M [4] C	PV1/4M [4] C		PGJ3-4M [4]	PGJ5/32-1/8M [4]	PGJ3-4M [4] C	PGJ5/32-1/8M [4] C		
	PV6M [4]		PV6M [4] C			PGJ3-6M [4]	PGJ3/32-1/4M [4]	PGJ3-6M [4] C	PGJ3/32-1/4M [4] C		
						PGJ4-180M [4]	PGJ3/16-1/8M [4]	PGJ4-180M [4] C	PGJ3/16-1/8M [4] C		
						PGJ4-3M [4]	PGJ3/16-5/32M [4]	PGJ4-3M [4] C	PGJ3/16-5/32M [4] C		
						PGJ4-1/8M [4]	PGJ3/16-1/4M [4]	PGJ4-1/8M [4] C	PGJ3/16-1/4M [4] C		
						PGJ4-6M [4]	PGJ1/4-1/8M [4]	PGJ4-6M [4] C	PGJ1/4-1/8M [4] C		
						PGJ6-3M [4]	PGJ1/4-5/32M [4]	PGJ6-3M [4] C	PGJ1/4-5/32M [4] C		
						PGJ6-1/8M [4]	PGJ1/4-6M [4]	PGJ6-1/8M [4] C	PGJ1/4-6M [4] C		
						PGJ6-4M [4]		PGJ6-4M [4] C			
						PGJ6-1/4M [4]		PGJ6-1/4M [4] C			
PE	Model type: Standard pkg		Model type: Clean-room pkg		PLJ	Model type: Standard pkg		Model type: Clean-room pkg			
Union Tee	PEøDM [4]		PEøDM [4] C		Plug-in Elbow	PLJøDM [4]		PLJøDM [4] C			
	PE180M [4]	PE1/8M [4]	PE180M [4] C	PE1/8M [4] C		PLJ3M [4]	PLJ1/8M [4]	PLJ3M [4] C	PLJ1/8M [4] C		
	PE3M [4]	PE5/32M [4]	PE3M [4] C	PE5/32M [4] C		PLJ4M [4]	PLJ5/32M [4]	PLJ4M [4] C	PLJ5/32M [4] C		
	PE4M [4]	PE1/4M [4]	PE4M [4] C	PE1/4M [4] C		PLJ6M [4]	PLJ3/16M [4]	PLJ6M [4] C	PLJ3/16M [4] C		
	PE6M [4]		PE6M [4] C				PLJ1/4M [4]		PLJ1/4M [4] C		
PEG	Model type: Standard pkg		Model type: Clean-room pkg		PLGJ	Model type: Standard pkg		Model type: Clean-room pkg			
Unequal Union Tee	PEGøD,-øD <sub>2</sub> M [4]		PEGøD,-øD <sub>2</sub> M [4] C		Unequal Plug-in Elbow	PLGJøD,-øD <sub>2</sub> M [4]		PLGJøD,-øD <sub>2</sub> M [4] C			
	PEG3-180M [4]	PEG1/8-5/32M [4]	PEG3-180M [4] C	PEG1/8-5/32M [4] C		PLGJ3-180M [4]	PLGJ1/8-3M [4]	PLGJ3-180M [4] C	PLGJ1/8-3M [4] C		
	PEG3-4M [4]	PEG5/32-1/8M [4]	PEG3-4M [4] C	PEG5/32-1/8M [4] C		PLGJ3-1/8M [4]	PLGJ1/8-5/32M [4]	PLGJ3-1/8M [4] C	PLGJ1/8-5/32M [4] C		
	PEG4-3M [4]	PEG3/32-1/4M [4]	PEG4-3M [4] C	PEG3/32-1/4M [4] C		PLGJ3-4M [4]	PLGJ1/8-1/4M [4]	PLGJ3-4M [4] C	PLGJ1/8-1/4M [4] C		
	PEG4-1/8M [4]	PEG1/4-5/32M [4]	PEG4-1/8M [4] C	PEG1/4-5/32M [4] C		PLGJ3-6M [4]	PLGJ5/32-1/8M [4]	PLGJ3-6M [4] C	PLGJ5/32-1/8M [4] C		
	PEG4-6M [4]		PEG4-6M [4] C			PLGJ4-180M [4]	PLGJ3/32-1/4M [4]	PLGJ4-180M [4] C	PLGJ3/32-1/4M [4] C		
	PEG6-4M [4]		PEG6-4M [4] C			PLGJ4-3M [4]	PLGJ3/16-1/8M [4]	PLGJ4-3M [4] C	PLGJ3/16-1/8M [4] C		
						PLGJ4-1/8M [4]	PLGJ3/16-5/32M [4]	PLGJ4-1/8M [4] C	PLGJ3/16-5/32M [4] C		
						PLGJ4-6M [4]	PLGJ3/16-1/4M [4]	PLGJ4-6M [4] C	PLGJ3/16-1/4M [4] C		
						PLGJ6-3M [4]	PLGJ1/4-1/8M [4]	PLGJ6-3M [4] C	PLGJ1/4-1/8M [4] C		
						PLGJ6-1/8M [4]	PLGJ1/4-5/32M [4]	PLGJ6-1/8M [4] C	PLGJ1/4-5/32M [4] C		
						PLGJ6-4M [4]	PLGJ1/4-6M [4]	PLGJ6-4M [4] C	PLGJ1/4-6M [4] C		
						PLGJ6-1/4M [4]		PLGJ6-1/4M [4] C			
PY	Model type: Standard pkg		Model type: Clean-room pkg		PYJ	Model type: Standard pkg		Model type: Clean-room pkg			
Union Y	PYøDM [4]		PYøDM [4] C		Plug-in Y	PYJøDM [4]		PYJøDM [4] C			
	PY3M [4]	PY1/8M [4]	PY3M [4] C	PY1/8M [4] C		PYJ3M [4]	PYJ1/8M [4]	PYJ3M [4] C	PYJ1/8M [4] C		
	PY4M [4]	PY5/32M [4]	PY4M [4] C	PY5/32M [4] C		PYJ4M [4]	PYJ5/32M [4]	PYJ4M [4] C	PYJ5/32M [4] C		
	PY6M [4]	PY1/4M [4]	PY6M [4] C	PY1/4M [4] C		PYJ6M [4]		PYJ6M [4] C			
PW	Model type: Standard pkg		Model type: Clean-room pkg		PWJ	Model type: Standard pkg		Model type: Clean-room pkg			
Unequal Union Y	PWøD,-øD <sub>2</sub> M [4]		PWøD,-øD <sub>2</sub> M [4] C		Unequal Plug-in Y	PWJøD,-øD <sub>2</sub> M [4]		PWJøD,-øD <sub>2</sub> M [4] C			
	PW4-3M [4]	PW5/32-1/8M [4]	PW4-3M [4] C	PW5/32-1/8M [4] C		PWJ4-3M [4]	PWJ3/32-1/8M [4]	PWJ4-3M [4] C	PWJ3/32-1/8M [4] C		
	PW6-3M [4]	PW1/4-1/8M [4]	PW6-3M [4] C	PW1/4-1/8M [4] C		PWJ6-3M [4]		PWJ6-3M [4] C			
	PW6-4M [4]	PW1/4-5/32M [4]	PW6-4M [4] C	PW1/4-5/32M [4] C		PWJ6-4M [4]		PWJ6-4M [4] C			
	PW4-1/8M [4]		PW4-1/8M [4] C			PWJ4-1/8M [4]		PWJ4-1/8M [4] C			
	PW6-1/8M [4]		PW6-1/8M [4] C			PWJ6-1/8M [4]		PWJ6-1/8M [4] C			
	PW1/8-3M [4]		PW1/8-3M [4] C								
PM	Model type: Standard pkg		Model type: Clean-room pkg		PIJ	Model type: Standard pkg		Model type: Clean-room pkg			
Bulkhead Union	PMøDM [4]		PMøDM [4] C		Union Stem	PIJøDM [4]		PIJøDM [4] C			
	PM3M [4]	PM1/8M [4]	PM3M [4] C	PM1/8M [4] C		PIJ3M [4]	PIJ1/8M [4]	PIJ3M [4] C	PIJ1/8M [4] C		
	PM4M [4]	PM5/32M [4]	PM4M [4] C	PM5/32M [4] C							
	PM6M [4]	PM1/4M [4]	PM6M [4] C	PM1/4M [4] C							
PZA	Model type: Standard pkg		Model type: Clean-room pkg		PP	Model type: Standard pkg		Model type: Clean-room pkg			
Cross A	PZAøDM [4]		PZAøDM [4] C		Plug	PPøDM [4]		PPøDM [4] C			
	PZA3M [4]	PZA1/8M [4]	PZA3M [4] C	PZA1/8M [4] C		PP180M [4]	PP1/8M [4]	PP180M [4] C	PP1/8M [4] C		
	PZA4M [4]	PZA5/32M [4]	PZA4M [4] C	PZA5/32M [4] C		PP3M [4]		PP3M [4] C			
	PZA6M [4]		PZA6M [4] C								
PZB	Model type: Standard pkg		Model type: Clean-room pkg								
Cross B	PZBøD,-øD <sub>2</sub> M [4]		PZBøD,-øD <sub>2</sub> M [4] C								
	PZB4-3M [4]	PZB3/32-1/8M [4]	PZB4-3M [4] C	PZB3/32-1/8M [4] C							
	PZB6-4M [4]		PZB6-4M [4] C								
	PZB4-1/8M [4]		PZB4-1/8M [4] C								
	PZB6-1/8M [4]		PZB6-1/8M [4] C								
	PZB1/8-3M [4]		PZB1/8-3M [4] C								



**Cautions**

1. Custom-made, build to order production
2. The white-letter model type in [ ] is new model.
3. [ ] is replaced with "W" if Light-gray specification is required otherwise please leave it blank.
4. The option: W, C, or WC is build to order production.
5. The model with low sales average may be build to order production. For details, please contact Pisco sales office or sales representative.



**Package specifications**

- 10 pcs. in a bag: Mini-Std. pkg
- 1 pc. in a bag (10 pcs./set): Mini clean-room pkg

Fitting Control Valve Vacuum Actuator Tube Parailchain Robot Parts