

## Plug Lead Type

# Base Mounted Manifold Bar Base

## Individual Wiring: C Kit

### S0700 Series



### How to Order Manifold

SS0755 - 08 C4 C -

Base Mounted

Stations

Symbol	Stations
02	2 stations
⋮	⋮
20	20 stations

Option

Symbol	Type
Nil	None
R (Note)	External pilot

Note) For details, refer to page 755.

\* For manifold optional parts, refer to pages 755 to 757.

Cylinder port size

Symbol	Port size	Manifold pitch
M5	M5 thread	8.5
C2	With ø2 One-touch fitting	
C3	With ø3.2 One-touch fitting	
C4	With ø4 One-touch fitting	
CM	Mixed sizes and with port plug (Note)	
N1	With ø1/8" One-touch fitting	7.5
N3	With ø5/32" One-touch fitting	
NM	Mixed sizes and with port plug (Note)	
M3	M3 thread	
V2	ø2 Barb fitting	
V3	ø3.2 Barb fitting	
V4	ø4 Barb fitting	
VM	Mixed sizes and with port plug (Note)	

Note) Specify "Mixed sizes and with port plug" on the manifold specification sheet.

Connector individual wiring

P, R port thread type

Symbol	Manifold pitch	
	8.5	7.5
Nil	Rc	M5
F	G	/
N	NPT	
T	NPTF	

### How to Order Valves

S07 1 5 - 5 G

Type of actuation

Symbol	Specifications
1	2-position single
2	2-position double
3	3-position closed center
A	4-position dual 3-port (N.C. + N.C.) [Exhaust center]
B	4-position dual 3-port (N.O. + N.O.) [Pressure center]
C	4-position dual 3-port (N.C. + N.O.)

Note) For symbol, refer to page 741.

Electrical entry

Symbol	Specifications
G	Grommet
M	Plug connector, with lead wire (With light/surge voltage suppressor)
MO	Plug connector, without lead wire (With light/surge voltage suppressor)

Voltage

Symbol	Type
5	24 VDC
6	12 VDC

Base Mounted Manifold

Function

Symbol	Type
Nil	Standard
R	External pilot (Note)

Note) Not compatible with dual 3-port valves.

### How to Order Manifold Assembly

Specify the part numbers for valves and options together beneath the manifold base part number.

<Example>

Connector kit

SS0755-07C4C · 1 set-Manifold base part no.

\* S0715-5G ····· 3 sets-Valve part no. (Stations 1 to 3)

\* S0725-5G ····· 2 sets-Valve part no. (Stations 4 to 5)

\* S07A5-5G ····· 2 sets-Valve part no. (Stations 6 to 7)

Prefix the asterisk to the part numbers of the solenoid valve etc.

Write sequentially from the 1st station on the D side. When part numbers written collectively are complicated, specify on the manifold specification sheet.

