

Parallel Type Air Gripper (Standard) Compact Series (Without Auto Switch)

MHZA2-6/MHZAJ2-6 Series

ø6

How to Order

MHZA 2 — 6 D [] [] — [] [] []

MHZAJ 2 — 6 D [] [] []

With dust cover ●

Number of fingers ●

2 2 fingers

Bore size ●

6 6 mm

Action ●

D	Double acting
S	Single acting (Normally open)
C	Single acting (Normally closed)

Finger option ●

[Standard]
Nil: Basic type

1: Side tapped mounting

2: Through-holes in opening/closing direction

3: Flat type fingers

● Made to Order
Refer to page 399 for details.

● Dust cover type

Nil	Chloroprene rubber (CR)
F	Fluororubber (FKM)
S	Silicone rubber (S)

● Body option

Nil: Basic type

E: End boss type Side ported (Double acting/Single acting)

K: End boss type Axial ported with ø4 One-touch fitting (Single acting)

H: End boss type Axial ported with ø4 hose nipple (Single acting)

M: End boss type Axial ported with M3 port (Single acting)