

3-color display

Digital Flow Monitor

LFE0 Series



How to Order

LFE0A - **MVC**

Type

0 Remote type monitor unit

For remote type sensor unit, select the analog output 1 to 5 V type.
Applicable sensors: LFE□□□□□

Output specifications

Symbol	OUT1	OUT2
A	NPN	NPN
B	PNP	PNP
C	NPN	Analog 1 to 5 V
D	NPN	Analog 4 to 20 mA

Lead wire

Nil	With power supply/output connection lead wire (2 m)	
N	Without power supply/output connection lead wire	

Lead wire is not connected, but shipped together.

Remote type monitor unit/Unit specifications

Symbol	Instantaneous flow rate	Accumulated flow
M	L/min	L
G	gal/min	gal

* Under the New Measurement Law, units other than SI (symbol "M") cannot be used in Japan.
Note) G: Made to Order

Reference: 1 [L/min] ↔ 0.2642 [gal/min]
1 [gal/min] ↔ 3.785 [L/min]

Option 2

Nil	Without connector	
C	Sensor connector (1 pc.)	

Connector is not connected, but shipped together.

Option 1

Nil	None	
T	Panel mount adapter	
V	Front protective cover + Panel mount adapter	

Option/Part No.

When only optional parts are required, order with the part numbers listed below.

Description	Part no.	Note
Panel mount adapter	ZS-26-B	With waterproof seal, mounting screw
Front protective cover + Panel mount adapter	ZS-26-C	With waterproof seal, mounting screw
Front protective cover only	ZS-26-01	Separately order panel mount adapter etc.
Power supply/output connection lead wire	ZS-40-W	Lead wire length 2 m
Sensor connector (e-con)	ZS-28-C-5	1 pc.
Lead wire with connector for copying	ZS-40-Y	Connect up to 10 slave units

- PFM
- PFMB
- PFMC
- PFMV
- PF2A
- PF3W
- LFE**
- PF2D
- IF