

Steam Valve: 2 Port Valve For Steam

VND Series

How to Order

Air operated

Body option

Nil	Standard (Copper alloy)
S*	Stainless steel body

* Threaded type only

Thread type

Nil	Rc
F	G
N	NPT
T	NPTF

VND 2 0 **D** **S** - **15A** -

Valve size

Symbol	Orifice dia. (mm)	Symbol		
		0	2	4
		N.C.	N.O.	N.C.
1	ø7	—	●	●
		—	●	●
2	ø15	—	●	●
		●	●	—
3	ø20	●	●	—
		●	●	—
4	ø25	●	●	—
		●	●	—
5	ø32	●	●	—
		●	●	—
6	ø40	●	●	—
		●	●	—
7	ø50	●	●	—
		●	●	—

Valve type

Symbol	Port size Rc
6A	1/8
8A	1/4
10A	3/8
10A	3/8
15A	1/2
20A	3/4
25A	1
32A	1 1/4
32F	1/4 B Flange
40A	1 1/2
40F	1/2 B Flange
50A	2
50F	2B Flange

Port size

Option

Nil	None
B*	With bracket
L	With indicator (visual verification of operation)
BL*	With bracket and indicator (visual verification of operation)

* Brackets (for valve size 1/2/3/4 only) will be assembled at the time of shipment. Bracket part no. Valve size 1: VN1-A16 (with thread) Valve size 2 to 4: VNC□-16