


DL

DOUBLE OFFSET WRENCH 45° Type

► Features

- The offset angle of 45° prevents collision with surrounding materials.
- Lightweight design and strength for loads surpassing the JIS standard.
- 12 points for all sizes.



Item No.	Size name (mm)	Size (mm)					N.W. (g)
		L	D	D1	T	T1	
DL89	8×9	173	14.5	13	6	5.5	50
DL810	8×10	173	16.5	13	6.5	5.5	55
DL1012	10×12	198	19.5	16.5	7.5	6.5	75
DL1013	10×13	198	21	16.5	8	6.5	90
DL1113	11×13	200	21	18	8	7	95
DL1214	12×14	221	22.5	19.5	8.5	7.5	110
DL1317	13×17	250	27	21	9.5	8	150
DL1417	14×17	250	27	22.5	9.5	8	155
DL1719	17×19	283	30	27	10	9.5	230
DL1721	17×21	300	31.5	26	11	10	270
DL1921	19×21	301	32	29	11	10	285
DL1922	19×22	302	33	29	11	10	285
DL1924	19×24	314	37	29	12.5	10.5	335
DL2126	21×26	346	37.5	32	13	11.5	430
DL2224	22×24	316	36	33	12	11	335
DL2427	24×27	348	39	36	13.5	13	460
DL2430	24×30	388	46.5	37.5	14	12.5	605
DL2632	26×32	395	49.5	40	15	13.5	690
DL2730	27×30	388	46.5	40	14	13.5	620
DL2732	27×32	395	49.5	40	15	13.5	690
DL2932	29×32	397	49.5	46.5	15	14	700
DL3032	30×32	397	49.5	46.5	15	14	700
DL3036	30×36	431	55	46.5	16	14	880
DL3235	32×35	431	55	49.5	16	15	850
DL3236	32×36	431	55	49.5	16	15	850
DL3641	36×41	458	63	55	18.5	16	1,250
DL4146	41×46	492	70.5	63	20.5	18.5	1,440



S4506N

DOUBLE OFFSET WRENCH 45° Type 6PCS-SET

► Features

- Frequently used 11 sizes.
- Aluminum case as standard acc.
- Mirror design.
- Nickel chrome plate finish.

Item No.	Set details	Set Q'ty(pcs)	Set N.W.(g)
S4506N	8×10·11×13·12×14·17×19·19×22·24×27	6	1,750

- Tool sets / cases
- Socket wrenches
- Ratchet wrenches
- Offset wrenches, grips
- Gear wrenches, open-end spanners
- Spanners
- Safety ropes
- Combination hammer
- Sockets
- Hex key wrenches
- Adjustable angle wrenches
- Pliers
- Hook spanners, pin spanners
- Toggle clamps
- C clamps
- L clamps
- Super setters
- Grip pliers
- Welding tools
- Iron man