

Color Type

G S		B S		B X		B B	
							
Panel	Silver	Panel	Silver	Panel	Silver	Panel	Black
Frame	Silver	Frame	Silver	Frame	Black	Frame	Black
Corner	Light gray	Corner	Black	Corner	Black	Corner	Black

Product no. / Dimensions

■ Please suffix color code at the end of the product number.

Product no.	H	W	D	Weight (kg)	Panel mount screw pcs
FC4- 9- 9□□	37.9	90	90	0.17	4
FC4-14- 9□□	37.9	140	90	0.24	4
FC4-14-14□□	37.9	140	140	0.33	4
FC4-19- 9□□	37.9	190	90	0.31	4
FC4-19-14□□	37.9	190	140	0.50	4
FC4-19-19□□	37.9	190	190	0.53	4
FC4-24-14□□	37.9	240	140	0.51	4
FC4-24-19□□	37.9	240	190	0.64	4
FC4-24-24□□	37.9	240	240	0.78	4
FC4-29-14□□	37.9	290	140	0.60	4
FC4-29-19□□	37.9	290	190	0.75	4
FC4-29-24□□	37.9	290	240	0.91	4
FC4-29-29□□	37.9	290	290	1.07	4
FC4-34-19□□	37.9	340	190	0.87	4
FC4-34-24□□	37.9	340	240	1.04	4
FC4-34-29□□	37.9	340	290	0.94	4
FC4-39-19□□	37.9	390	190	0.97	6
FC4-39-24□□	37.9	390	240	1.17	6
FC4-39-29□□	37.9	390	290	1.37	6
FC4-39-39□□	37.9	390	390	1.77	8
FC4-49-24□□	37.9	490	240	1.39	6
FC4-49-29□□	37.9	490	290	1.64	6
FC4-49-39□□	37.9	490	390	2.12	8
FC4-59-29□□	37.9	590	290	1.92	6
FC4-59-39□□	37.9	590	390	2.46	8
FC5-10-10□□	50.4	100	100	0.24	4
FC5-15-10□□	50.4	150	100	0.33	4
FC5-15-15□□	50.4	150	150	0.44	4
FC5-20-10□□	50.4	200	100	0.42	4
FC5-20-15□□	50.4	200	150	0.55	4
FC5-20-20□□	50.4	200	200	0.68	4
FC5-25-15□□	50.4	250	150	0.66	4
FC5-25-20□□	50.4	250	200	0.81	4
FC5-25-25□□	50.4	250	250	0.97	4
FC5-30-15□□	50.4	300	150	0.77	4
FC5-30-20□□	50.4	300	200	0.94	4
FC5-30-25□□	50.4	300	250	1.11	4
FC5-30-30□□	50.4	300	300	1.29	4
FC5-35-20□□	50.4	350	200	1.07	4
FC5-35-25□□	50.4	350	250	1.26	4
FC5-35-30□□	50.4	350	300	1.46	4
FC5-40-20□□	50.4	400	200	1.20	6
FC5-40-25□□	50.4	400	250	1.42	6
FC5-40-30□□	50.4	400	300	1.64	6

Product no.	H	W	D	Weight (kg)	Panel mount screw pcs
FC5-40-40□□	50.4	400	400	2.07	8
FC5-50-25□□	50.4	500	250	1.66	6
FC5-50-30□□	50.4	500	300	1.92	6
FC5-50-40□□	50.4	500	400	2.44	8
FC5-60-30□□	50.4	600	300	2.22	6
FC5-60-40□□	50.4	600	400	2.81	8
FC6-10-10□□	62.9	100	100	0.26	4
FC6-15-10□□	62.9	150	100	0.35	4
FC6-15-15□□	62.9	150	150	0.47	4
FC6-20-10□□	62.9	200	100	0.45	4
FC6-20-15□□	62.9	200	150	0.58	4
FC6-20-20□□	62.9	200	200	0.72	4
FC6-25-15□□	62.9	250	150	0.70	4
FC6-25-20□□	62.9	250	200	0.85	4
FC6-25-25□□	62.9	250	250	1.01	4
FC6-30-15□□	62.9	300	150	0.81	4
FC6-30-20□□	62.9	300	200	0.99	4
FC6-30-25□□	62.9	300	250	1.16	4
FC6-30-30□□	62.9	300	300	1.35	4
FC6-35-20□□	62.9	350	200	1.12	4
FC6-35-25□□	62.9	350	250	1.32	4
FC6-35-30□□	62.9	350	300	1.52	4
FC6-40-20□□	62.9	400	200	1.25	6
FC6-40-25□□	62.9	400	250	1.47	6
FC6-40-30□□	62.9	400	300	1.70	6
FC6-40-40□□	62.9	400	400	2.15	8
FC6-50-25□□	62.9	500	250	1.72	6
FC6-50-30□□	62.9	500	300	1.99	6
FC6-50-40□□	62.9	500	400	2.52	8
FC6-60-30□□	62.9	600	300	2.29	6
FC6-60-40□□	62.9	600	400	2.43	8
FC8-10-10□□	75.4	100	100	0.28	4
FC8-15-10□□	75.4	150	100	0.38	4
FC8-15-15□□	75.4	150	150	0.50	4
FC8-20-10□□	75.4	200	100	0.48	4
FC8-20-15□□	75.4	200	150	0.62	4
FC8-20-20□□	75.4	200	200	0.76	4
FC8-25-15□□	75.4	250	150	0.74	4
FC8-25-20□□	75.4	250	200	0.90	4
FC8-25-25□□	75.4	250	250	1.07	4
FC8-30-15□□	75.4	300	150	0.86	4
FC8-30-20□□	75.4	300	200	1.04	4
FC8-30-25□□	75.4	300	250	1.23	4
FC8-30-30□□	75.4	300	300	1.42	4