

Product no. / Dimensions

Product no.	H	W	D	Weight (kg)
MSY 66-16-23 □	66	160	230	1.4
MSY 66-16-28 □	66	160	280	1.6
MSY 66-21-23 □	66	210	230	1.6
MSY 66-21-28 □	66	210	280	1.9
MSY 66-21-35 □	66	210	350	2.3
MSY 66-26-23 □	66	260	230	1.9
MSY 66-26-28 □	66	260	280	2.2
MSY 66-26-35 □	66	260	350	2.7
MSY 66-32-23 □	66	320	230	2.2
MSY 66-32-28 □	66	320	280	2.6
MSY 66-32-35 □	66	320	350	3.1
MSY 66-32-45 □	66	320	450	3.9
MSY 66-37-23 □	66	370	230	2.5
MSY 66-37-28 □	66	370	280	2.9
MSY 66-37-35 □	66	370	350	3.5
MSY 66-37-45 □	66	370	450	4.2
MSY 66-43-23 □	66	430	230	2.8
MSY 66-43-28 □	66	430	280	3.3
MSY 66-43-35 □	66	430	350	3.9
MSY 66-43-45 □	66	430	450	4.9
MSY 88-16-23 □	88	160	230	1.5
MSY 88-16-28 □	88	160	280	1.8
MSY 88-21-23 □	88	210	230	1.8
MSY 88-21-28 □	88	210	280	2.1
MSY 88-21-35 □	88	210	350	2.5
MSY 88-26-23 □	88	260	230	2.1
MSY 88-26-28 □	88	260	280	2.4
MSY 88-26-35 □	88	260	350	2.9
MSY 88-32-23 □	88	320	230	2.4
MSY 88-32-28 □	88	320	280	2.8
MSY 88-32-35 □	88	320	350	3.4
MSY 88-32-45 □	88	320	450	4.2
MSY 88-37-23 □	88	370	230	2.7
MSY 88-37-28 □	88	370	280	3.1
MSY 88-37-35 □	88	370	350	3.7
MSY 88-37-45 □	88	370	450	4.5
MSY 88-43-23 □	88	430	230	3.0
MSY 88-43-28 □	88	430	280	3.5
MSY 88-43-35 □	88	430	350	4.2
MSY 88-43-45 □	88	430	450	5.2

Product no.	H	W	D	Weight (kg)
MSY 99-16-23 □	99	160	230	1.6
MSY 99-16-28 □	99	160	280	1.8
MSY 99-21-23 □	99	210	230	1.8
MSY 99-21-28 □	99	210	280	2.1
MSY 99-21-35 □	99	210	350	2.6
MSY 99-26-23 □	99	260	230	2.2
MSY 99-26-28 □	99	260	280	2.5
MSY 99-26-35 □	99	260	350	3.0
MSY 99-32-23 □	99	320	230	2.5
MSY 99-32-28 □	99	320	280	2.9
MSY 99-32-35 □	99	320	350	3.5
MSY 99-32-45 □	99	320	450	4.3
MSY 99-37-23 □	99	370	230	2.7
MSY 99-37-28 □	99	370	280	3.2
MSY 99-37-35 □	99	370	350	3.8
MSY 99-37-45 □	99	370	450	4.6
MSY 99-43-23 □	99	430	230	3.1
MSY 99-43-28 □	99	430	280	3.6
MSY 99-43-35 □	99	430	350	4.3
MSY 99-43-45 □	99	430	450	5.3
MSY133-16-23 □	133	160	230	1.8
MSY133-16-28 □	133	160	280	2.1
MSY133-21-23 □	133	210	230	2.1
MSY133-21-28 □	133	210	280	2.4
MSY133-21-35 □	133	210	350	2.9
MSY133-26-23 □	133	260	230	2.4
MSY133-26-28 □	133	260	280	2.8
MSY133-26-35 □	133	260	350	3.3
MSY133-32-23 □	133	320	230	2.7
MSY133-32-28 □	133	320	280	3.2
MSY133-32-35 □	133	320	350	3.8
MSY133-32-45 □	133	320	450	4.6
MSY133-37-23 □	133	370	230	3.0
MSY133-37-28 □	133	370	280	3.5
MSY133-37-35 □	133	370	350	4.2
MSY133-37-45 □	133	370	450	5.0
MSY133-43-23 □	133	430	230	3.4
MSY133-43-28 □	133	430	280	3.9
MSY133-43-35 □	133	430	350	4.7
MSY133-43-45 □	133	430	450	5.8