

Product no. / Dimensions

Product no.	H	W	D	Weight (kg)
MOY 66-16-23 □	66	160	230	1.0
MOY 66-16-28 □	66	160	280	1.1
MOY 66-21-23 □	66	210	230	1.2
MOY 66-21-28 □	66	210	280	1.3
MOY 66-21-35 □	66	210	350	1.6
MOY 66-26-23 □	66	260	230	1.3
MOY 66-26-28 □	66	260	280	1.5
MOY 66-26-35 □	66	260	350	1.8
MOY 66-32-23 □	66	320	230	1.5
MOY 66-32-28 □	66	320	280	1.7
MOY 66-32-35 □	66	320	350	2.0
MOY 66-32-45 □	66	320	450	2.4
MOY 66-37-23 □	66	370	230	1.7
MOY 66-37-28 □	66	370	280	1.9
MOY 66-37-35 □	66	370	350	2.2
MOY 66-37-45 □	66	370	450	2.6
MOY 66-43-23 □	66	430	230	1.9
MOY 66-43-28 □	66	430	280	2.1
MOY 66-43-35 □	66	430	350	2.5
MOY 66-43-45 □	66	430	450	3.0
MOY 88-16-23 □	88	160	230	1.1
MOY 88-16-28 □	88	160	280	1.3
MOY 88-21-23 □	88	210	230	1.3
MOY 88-21-28 □	88	210	280	1.5
MOY 88-21-35 □	88	210	350	1.8
MOY 88-26-23 □	88	260	230	1.5
MOY 88-26-28 □	88	260	280	1.7
MOY 88-26-35 □	88	260	350	2.0
MOY 88-32-23 □	88	320	230	1.7
MOY 88-32-28 □	88	320	280	1.9
MOY 88-32-35 □	88	320	350	2.3
MOY 88-32-45 □	88	320	450	2.7
MOY 88-37-23 □	88	370	230	1.9
MOY 88-37-28 □	88	370	280	2.1
MOY 88-37-35 □	88	370	350	2.5
MOY 88-37-45 □	88	370	450	2.9
MOY 88-43-23 □	88	430	230	2.1
MOY 88-43-28 □	88	430	280	2.3
MOY 88-43-35 □	88	430	350	2.7
MOY 88-43-45 □	88	430	450	3.3

Product no.	H	W	D	Weight (kg)
MOY 99-16-23 □	99	160	230	1.2
MOY 99-16-28 □	99	160	280	1.4
MOY 99-21-23 □	99	210	230	1.4
MOY 99-21-28 □	99	210	280	1.6
MOY 99-21-35 □	99	210	350	1.8
MOY 99-26-23 □	99	260	230	1.6
MOY 99-26-28 □	99	260	280	1.8
MOY 99-26-35 □	99	260	350	2.1
MOY 99-32-23 □	99	320	230	1.8
MOY 99-32-28 □	99	320	280	2.0
MOY 99-32-35 □	99	320	350	2.4
MOY 99-32-45 □	99	320	450	2.8
MOY 99-37-23 □	99	370	230	2.0
MOY 99-37-28 □	99	370	280	2.2
MOY 99-37-35 □	99	370	350	2.6
MOY 99-37-45 □	99	370	450	3.0
MOY 99-43-23 □	99	430	230	2.2
MOY 99-43-28 □	99	430	280	2.4
MOY 99-43-35 □	99	430	350	2.8
MOY 99-43-45 □	99	430	450	3.4
MOY133-16-23 □	132.5	160	230	1.4
MOY133-16-28 □	132.5	160	280	1.6
MOY133-21-23 □	132.5	210	230	1.6
MOY133-21-28 □	132.5	210	280	1.8
MOY133-21-35 □	132.5	210	350	2.1
MOY133-26-23 □	132.5	260	230	1.8
MOY133-26-28 □	132.5	260	280	2.1
MOY133-26-35 □	132.5	260	350	2.4
MOY133-32-23 □	132.5	320	230	2.0
MOY133-32-28 □	132.5	320	280	2.3
MOY133-32-35 □	132.5	320	350	2.7
MOY133-32-45 □	132.5	320	450	3.2
MOY133-37-23 □	132.5	370	230	2.2
MOY133-37-28 □	132.5	370	280	2.5
MOY133-37-35 □	132.5	370	350	2.9
MOY133-37-45 □	132.5	370	450	3.4
MOY133-43-23 □	132.5	430	230	2.5
MOY133-43-28 □	132.5	430	280	2.8
MOY133-43-35 □	132.5	430	350	3.2
MOY133-43-45 □	132.5	430	450	3.8