

Components

■ Refer to page 250 for more information on rack mounting bracket.

No.	Part name	Pcs	Material	Color / Finish
1	Front panel	1	Aluminium A1050P t=2.0	Silver • Black / Hairline brushed & Anodized
-	Rear panel	1	Aluminium A1050P t=2.0	Silver • Black / Anodized
3	Side frame	2	Extruded aluminium A6063S-T5	Gray • Black / Painted
4	Front frame	2	Extruded aluminium A6063S-T5	Gray • Black / Painted
-	Rear frame	2	Extruded aluminium A6063S-T5	Silver / Anodized
6	Top cover	1	Steel SPCC t=1.0	Light gray • Black / Painted
7	Bottom cover	1	Steel SPCC t=1.0	Light gray • Black / Painted
8	Corner block	2	Diecast aluminium ADC12	Gray • Black / Painted
9	Rear feet	2	ABS UL94V-0	Gray • Black
10	Rubber feet	4	Polyurethane	Black
11	Rack mounting bracket	2	Extruded aluminium A6063S-T5	Gray • Black painted

■ Note: Front / rear panels are covered with a protective film on one side. Remove before assembly.

Included screws and nuts
 M4-6 countersunk • Trivalent chromate x 4 pcs
 M4-8 Pan head • Trivalent chromate x 8 pcs
 M4-10 Binding head • Black trivalent chromate x 4 pcs
 M5-10 Flat head • Black trivalent chromate x 4 pcs
 M5 Nut (Product no. MZ-5) x 4 pcs

Accessories (Optional parts)



Mounting plate MSC series
See page MSC • MSC-L1



L-bracket MSCL series
See page MSC • MSCL-1



Aluminium handle OH series
See page OH • KH-1



Cable hook CBF series
See page TL • CBF-1

Color Type

■ Please suffix color code at the end of the product number.

● G		● B		● BS	
Panel	Silver	Panel	Black	Panel	Silver
Top • Bottom cover	Light gray	Top • Bottom cover	Black	Top • Bottom cover	Black
Side frame	Gray	Side frame	Black	Side frame	Black

Product no. / Dimensions

Product no.	H	W	D	Weight (kg)
MSR 88-43-23 □	88	430	230	3.1
MSR 88-43-28 □	88	430	280	3.5
MSR 88-43-35 □	88	430	350	4.2
MSR 88-43-45 □	88	430	450	5.1
MSR133-43-23 □	132.5	430	230	3.6
MSR133-43-28 □	132.5	430	280	4.1
MSR133-43-35 □	132.5	430	350	4.8
MSR133-43-45 □	132.5	430	450	5.8
MSR177-43-23 □	177	430	230	4.3
MSR177-43-28 □	177	430	280	4.9
MSR177-43-35 □	177	430	350	5.7
MSR177-43-45 □	177	430	450	6.9
MSR222-43-23 □	221.5	430	230	4.7
MSR222-43-28 □	221.5	430	280	5.3
MSR222-43-35 □	221.5	430	350	6.2
MSR222-43-45 □	221.5	430	450	7.5