

Product no. / Dimensions

Product no.	H	W	D	Weight (kg)
MON 66-16-16 □	66	160	160	0.9
MON 66-16-23 □	66	160	230	1.1
MON 66-16-28 □	66	160	280	1.3
MON 66-21-16 □	66	210	160	1.1
MON 66-21-23 □	66	210	230	1.3
MON 66-21-28 □	66	210	280	1.5
MON 66-21-35 □	66	210	350	1.7
MON 66-26-23 □	66	260	230	1.5
MON 66-26-28 □	66	260	280	1.7
MON 66-26-35 □	66	260	350	2.0
MON 66-32-23 □	66	320	230	1.7
MON 66-32-28 □	66	320	280	1.9
MON 66-32-35 □	66	320	350	2.2
MON 66-32-45 □	66	320	450	2.6
MON 66-37-23 □	66	370	230	1.9
MON 66-37-28 □	66	370	280	2.1
MON 66-37-35 □	66	370	350	2.4
MON 66-37-45 □	66	370	450	2.8
MON 66-43-23 □	66	430	230	2.1
MON 66-43-28 □	66	430	280	2.4
MON 66-43-35 □	66	430	350	2.7
MON 66-43-45 □	66	430	450	3.2
MON 88-16-16 □	88	160	160	1.0
MON 88-16-23 □	88	160	230	1.3
MON 88-16-28 □	88	160	280	1.5
MON 88-21-16 □	88	210	160	1.2
MON 88-21-23 □	88	210	230	1.5
MON 88-21-28 □	88	210	280	1.7
MON 88-21-35 □	88	210	350	1.9
MON 88-26-23 □	88	260	230	1.7
MON 88-26-28 □	88	260	280	1.9
MON 88-26-35 □	88	260	350	2.2
MON 88-32-23 □	88	320	230	1.9
MON 88-32-28 □	88	320	280	2.1
MON 88-32-35 □	88	320	350	2.5
MON 88-32-45 □	88	320	450	2.9
MON 88-37-23 □	88	370	230	2.1
MON 88-37-28 □	88	370	280	2.3
MON 88-37-35 □	88	370	350	2.7
MON 88-37-45 □	88	370	450	3.1
MON 88-43-23 □	88	430	230	2.3
MON 88-43-28 □	88	430	280	2.6
MON 88-43-35 □	88	430	350	3.0
MON 88-43-45 □	88	430	450	3.5

Product no.	H	W	D	Weight (kg)
MON 99-16-16 □	99	160	160	1.1
MON 99-16-23 □	99	160	230	1.3
MON 99-16-28 □	99	160	280	1.5
MON 99-21-16 □	99	210	160	1.3
MON 99-21-23 □	99	210	230	1.5
MON 99-21-28 □	99	210	280	1.7
MON 99-21-35 □	99	210	350	2.0
MON 99-26-23 □	99	260	230	1.7
MON 99-26-28 □	99	260	280	2.0
MON 99-26-35 □	99	260	350	2.3
MON 99-32-23 □	99	320	230	2.0
MON 99-32-28 □	99	320	280	2.2
MON 99-32-35 □	99	320	350	2.6
MON 99-32-45 □	99	320	450	3.0
MON 99-37-23 □	99	370	230	2.1
MON 99-37-28 □	99	370	280	2.4
MON 99-37-35 □	99	370	350	2.8
MON 99-37-45 □	99	370	450	3.2
MON 99-43-23 □	99	430	230	2.4
MON 99-43-28 □	99	430	280	2.7
MON 99-43-35 □	99	430	350	3.1
MON 99-43-45 □	99	430	450	3.7
MON133-16-16 □	132.5	160	160	1.3
MON133-16-23 □	132.5	160	230	1.6
MON133-16-28 □	132.5	160	280	1.8
MON133-21-16 □	132.5	210	160	1.5
MON133-21-23 □	132.5	210	230	1.8
MON133-21-28 □	132.5	210	280	2.0
MON133-21-35 □	132.5	210	350	2.3
MON133-26-23 □	132.5	260	230	2.0
MON133-26-28 □	132.5	260	280	2.3
MON133-26-35 □	132.5	260	350	2.6
MON133-32-23 □	132.5	320	230	2.3
MON133-32-28 □	132.5	320	280	2.5
MON133-32-35 □	132.5	320	350	2.9
MON133-32-45 □	132.5	320	450	3.4
MON133-37-23 □	132.5	370	230	2.5
MON133-37-28 □	132.5	370	280	2.8
MON133-37-35 □	132.5	370	350	3.2
MON133-37-45 □	132.5	370	450	3.6
MON133-43-23 □	132.5	430	230	2.7
MON133-43-28 □	132.5	430	280	3.0
MON133-43-35 □	132.5	430	350	3.5
MON133-43-45 □	132.5	430	450	4.1