

Product no. / Dimensions

Product no.	H	W	D	Weight (kg)
MSN 66-16-16 □	66	160	160	1.2
MSN 66-16-23 □	66	160	230	1.5
MSN 66-16-28 □	66	160	280	1.8
MSN 66-21-16 □	66	210	160	1.4
MSN 66-21-23 □	66	210	230	1.8
MSN 66-21-28 □	66	210	280	2.1
MSN 66-21-35 □	66	210	350	2.5
MSN 66-26-23 □	66	260	230	2.1
MSN 66-26-28 □	66	260	280	2.4
MSN 66-26-35 □	66	260	350	2.9
MSN 66-32-23 □	66	320	230	2.4
MSN 66-32-28 □	66	320	280	2.8
MSN 66-32-35 □	66	320	350	3.4
MSN 66-32-45 □	66	320	450	4.1
MSN 66-37-23 □	66	370	230	2.6
MSN 66-37-28 □	66	370	280	3.1
MSN 66-37-35 □	66	370	350	3.7
MSN 66-37-45 □	66	370	450	4.4
MSN 66-43-23 □	66	430	230	3.0
MSN 66-43-28 □	66	430	280	3.5
MSN 66-43-35 □	66	430	350	4.2
MSN 66-43-45 □	66	430	450	5.2
MSN 88-16-16 □	88	160	160	1.3
MSN 88-16-23 □	88	160	230	1.6
MSN 88-16-28 □	88	160	280	1.9
MSN 88-21-16 □	88	210	160	1.5
MSN 88-21-23 □	88	210	230	1.9
MSN 88-21-28 □	88	210	280	2.3
MSN 88-21-35 □	88	210	350	2.7
MSN 88-26-23 □	88	260	230	2.3
MSN 88-26-28 □	88	260	280	2.6
MSN 88-26-35 □	88	260	350	3.1
MSN 88-32-23 □	88	320	230	2.6
MSN 88-32-28 □	88	320	280	3.0
MSN 88-32-35 □	88	320	350	3.6
MSN 88-32-45 □	88	320	450	4.4
MSN 88-37-23 □	88	370	230	2.9
MSN 88-37-28 □	88	370	280	3.3
MSN 88-37-35 □	88	370	350	4.0
MSN 88-37-45 □	88	370	450	4.7
MSN 88-43-23 □	88	430	230	3.2
MSN 88-43-28 □	88	430	280	3.7
MSN 88-43-35 □	88	430	350	4.4
MSN 88-43-45 □	88	430	450	5.5

Product no.	H	W	D	Weight (kg)
MSN 99-16-16 □	99	160	160	1.3
MSN 99-16-23 □	99	160	230	1.7
MSN 99-16-28 □	99	160	280	2.0
MSN 99-21-16 □	99	210	160	1.6
MSN 99-21-23 □	99	210	230	2.0
MSN 99-21-28 □	99	210	280	2.3
MSN 99-21-35 □	99	210	350	2.8
MSN 99-26-23 □	99	260	230	2.3
MSN 99-26-28 □	99	260	280	2.7
MSN 99-26-35 □	99	260	350	3.2
MSN 99-32-23 □	99	320	230	2.6
MSN 99-32-28 □	99	320	280	3.1
MSN 99-32-35 □	99	320	350	3.7
MSN 99-32-45 □	99	320	450	4.5
MSN 99-37-23 □	99	370	230	2.9
MSN 99-37-28 □	99	370	280	3.4
MSN 99-37-35 □	99	370	350	4.1
MSN 99-37-45 □	99	370	450	4.8
MSN 99-43-23 □	99	430	230	3.3
MSN 99-43-28 □	99	430	280	3.8
MSN 99-43-35 □	99	430	350	4.5
MSN 99-43-45 □	99	430	450	5.6
MSN133-16-16 □	133	160	160	1.5
MSN133-16-23 □	133	160	230	1.9
MSN133-16-28 □	133	160	280	2.2
MSN133-21-16 □	133	210	160	1.8
MSN133-21-23 □	133	210	230	2.3
MSN133-21-28 □	133	210	280	2.6
MSN133-21-35 □	133	210	350	3.1
MSN133-26-23 □	133	260	230	2.6
MSN133-26-28 □	133	260	280	3.0
MSN133-26-35 □	133	260	350	3.5
MSN133-32-23 □	133	320	230	2.9
MSN133-32-28 □	133	320	280	3.4
MSN133-32-35 □	133	320	350	4.0
MSN133-32-45 □	133	320	450	4.9
MSN133-37-23 □	133	370	230	3.3
MSN133-37-28 □	133	370	280	3.8
MSN133-37-35 □	133	370	350	4.4
MSN133-37-45 □	133	370	450	5.2
MSN133-43-23 □	133	430	230	3.7
MSN133-43-28 □	133	430	280	4.2
MSN133-43-35 □	133	430	350	4.9
MSN133-43-45 □	133	430	450	6.0