

TRUSCO Stock 38,650 Items


Reamer Punch



- Features**
- Temporarily tighten the holes of the iron plate that is aligned with the drift punch and use it when taking out an angle or undergoing an inspection.
- Specs**
- Hardening Penetration: HRC40
- Materials**
- Carbon Steel
- Origin**
- Japan



TRMP Type



Item No.	L1 (mm)	L2 (mm)
TRMP-17.5	90	20
TRMP-20.5	100	25
TRMP-21.5	100	25
TRMP-22.5	100	25
TRMP-23.5	100	25
TRMP-24.5	100	25
TRMP-26.5	130	25

Order Unit: 1 Piece

(Price revision date: Jan, 2016) TRUSCO NAKAYAMA CORPORATION

Order Code	Item No.	Price (per piece)	MSRP (per piece)	Total Length (mm)	Tip Diameter (mm)	Max Diameter (mm)	SPQ (piece)	Weight (g)
229-5148	TRMP-17.5	¥1,602	¥1,730	130	12	17.5	10	240
229-5156	TRMP-20.5	¥1,796	¥1,940	150	14	20.5	10	360
229-5164	TRMP-21.5	¥1,796	¥1,940	150	15	21.5	10	420
229-5172	TRMP-22.5	¥1,981	¥2,140	150	16	22.5	10	450
229-5181	TRMP-23.5	¥1,981	¥2,140	150	18	23.5	10	500
229-5199	TRMP-24.5	¥1,981	¥2,140	150	19	24.5	10	540
229-5202	TRMP-26.5	¥2,981	¥3,220	180	21	26.5	5	730

Contact us: 0120-509-849 <http://www.orange-book.com/>

TONE Stock 2,937 Items

Pin Punch

- Features**
- Most suitable for removing parallel pin, spring pin and tapered pin.
 - An easy-to-grasp concavo-convex shaped grip.
 - Hexagonal shape which does not roll easily.
- Materials**
- Structural Steel
- Origin**
- Japan



PP-04



PP300 (set)

PP800 (set)

Order Unit: 1 Piece

Order Code	Item No.	Price (per piece)	MSRP (per piece)	Total Length (mm)	Width (mm)	Tip Diameter (mm)	SPQ (piece)	Weight (g)
498-1511	PP-02	¥764	¥950	140	8	2.0	10	44
498-1529	PP-03	¥764	¥950	140	8	3.0	10	42
498-1537	PP-04	¥764	¥950	150	8	4.0	10	45
498-1596	PP-4.5	¥764	¥950	150	8	4.5	10	46
498-1545	PP-05	¥764	¥950	150	8	5.0	10	48
498-1553	PP-06	¥802	¥1,000	160	8	6.0	10	55
498-1561	PP-07	¥802	¥1,000	160	8	7.0	10	59
498-1570	PP-08	¥802	¥1,000	160	8	8.0	10	65

Set

Order Unit: 1 Set

Order Code	Item No.	Price (per set)	MSRP (per set)	Set Contents (mm)	Set Contents (piece)	SPQ (set)	Weight (g/set)
498-1588	PP300	¥2,283	¥2,850	4.0, 4.5, 5.0	3	5	160
498-1600	PP800	¥6,218	¥7,750	2.0, 3.0, 4.0, 4.5, 5.0, 6.0, 7.0, 8.0	8	3	470

Contact us: 0721-56-1850 <http://www.tonetool.co.jp/>


KYOTO TOOL KTC Stock 2,641 Items

Knock Pin Punch

- Features**
- New design differing from existing knock pin punch.
 - Body is hexagonal shaped which does not roll easily.
 - Also, chucking rubber is effective for increasing usability.
- Origin**
- Japan

Warning

- Please wear safety glasses when working.
- Please use an appropriately sized product.
- Please set the chucking rubber unfliningly.



PK-4185



PK8 (set)

Order Unit: 1 Piece

Order Code	Item No.	Price (per piece)	MSRP (per piece)	Total Length (mm)	Width (mm)	Tip Diameter (mm)	SPQ (piece)	Weight (g)
373-7161	PK-2125	¥1,555	¥1,680	125	8	1.8	10	46
373-7187	PK-3135	¥1,555	¥1,680	135	8	2.8	10	46
373-7195	PK-4185	¥1,555	¥1,680	185	10	3.8	10	98
373-7209	PK-45185	¥1,555	¥1,680	185	10	4.3	10	100
373-7217	PK-5190	¥1,555	¥1,680	191	10	4.8	10	100
373-7225	PK-6207	¥2,019	¥2,180	207	12	5.8	10	150
373-7233	PK-7212	¥2,019	¥2,180	212	12	6.8	10	160
373-7250	PK-8217	¥2,019	¥2,180	217	12	7.8	10	170

Set

Features • Convenient set gathering major sizes into one.

Order Unit: 1 Set

Order Code	Item No.	Price (per set)	MSRP (per set)	Set Contents	Set Contents (piece)	SPQ (set)	Weight (g/set)
373-7179	PK3	¥4,666	¥5,040	PK-4185, 45185, 5190	3	10	300
373-7241	PK8	¥13,793	¥14,900	PK-2125, 3135, 4185, 45185, 5190, 6207, 7212, 8217	8	5	960

URL <http://ktc.jp/>