

Prices displayed include 8% tax.

For Batteries, see p. 10-461 to 474



Stock 195 Items

Electroscope "Super Next 3E Checker" (for both alternating/direct current)



- Features**
- Electronic sounds and lights aid in identifying in this electroscope.
 - Divided power detection (100/200V differentiation), coating/bare wire power detection, direct power detection, continuity and polarity check can be performed.
 - Sensitivity can be adjusted.
- Specs**
- W x D x H: 22 x 21 x 132mm
 - Power Supply: Button Type Alkaline Battery (LR44) x 2 (accessory)
- Origin**
- Japan

Order Unit: 1 Piece

JEFCON

| Order Code | Item No. | Price (per piece) | MSRP (per piece) | DC Voltage (V) | AC Voltage (V) | SPQ (piece) | Weight (g) |
|------------|----------|-------------------|------------------|----------------|----------------|-------------|------------|
| 858-6313 | SEC-920 | ¥6,091 | ¥6,580 | 1.2 to 24 | 80 to 300 | 1 | 29 |

Contact us: 072-986-5900 <http://www.jefcon.co.jp/>



Stock 195 Items

Electroscope "Super Next 3E Checker" (for both alternating/direct current)



- Features**
- Divided power detection (100/200V), coating power detection, direct power detection and polarity check can be performed.
- Specs**
- W x D x H: 25 x 22 x 132mm
 - Power Supply: Lithium Coin Cell Battery (CR2032) x 1 (accessory)
 - Alternating current voltage: Direct power detection AC100V ground voltage AC80 to 120V, direct power detection AC200V ground voltage AC160 to 300V, coating power detection AC80 to 300V
- Origin**
- Japan

Order Unit: 1 Piece

JEFCON

| Order Code | Item No. | Price (per piece) | MSRP (per piece) | DC Voltage (V) | AC Voltage (V) | SPQ (piece) | Weight (g) |
|------------|----------|-------------------|------------------|----------------|----------------|-------------|------------|
| 419-5680 | SEC-902B | ¥5,536 | ¥5,980 | 1.2~24 | 80~300 | 1 | 33 |

Contact us: 072-986-5900 <http://www.jefcon.co.jp/>



Stock 195 Items

Electroscope "Ultra 4E Checker" (for both alternating/direct current)



- Features**
- This electroscope can also detect metal.
 - Divided power detection (100/200V), coating power detection, direct power detection and polarity check can be performed.
- Specs**
- W x D x H: 33 x 23 x 140mm
 - Power supply: Lithium ion coin cell battery (CR2032) x 1 (included)
 - Alternating current voltage: Direct power detection AC100V ground voltage AC80 to 120V, direct power detection AC200V ground voltage AC160 to 300V, coating power detection AC80 to 300V
- Origin**
- Japan

Order Unit: 1 Piece

JEFCON

| Order Code | Item No. | Price (per piece) | MSRP (per piece) | DC Voltage (V) | AC Voltage (V) | SPQ (piece) | Weight (g) |
|------------|----------|-------------------|------------------|----------------|----------------|-------------|------------|
| 419-5698 | SEC-903B | ¥9,238 | ¥9,980 | 0.8 to 24 | 80 to 300 | 1 | 47 |

Contact us: 072-986-5900 <http://www.jefcon.co.jp/>



Stock 298 Items

Electroscope (for both alternating/direct current)



- Features**
- All in one model that this instrument can detect contact type AC and DC and non-contact type AC by itself.
 - Power detection is made reliable with LED and buzzer.
 - Convenient probe lighting function in dark place.
 - Non-contact AC detection voltage is equipped with a non-step volume sensitivity adjustment function.
 - Has a worry free self-test function.
- Specs**
- W x D x H: 17.5 x 18 x 132mm
 - Power supply: Button type battery (LR44) x 2 (sold separately)
 - Detection voltage: Contact type DC: 5 to 1000V, contact type AC: 7 to 1000V, non-contact type AC: 30 to 1000V
- Origin**
- China

Order Unit: 1 Piece

(Price revision date: Feb, 2015) CUSTOM

| Order Code | Item No. | Price (per piece) | MSRP (per piece) | DC Voltage (V) | AC Voltage (V) | SPQ (piece) | Weight (g) |
|------------|----------|-------------------|------------------|----------------|----------------|-------------|------------|
| 494-9803 | V17 | ¥3,694 | ¥3,800 | 5 to 1000 | 7 to 1000 | 1 | 24 |

Contact us: 03-3255-1117 <http://www.kk-custom.co.jp/>



Stock 38,650 Items

Electroscope (AC exclusive)



- Features**
- Ability to detect electricity from top of cord or cable insulation.
 - The buzzer and lamp notify detection status.
 - Sensitivity can be freely adjusted from low to hi.
- Specs**
- W x D x H: 31 x 26 x 145mm
 - Power supply: Button type alkaline battery (LR44) x 2 (sold separately)
- Origin**
- China

Order Unit: 1 Piece

(Price revision date: Jan, 2016) TRUSCO NAKAYAMA CORPORATION

| Order Code | Item No. | Price (per piece) | MSRP (per piece) | DC Voltage (V) | AC Voltage (V) | SPQ (piece) | Weight (g) |
|------------|----------|-------------------|------------------|----------------|----------------|-------------|------------|
| 329-5273 | TV-2001 | ¥2,414 | ¥2,980 | - | 5 to 600 | 20 | 31 |

Contact us: 0120-509-849 <http://www.orange-book.com/>

Multimeters

Crampmeters

Insulation Resistance Testers

Detectors

Phase Detectors

Cable Locators

Static Electricity Meters

Thermometers, Hygrometers

Heat Sensor/Measuring Instruments

Test Instruments for Environments

Gas Detectors

Water Measuring Instruments

Vibration Meters, Tacho Meters

Hardness Testers

Viscometers

Coating Thickness Meters, Detectors

Nondestructive Inspection Systems

Flowmeters

Pressure Gauges

Vacuum Gauges

Stopwatches, Timers

Counters

Balances

Tension Gauges

Torque Equipments