

Socket Bits (for power tools)

For Impact Screwdrivers, see p. 5-77 to 100/For Drill Screwdrivers, see p. 5-124 to 156 The number next to the logo mark indicates items in stock for each brand.



Stock
38,650
Items

Electric Screwdriver Socket




TEF-17

TEF-17-10
(10 pieces)

- Features
- Floral bore size enables highly accurate torque precision.
 - Possible to insert smoothly into the bolt nut compared to the hexagonal bore.
- Materials
- Chrome vanadium steel (SCRV4)
- Origin
- Japan

Dimensions



Order Unit: 1 Piece

(Price revision date: Jan, 2018) TRUSCO NAKAYAMA CORPORATION

Order Code	Item No.	Price (per piece)	MSRP (per piece)	Opposite Side Dimension (mm)	Shaft Dimension (mm)	Total Length (mm)	SPQ (piece)	Weight (g)
252-9114	TEF-8	¥ 870	¥ 940	8	6.35	105	6	53
252-9122	TEF-9	¥ 870	¥ 940	9	6.35	105	6	55
252-9131	TEF-10	¥ 897	¥ 970	10	6.35	105	6	61
252-9149	TEF-11	¥ 897	¥ 970	11	6.35	105	6	70
252-9157	TEF-12	¥ 897	¥ 970	12	6.35	105	6	76
252-9165	TEF-13	¥ 954	¥ 1,030	13	6.35	105	6	86
252-9173	TEF-14	¥ 972	¥ 1,050	14	6.35	105	6	92
252-9181	TEF-15	¥ 972	¥ 1,050	15	6.35	105	6	100
252-9190	TEF-16	¥ 972	¥ 1,050	16	6.35	105	6	105
252-9203	TEF-17	¥ 972	¥ 1,050	17	6.35	105	6	112
252-9211	TEF-18	¥ 1,027	¥ 1,110	18	6.35	105	6	118
252-9220	TEF-19	¥ 1,027	¥ 1,110	19	6.35	105	6	128
252-9238	TEF-21	¥ 1,120	¥ 1,210	21	6.35	105	6	144
252-9246	TEF-22	¥ 1,203	¥ 1,300	22	6.35	105	6	150
252-9254	TEF-23	¥ 1,610	¥ 1,740	23	6.35	105	6	163
252-9262	TEF-24	¥ 1,750	¥ 1,890	24	6.35	105	6	170

10 Pieces Features • Affordable with 10 pieces.

Order Unit: 1 Box

(Price revision date: Jan, 2018)

Order Code	Item No.	Price (per box)	MSRP (per box)	Opposite Side Dimension (mm)	Shaft Dimension (mm)	Total Length (mm)	SPQ (box)	Weight (g/box)
488-6755	TEF-8-10	¥ 8,387	¥ 9,060	8	6.35	105	1	530
488-6607	TEF-10-10	¥ 8,655	¥ 9,350	10	6.35	105	1	610
488-6631	TEF-13-10	¥ 9,211	¥ 9,950	13	6.35	105	1	860
488-6666	TEF-17-10	¥ 9,396	¥ 10,150	17	6.35	105	1	1120
488-6691	TEF-19-10	¥ 9,951	¥ 10,750	19	6.35	105	1	1280

Contact us:0120-509-849 <http://www.orange-book.com/>

Stock
38,650
Items

Electric Screwdriver Socket




TEF-215

TEF-17S-10
(10 pieces)

- Features
- Short type.
 - Floral bore size enables highly accurate torque precision.
 - Possible to insert smoothly into the bolt nut compared to the hexagonal bore.
- Materials
- Chrome vanadium steel (SCRV4)
- Origin
- Japan

Dimensions



Order Unit: 1 Piece

(Price revision date: Jan, 2018) TRUSCO NAKAYAMA CORPORATION

Order Code	Item No.	Price (per piece)	MSRP (per piece)	Opposite Side Dimension (mm)	Shaft Dimension (mm)	Total Length (mm)	SPQ (piece)	Weight (g)
449-8917	TEF-5.5S	¥ 454	¥ 490	5.5	6.35	65	6	27
449-8925	TEF-6S	¥ 454	¥ 490	6	6.35	65	6	27
449-8933	TEF-7S	¥ 454	¥ 490	7	6.35	65	6	29
252-9271	TEF-8S	¥ 454	¥ 490	8	6.35	75	6	35
252-9289	TEF-10S	¥ 490	¥ 530	10	6.35	75	6	40
252-9297	TEF-12S	¥ 537	¥ 580	12	6.35	75	6	51
252-9301	TEF-13S	¥ 546	¥ 590	13	6.35	75	6	58
252-9319	TEF-14S	¥ 555	¥ 600	14	6.35	75	6	63
252-9327	TEF-17S	¥ 879	¥ 950	17	6.35	75	6	76
252-9335	TEF-19S	¥ 879	¥ 950	19	6.35	75	6	85
252-9343	TEF-21S	¥ 1,027	¥ 1,110	21	6.35	75	6	95
449-8941	TEF-22S	¥ 1,194	¥ 1,290	22	6.35	75	6	99
252-9351	TEF-24S	¥ 1,583	¥ 1,710	24	6.35	75	6	110

10 Pieces Features • Affordable with 10 pieces.

Order Unit: 1 Box

(Price revision date: Jan, 2018)

Order Code	Item No.	Price (per box)	MSRP (per box)	Opposite Side Dimension (mm)	Shaft Dimension (mm)	Total Length (mm)	SPQ (box)	Weight (g/box)
488-6771	TEF-8S-10	¥ 4,378	¥ 4,730	8	6.35	75	1	350
488-6623	TEF-10S-10	¥ 4,749	¥ 5,130	10	6.35	75	1	400
488-6658	TEF-13S-10	¥ 5,249	¥ 5,670	13	6.35	75	1	580
488-6682	TEF-17S-10	¥ 8,479	¥ 9,160	17	6.35	75	1	760
488-6712	TEF-19S-10	¥ 8,479	¥ 9,160	19	6.35	75	1	850

Contact us:0120-509-849 <http://www.orange-book.com/>