

Combination Ratchet Wrenches

The number next to the logo mark indicates items in stock for each brand.

Stock
38,650
Items

Ratchet Combination Wrench



Opposite Side Dimension

Features

- Switching between normal and reverse is not attached.
- Since it is a straight shape, it is optimum for work in narrow places and deep places.
- Feed angle 5° has been realized.
- The finish side is beautiful, the touch is good and there is a heavy feeling.
- Surface treatment is trivalent chromium plating.

Materials •Chrome Vanadium Steel (Cr-V)

Origin •Taiwan

Order Unit: 1 Piece

TRUSCO NAKAYAMA CORPORATION

Order Code	Item No.	Price (per piece)	MSRP (per piece)	Opposite Side Dimension (mm)	Thickness (mm)		Total Length (mm)	SPQ (piece)	Weight (g)
					Spanner	Ring			
415-9489	TGRW-07	¥ 713	¥ 770	7	4.7	7.0	136	10	36
415-9497	TGRW-08	¥ 750	¥ 810	8	4.7	7.0	136	10	35
415-9501	TGRW-10	¥ 833	¥ 900	10	5.4	7.7	160	10	55
415-9519	TGRW-12	¥ 990	¥ 1,070	12	6.0	8.7	174	10	79
415-9527	TGRW-13	¥ 1,027	¥ 1,110	13	6.2	9.3	180	10	93
415-9535	TGRW-14	¥ 1,130	¥ 1,220	14	6.9	9.4	193	10	120
415-9543	TGRW-17	¥ 1,379	¥ 1,490	17	8.3	10.9	233	10	188
415-9551	TGRW-19	¥ 1,527	¥ 1,650	19	9.0	11.5	250	10	238

TGRW-17

Total Length

Warning

- 7, 8mm across-flat have 60 teeth.
- 10 to 19mm across-flat have 72 teeth.



TGRW-800 (when expands) (when in storage)

Set Accessories •Storage Pouch

Order Unit: 1 Set

Order Code	Item No.	Price (per set)	MSRP (per set)	Set Contents (mm)	Set Contents (piece)	SPQ (set)	Weight (g/set)
415-9560	TGRW-800	¥ 8,535	¥ 9,220	7, 8, 10, 12, 13, 14, 17, 19	8	1	1064

Contact us:0120-509-849 <http://www.orange-book.com/>Stock
38,650
Items

Ratchet Combination Wrench (short type)



Opposite Side Dimension

Features

- Switching between normal and reverse is not attached.
- Since it is a straight shape, it is optimum for work in narrow places and deep places.
- Feed angle 5° has been realized.
- The finish side is beautiful, the touch is good and there is a heavy feeling.
- Surface treatment is trivalent chromium plating.

Materials •Chrome Vanadium Steel (Cr-V)

Origin •Taiwan

Order Unit: 1 Piece

TRUSCO NAKAYAMA CORPORATION

Order Code	Item No.	Price (per piece)	MSRP (per piece)	Opposite Side Dimension (mm)	Thickness (mm)		Total Length (mm)	SPQ (piece)	Weight (g)
					Spanner	Ring			
415-9390	TGRW-07S	¥ 638	¥ 690	7	5.1	7.0	88	10	24
415-9403	TGRW-08S	¥ 685	¥ 740	8	5.1	7.0	88	10	23
415-9411	TGRW-10S	¥ 741	¥ 800	10	5.5	7.7	96	10	41
415-9420	TGRW-12S	¥ 907	¥ 980	12	6.1	8.7	104	10	56
415-9438	TGRW-13S	¥ 917	¥ 990	13	6.3	9.3	108	10	64
415-9446	TGRW-14S	¥ 1,000	¥ 1,080	14	6.7	9.4	114	10	86
415-9454	TGRW-17S	¥ 1,324	¥ 1,430	17	7.8	10.9	128	10	123
415-9462	TGRW-19S	¥ 1,444	¥ 1,560	19	8.5	11.5	138	10	154

TGRW-17S

Total Length

Warning

- 7, 8mm across-flat have 60 teeth.
- 10 to 19mm across-flat have 72 teeth.



TGRW-800S (when opening) (when in storage)

Set Accessories •Storage Pouch

Order Unit: 1 Set

Order Code	Item No.	Price (per set)	MSRP (per set)	Set Contents (mm)	Set Contents (piece)	SPQ (set)	Weight (g/set)
415-9471	TGRW-800S	¥ 7,841	¥ 8,470	7, 8, 10, 12, 13, 14, 17, 19	8	1	710

Contact us:0120-509-849 <http://www.orange-book.com/>Stock
38,650
Items

Ratchet Combination Wrench (long type)



Opposite Side Dimension

Features

- Switching between normal and reverse is not attached.
- Since it is a straight shape, it is optimum for work in narrow places and deep places.
- Feed angle 5° has been realized.
- The finish side is beautiful, the touch is good and there is a heavy feeling.
- Surface treatment is trivalent chromium plating.

Materials •Chrome Vanadium Steel (Cr-V)

Origin •Taiwan

Order Unit: 1 Piece

TRUSCO NAKAYAMA CORPORATION

Order Code	Item No.	Price (per piece)	MSRP (per piece)	Opposite Side Dimension (mm)	Thickness (mm)		Total Length (mm)	SPQ (piece)	Weight (g)
					Spanner	Ring			
415-9578	TGRW-07L	¥ 806	¥ 870	7	5.1	7.0	150	10	36
415-9586	TGRW-08L	¥ 833	¥ 900	8	5.1	7.0	150	10	35
415-9594	TGRW-10L	¥ 926	¥ 1,000	10	5.8	7.7	180	10	59
415-9608	TGRW-12L	¥ 1,092	¥ 1,180	12	6.4	8.7	207	10	82
415-9616	TGRW-13L	¥ 1,138	¥ 1,230	13	6.7	9.3	220	10	107
415-9624	TGRW-14L	¥ 1,250	¥ 1,350	14	7.4	9.4	235	10	131
415-9632	TGRW-17L	¥ 1,527	¥ 1,650	17	8.8	10.9	275	10	208
415-9641	TGRW-19L	¥ 1,695	¥ 1,830	19	9.5	11.5	305	10	260

TGRW-17L

Total Length

Warning

- 7, 8mm across-flat have 60 teeth.
- 10 to 19mm across-flat have 72 teeth.



TGRW-800L (when opening) (when in storage)

Set Accessories •Storage Pouch

Order Unit: 1 Set

Order Code	Item No.	Price (per set)	MSRP (per set)	Set Contents (mm)	Set Contents (piece)	SPQ (set)	Weight (g/set)
415-9659	TGRW-800L	¥ 9,526	¥ 10,290	7, 8, 10, 12, 13, 14, 17, 19	8	1	1158

Contact us:0120-509-849 <http://www.orange-book.com/>