

# Ball-Point Hexagonal Wrenches (stainless steel type)

The number next to the logo mark indicates items in stock for each brand.


**Stock**  
38,650  
Items

## Stainless Steel Ball-Point Hexagonal Wrench



- Features**
- Stainless steel Ball-point L type wrench excellent in corrosion resistance, chemicals resistance and hygienic.
  - A Ball-point type that can be used by tilting about 25°.

**Materials** •Stainless Steel (SUS420) **Origin** •Taiwan

**Order Unit:** 1 Piece

TRUSCO NAKAYAMA CORPORATION

| Order Code | Item No. | Price (per piece) | MSRP (per piece) | Opposite Side Dimension (mm) | Length Excl. Head (mm) | Total Length (mm) | SPQ (piece) | Weight (g) |
|------------|----------|-------------------|------------------|------------------------------|------------------------|-------------------|-------------|------------|
| 445-6491   | TSSB-15  | ¥ 546             | ¥ 590            | 1.5                          | 14                     | 77                | 12          | 3.0        |
| 445-6505   | TSSB-20  | ¥ 546             | ¥ 590            | 2.0                          | 16                     | 83                | 12          | 3.5        |
| 445-6513   | TSSB-25  | ¥ 555             | ¥ 600            | 2.5                          | 18                     | 90                | 12          | 5.8        |
| 445-6521   | TSSB-30  | ¥ 555             | ¥ 600            | 3.0                          | 20                     | 98                | 12          | 11.0       |
| 445-6530   | TSSB-40  | ¥ 573             | ¥ 620            | 4.0                          | 25                     | 106               | 12          | 20.0       |
| 445-6548   | TSSB-50  | ¥ 658             | ¥ 710            | 5.0                          | 28                     | 118               | 12          | 32.0       |
| 445-6556   | TSSB-60  | ¥ 768             | ¥ 830            | 6.0                          | 32                     | 137               | 12          | 49.0       |
| 445-6564   | TSSB-80  | ¥1,074            | ¥1,160           | 8.0                          | 36                     | 156               | 12          | 112.0      |
| 445-6483   | TSSB-100 | ¥1,389            | ¥1,500           | 10.0                         | 40                     | 170               | 12          | 181.0      |

**Set** **Features** •The holder rotates, making it easy to put in and out wrenches of various sizes.

**Order Unit:** 1 Set

| Order Code | Item No. | Price (per set) | MSRP (per set) | Set Contents (mm)              | Set Contents (piece) | SPQ (set) | Weight (g/set) |
|------------|----------|-----------------|----------------|--------------------------------|----------------------|-----------|----------------|
| 445-6572   | TSSB-95  | ¥5,091          | ¥5,500         | 1.5, 2, 2.5, 3, 4, 5, 6, 8, 10 | 9                    | 6         | 448            |

**Contact us:0120-509-849** <http://www.orange-book.com/>


**Stock**  
38,650  
Items

## Stainless Steel Ball-Point Hexagonal Wrench (long type)



- Features**
- Stainless steel long Ball-point L type wrench excellent corrosion resistance, chemicals resistance, hygiene.
  - A Ball-point type that can be used by tilting about 25°.

**Materials** •Stainless Steel (SUS420) **Origin** •Taiwan

**Order Unit:** 1 Piece

TRUSCO NAKAYAMA CORPORATION

| Order Code | Item No.  | Price (per piece) | MSRP (per piece) | Opposite Side Dimension (mm) | Length Excl. Head (mm) | Total Length (mm) | SPQ (piece) | Weight (g) |
|------------|-----------|-------------------|------------------|------------------------------|------------------------|-------------------|-------------|------------|
| 445-6599   | TSSBL-15  | ¥ 658             | ¥ 710            | 1.5                          | 14                     | 90                | 12          | 3.5        |
| 445-6602   | TSSBL-20  | ¥ 658             | ¥ 710            | 2.0                          | 16                     | 100               | 12          | 4.0        |
| 445-6611   | TSSBL-25  | ¥ 666             | ¥ 720            | 2.5                          | 18                     | 112               | 12          | 7.0        |
| 445-6629   | TSSBL-30  | ¥ 666             | ¥ 720            | 3.0                          | 20                     | 126               | 12          | 14.0       |
| 445-6637   | TSSBL-40  | ¥ 741             | ¥ 800            | 4.0                          | 25                     | 140               | 12          | 25.0       |
| 445-6645   | TSSBL-50  | ¥ 879             | ¥ 950            | 5.0                          | 28                     | 160               | 12          | 41.0       |
| 445-6653   | TSSBL-60  | ¥1,130            | ¥1,220           | 6.0                          | 32                     | 180               | 12          | 62.0       |
| 445-6661   | TSSBL-80  | ¥1,444            | ¥1,560           | 8.0                          | 36                     | 200               | 12          | 139.0      |
| 445-6581   | TSSBL-100 | ¥1,981            | ¥2,140           | 10.0                         | 40                     | 224               | 12          | 228.0      |

**Set** **Features** •The holder rotates, making it easy to put in and out wrenches of various sizes.

**Order Unit:** 1 Set

| Order Code | Item No. | Price (per set) | MSRP (per set) | Set Contents (mm)              | Set Contents (piece) | SPQ (set) | Weight (g/set) |
|------------|----------|-----------------|----------------|--------------------------------|----------------------|-----------|----------------|
| 445-6670   | TSSBL-95 | ¥6,480          | ¥7,000         | 1.5, 2, 2.5, 3, 4, 5, 6, 8, 10 | 9                    | 6         | 551            |

**Contact us:0120-509-849** <http://www.orange-book.com/>


**Stock**  
2,937  
Items

## SUS Long Ball-Point L Type Wrench



- Features**
- Ideal for tightening/loosening hexagon socket head cap screw.
  - A ball point type that can be used tilted.

**Materials** •Stainless Steel

**Origin** •Japan

**Order Unit:** 1 Piece

TONE CO. LTD.

| Order Code | Item No. | Price (per piece) | MSRP (per piece) | Opposite Side Dimension (mm) | Length Excl. Head (mm) | Total Length (mm) | SPQ (piece) | Weight (g) |
|------------|----------|-------------------|------------------|------------------------------|------------------------|-------------------|-------------|------------|
| 389-3812   | SBL-2.5  | ¥1,754            | ¥1,625           | 2.5                          | 18                     | 84                | 1           | 20         |
| 389-3758   | SBL-03   | ¥1,862            | ¥1,725           | 3.0                          | 20                     | 95                | 1           | 20         |
| 389-3766   | SBL-04   | ¥1,922            | ¥1,780           | 4.0                          | 23                     | 107               | 1           | 25         |
| 389-3774   | SBL-05   | ¥2,078            | ¥1,925           | 5.0                          | 28                     | 120               | 1           | 35         |
| 389-3782   | SBL-06   | ¥2,786            | ¥2,580           | 6.0                          | 32                     | 135               | 1           | 65         |
| 389-3791   | SBL-08   | ¥3,823            | ¥3,540           | 8.0                          | 36                     | 150               | 1           | 155        |
| 389-3804   | SBL-10   | ¥4,666            | ¥4,320           | 10.0                         | 40                     | 170               | 1           | 180        |

**Set** **Accessories** •Wrench stand

**Order Unit:** 1 Set

| Order Code | Item No. | Price (per set) | MSRP (per set) | Set Contents (mm)      | Set Contents (piece) | SPQ (set) | Weight (g/set) |
|------------|----------|-----------------|----------------|------------------------|----------------------|-----------|----------------|
| 389-3821   | SBL700   | ¥21,276         | ¥19,700        | 2.5, 3, 4, 5, 6, 8, 10 | 7                    | 1         | 680            |

**Contact us:0721-56-1850** <http://www.tonetool.co.jp/>