











Type	Gate  125			Gate  125			Gate  125 Body Marking: Class 125 PN25			Gate  PN16			Gate  PN16 Body Marking: Class 125 PN16			
Fig	125E-BS-N			125E-BS-NR-NPT<UL1R1>			125E-BS-N-PN25-			H-BS-PN16-			H-BS(B62)PN16-			
Product Code	206A			206A			206P			275P			272P			
inch	mm	L	H	D	L	H	D	L	H	D	L	H	D	L	H	D
1/4	8	42	75	48	42	75	48									
3/8	10	38	74	48	38	74	48				43	76	48			
1/2	15	42	74	48	42	74	48	42	74	48	43	76	48	43	76	48
3/4	20	47	85	55	47	85	55	47	85	55	48	86	55	48	85	55
1	25	50	97	63	50	97	63	50	97	63	53	98	63	53	97	63
1 1/4	32	60	116	70	60	116	70	60	116	70	60	118	70	60	117	70
1 1/2	40	63	125	80	63	125	80	63	125	80	63	126	80	63	128	70
2	50	72	155	90	72	155	90	72	155	90	71	154	80	71	151	80
2 1/2	65	90	201	110	90	201	110				87	180	90	87	180	90
3	80	100	223	125	100	223	125				96	211	100	96	211	100
4	100	140	302	160	140	302	160									
Body	Cast Bronze			Cast Bronze			Cast Bronze			Cast Bronze			Cast Bronze			
Bonnet/Cap	Cast Bronze			Cast Bronze			Cast Bronze			Cast Bronze			Cast Bronze			
Stem	Dezincification Resistant Brass			Dezincification Resistant Brass			Dezincification Resistant Brass			Dezincification Resistant Brass			Dezincification Resistant Brass			
Disc/Ball	Dezincification Resistant Brass or Cast Bronze			Dezincification Resistant Brass or Cast Bronze			Dezincification Resistant Brass or Cast Bronze			Cast Bronze			Cast Bronze			
Packing	Aramid Fibers Graphite			Aramid Fibers Graphite			Aramid Fibers Graphite			Aramid Fibers Graphite			Aramid Fibers Graphite			
Hand Wheel	Aluminum Die-Cast			Aluminum Die-Cast			Aluminum Die-Cast			Aluminum Die-Cast			Aluminum Die-Cast			
Note	Screwed Bonnet (Size 2 1/2 to 4) Inside Screw Non Rising Stem			Screwed Bonnet (Size 2 1/2 to 4) Inside Screw Non Rising Stem			Screwed Bonnet (Size 2 1/2 to 4) Inside Screw Non Rising Stem			Non-rising Stem			Non-rising Stem			

Type	Gate  150			Gate  150			Gate  125 Body Marking: Class 125 WSD*			Gate  PN25			Gate  150			
Fig	150-BS-N			150-BSF-NR-F150-<UC8R1>			125E-BS-SE-NR-<ZS2R1>			125E-BS-SE-NR-<Z01R2>			150-BSR-N			
Product Code	204A			205A			207A			207P			209			
inch	mm	L	H	D	L	H	D	L	H	D	L	H	D	L	H	D
3/8	10	43	87	48												
1/2	15	48	96	55	75	96	55	46	81	48	46	81	48	51	137	55
3/4	20	53	112	63	80	112	63	61	90	55	61	90	55	56	157	70
1	25	62	123	70	95	123	70	72	106	63	72	106	63	66	180	70
1 1/4	32	69	141	80	110	142	80	78	119	70	78	119	70	68	216	80
1 1/2	40	75	164	90	120	165	90	87	135	80	87	135	80	74	257	90
2	50	86	197	100	140	197	100	102	159	90	102	159	90	84	296	100
2 1/2	65	105	224	110	165	224	110									
3	80	116	261	125	190	263	140									
4	100				230	309	225									
Body	Cast Bronze			Cast Bronze			Cast Bronze			Cast Bronze			Cast Bronze			
Bonnet/Cap	Forged Brass			Forged Brass or Cast Bronze			Cast Bronze			Cast Bronze			Cast Bronze			
Stem	Dezincification Resistant Brass			Dezincification Resistant Brass			Dezincification Resistant Brass			Dezincification Resistant Brass			Cast Bronze			
Disc/Ball	Cast Bronze			Cast Bronze			Dezincification Resistant Brass or Cast Bronze			Dezincification Resistant Brass			Cast Bronze			
Packing	Aramid Fibers Graphite			Aramid Fibers Graphite			Aramid Fibers Graphite			Aramid Fibers Graphite			Aramid Fibers Graphite			
Hand Wheel	Aluminum Die-Cast			Zinc Die-Cast or Aluminum Die-Cast or Ductile Iron			Aluminum Die-Cast						Aluminum Die-Cast			
Note	Screwed Bonnet Inside Screw Non Rising Stem			Screwed Bonnet Inside Screw Non Rising Stem			Inside Screw Non Rising Stem *Water Supply Dept (HK)			Non-rising Stem Solid Wedge Disc			Screwed Bonnet Inside Screw			